

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192832

Luminaire Tested: **LDA6A75950D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75950D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7113.5 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192832

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192832

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	96	89	84	80		87	82	78			84	80	77			82
4	92	83	76	71	90	82	76	71		79	74	70			77	73	69			75
5	86	76	69	64	84	75	68	63		73	67	63			71	66	62			69
6	80	69	62	57	79	69	62	57		67	61	56			65	60	56			64
7	75	64	56	51	73	63	56	51		62	55	51			60	55	50			59
8	70	59	51	46	69	58	51	46		57	50	46			56	50	46			54
9	66	54	47	42	64	53	47	42		52	46	42			51	46	42			50
10	61	50	43	38	60	49	43	38		48	42	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	110090	110090	110090
5°	213317	104908	35384
10°	362429	91810	15887
15°	558477	73224	25261
20°	808465	47651	43946
25°	1186157	45982	56501
30°	1379187	43564	43298
35°	1395968	23082	22888
40°	1155765	8702	9611
45°	872889	2962	3504
50°	597217	1092	1092
55°	83075	946	143
60°	2171	921	0
65°	545	1284	0
70°	240	1587	0
75°	0	2097	0
80°	0	3567	474
85°	0	7108	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192832

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.7	3.0
10°-20°	890.6	12.5
20°-30°	2031.6	28.6
30°-40°	2351.0	33.1
40°-50°	1417.8	19.9
50°-60°	192.6	2.7
60°-70°	6.2	0.1
70°-80°	6.7	0.1
80°-90°	6.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3132.8	44.0
0°-40°	5483.8	77.1
0°-60°	7094.3	99.7
0°-90°	7113.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7113.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2008	2008	2008	2008	2008	
5°	3876	3174	1906	1043	643	451
15°	9840	5531	1290	397	445	2913
25°	19610	6555	760	914	934	8874
35°	20859	4997	345	352	342	12571
45°	11259	1361	38	47	45	8804
55°	869	10	10	7	2	1704
65°	4	6	10	6	0	6
75°	0	7	10	7	0	0
85°	0	7	11	7	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P1192832

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2
2.5°	2904.1	2877.3	2888.6	2859.1	2784.1	2768.5	2767.0	2747.4	2683.7	2634.2	2574.9
5°	3876.4	3875.1	3882.1	3818.6	3687.2	3646.1	3626.4	3578.2	3424.2	3305.5	3174.2
7.5°	5090.5	5082.0	5073.5	4957.7	4751.2	4672.1	4621.3	4447.5	4235.5	4024.9	3790.3
10°	6510.8	6506.7	6474.0	6270.5	5939.9	5794.2	5695.2	5419.8	5079.2	4779.5	4381.0
12.5°	8159.9	8121.8	8064.0	7765.8	7312.1	7153.7	6936.2	6499.5	5976.5	5517.3	4960.4
15°	9840.3	9785.3	9682.1	9299.1	8736.6	8466.7	8196.9	7621.6	6912.2	6245.1	5531.4
17.5°	11484.0	11423.3	11181.5	10531.4	9981.7	9652.3	9352.7	8562.7	7729.0	6871.2	5966.7
20°	13858.2	13637.7	13216.5	12192.0	11170.3	10576.7	10226.1	9391.0	8359.2	7360.1	6276.2
22.5°	17029.5	16540.6	15643.1	13978.2	12518.5	11662.0	11088.2	9977.3	8812.9	7679.5	6467.0
25°	19610.0	19388.1	18367.9	15999.3	13721.1	12711.9	11913.5	10443.8	9143.6	7893.0	6554.6
27.5°	21273.4	21218.3	20052.3	17672.5	14703.3	13379.1	12487.3	10751.8	9303.2	7938.1	6512.1
30°	21787.8	21874.0	20754.8	18240.7	14987.4	13513.2	12538.2	10756.1	9180.4	7733.3	6240.9
32.5°	21749.7	21753.9	20381.7	17750.3	14525.2	13123.2	12114.3	10398.5	8726.7	7220.2	5725.0
35°	20859.3	20640.4	19088.6	16243.7	13449.8	12213.2	11274.8	9706.0	7979.1	6448.6	4997.2
37.5°	18904.9	18618.0	16809.0	14314.6	12176.3	11033.0	10275.5	8797.4	7088.7	5624.6	4245.4
40°	16150.4	15743.4	14251.0	12521.3	10783.0	9923.7	9287.7	7781.3	6136.3	4816.2	3540.1
42.5°	13393.2	13193.9	12207.5	10801.3	9611.5	8803.1	8138.8	6717.0	5220.5	4019.3	2648.5
45°	11259.1	11088.2	10425.4	9498.3	8330.9	7593.4	6953.1	5607.7	4056.0	2696.4	1360.9
47.5°	9704.8	9566.2	8931.7	7958.0	6677.6	5870.6	5210.6	3677.3	2297.9	1164.5	340.5
50°	7002.6	6861.2	6239.5	5111.7	3955.6	3280.1	2805.2	1642.2	651.5	236.0	35.4
52.5°	3432.8	3316.9	2894.3	2166.5	1454.2	1045.8	764.6	308.0	74.9	25.4	17.0
55°	869.2	798.4	665.7	418.3	205.0	123.0	79.1	28.3	18.4	14.0	9.9
57.5°	49.5	48.0	43.8	32.4	24.1	21.2	18.4	14.0	9.9	8.4	7.1
60°	19.8	18.4	17.0	14.0	11.3	9.9	9.9	7.1	5.6	5.6	5.6
62.5°	8.4	8.4	8.4	7.1	5.6	5.6	5.6	4.2	5.6	5.6	5.6
65°	4.2	4.2	4.2	2.7	2.7	2.7	4.2	4.2	4.2	5.6	5.6
67.5°	2.7	1.5	1.5	1.5	2.7	2.7	2.7	4.2	4.2	5.6	5.6
70°	1.5	1.5	1.5	1.5	2.7	2.7	2.7	4.2	4.2	5.6	7.1
72.5°	0.0	1.5	1.5	1.5	2.7	2.7	2.7	4.2	4.2	5.6	7.1
75°	0.0	1.5	1.5	1.5	2.7	2.7	2.7	4.2	5.6	5.6	7.1
77.5°	0.0	1.5	1.5	1.5	2.7	2.7	2.7	4.2	5.6	5.6	7.1
80°	0.0	1.5	1.5	1.5	2.7	2.7	2.7	4.2	5.6	5.6	7.1
82.5°	0.0	0.0	1.5	1.5	2.7	2.7	2.7	4.2	5.6	5.6	7.1
85°	0.0	0.0	1.5	1.5	2.7	2.7	2.7	4.2	5.6	5.6	7.1
87.5°	0.0	0.0	1.5	1.5	2.7	2.7	2.7	4.2	4.2	5.6	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192832

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2
2.5°	2498.6	2447.7	2372.9	2323.5	2275.3	2230.0	2155.2	2112.9	2036.4	1965.8	1905.0
5°	3015.8	2888.6	2734.6	2603.2	2518.4	2435.0	2283.8	2172.1	2032.2	1906.4	1790.6
7.5°	3538.8	3314.0	3061.0	2844.8	2713.5	2584.8	2358.6	2177.9	1980.0	1800.4	1629.5
10°	4013.7	3675.9	3318.2	3008.8	2830.8	2664.0	2365.8	2125.4	1871.1	1649.3	1434.4
12.5°	4454.5	3992.4	3526.0	3121.9	2901.4	2700.7	2336.0	2042.0	1739.7	1476.9	1226.7
15°	4847.4	4253.8	3677.3	3186.8	2928.2	2690.8	2266.9	1924.8	1584.2	1290.2	973.8
17.5°	5145.6	4416.4	3743.7	3176.9	2880.2	2615.9	2148.1	1777.8	1418.9	1062.8	705.1
20°	5326.5	4485.5	3729.5	3100.7	2776.9	2497.1	2006.8	1618.1	1219.6	816.8	621.7
22.5°	5402.8	4479.9	3663.1	2986.3	2649.7	2367.2	1871.1	1462.7	1010.5	739.1	648.8
25°	5415.5	4422.1	3569.8	2860.3	2524.0	2242.8	1734.0	1286.0	877.6	760.2	726.4
27.5°	5318.0	4286.3	3394.7	2679.5	2347.4	2056.3	1529.1	1021.8	823.9	757.5	780.1
30°	5029.8	3976.8	3085.2	2361.5	2040.8	1749.5	1092.4	801.3	684.0	688.2	693.8
32.5°	4522.4	3462.4	2587.7	1896.5	1546.1	1153.2	679.7	535.6	520.1	520.1	517.2
35°	3845.4	2833.5	2030.7	1199.8	768.9	554.0	351.8	353.3	346.2	344.9	343.4
37.5°	3145.9	2235.7	1286.0	496.0	333.6	231.7	207.7	210.6	207.7	212.1	209.1
40°	2480.2	1380.7	469.1	158.2	117.3	113.2	115.9	118.8	118.8	121.6	121.6
42.5°	1441.4	457.9	123.0	63.5	63.5	60.7	62.2	65.0	66.5	67.9	66.5
45°	428.3	94.7	39.6	35.4	35.4	33.9	33.9	35.4	36.7	38.2	38.2
47.5°	67.9	26.8	22.7	19.8	19.8	19.8	19.8	19.8	21.2	21.2	22.7
50°	21.2	17.0	14.0	12.8	12.8	11.3	11.3	12.8	12.8	12.8	14.0
52.5°	12.8	9.9	9.9	8.4	9.9	9.9	8.4	9.9	9.9	9.9	11.3
55°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	9.9	9.9	9.9
57.5°	7.1	7.1	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
60°	7.1	7.1	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	9.9
62.5°	7.1	7.1	8.4	8.4	8.4	8.4	8.4	8.4	9.9	9.9	9.9
65°	7.1	7.1	8.4	8.4	8.4	8.4	8.4	9.9	9.9	9.9	9.9
67.5°	7.1	8.4	8.4	8.4	8.4	9.9	9.9	9.9	9.9	9.9	9.9
70°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
72.5°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
75°	8.4	8.4	8.4	9.9	9.9	9.9	9.9	9.9	9.9	9.9	11.3
77.5°	8.4	8.4	9.9	9.9	9.9	9.9	9.9	9.9	11.3	11.3	11.3
80°	8.4	8.4	9.9	9.9	9.9	9.9	9.9	11.3	11.3	11.3	11.3
82.5°	8.4	8.4	9.9	9.9	9.9	9.9	9.9	11.3	11.3	11.3	11.3
85°	8.4	8.4	9.9	9.9	9.9	9.9	9.9	11.3	11.3	11.3	11.3
87.5°	8.4	8.4	9.9	9.9	9.9	9.9	9.9	11.3	11.3	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192832

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2
2.5°	1852.8	1787.7	1756.7	1712.9	1681.8	1612.5	1584.2	1536.2	1496.6	1431.7	1435.8
5°	1691.7	1568.6	1485.3	1420.3	1375.1	1264.8	1191.3	1113.5	1042.9	955.3	922.8
7.5°	1468.3	1317.2	1190.0	1112.3	1054.2	907.3	744.7	617.6	521.6	452.2	425.4
10°	1245.1	1048.6	846.6	726.4	643.0	501.7	429.6	395.6	364.6	326.5	301.1
12.5°	985.1	705.1	521.6	473.4	439.4	392.9	346.2	309.5	316.6	317.9	327.9
15°	672.7	507.3	449.5	416.9	380.1	353.3	368.8	378.7	397.1	398.5	411.3
17.5°	546.9	476.3	429.6	428.3	431.1	446.6	470.6	483.4	507.3	512.9	531.4
20°	546.9	505.9	545.5	545.5	552.6	573.8	605.0	623.2	650.0	660.1	682.6
22.5°	623.2	651.5	701.0	706.6	709.5	732.2	771.6	790.0	821.0	826.7	850.7
25°	760.2	785.8	831.1	835.2	836.7	853.6	883.3	893.2	914.5	903.1	917.2
27.5°	804.0	815.4	843.6	846.6	839.5	846.6	857.9	857.9	864.9	842.4	846.6
30°	706.6	709.5	723.5	725.0	709.5	712.3	713.8	712.3	710.8	686.9	686.9
32.5°	524.3	524.3	542.7	538.5	521.6	525.7	525.7	525.7	524.3	504.6	501.7
35°	347.7	349.1	364.6	361.8	349.1	351.8	351.8	356.2	351.8	340.5	337.8
37.5°	212.1	213.3	220.5	221.9	217.7	219.0	220.5	219.0	221.9	216.2	213.3
40°	123.0	125.7	131.4	132.8	131.4	131.4	132.8	134.3	140.0	132.8	129.9
42.5°	72.1	73.5	76.3	76.3	76.3	76.3	77.7	79.1	80.5	79.1	77.7
45°	41.1	42.3	43.8	43.8	45.2	43.8	45.2	45.2	46.7	45.2	45.2
47.5°	24.1	24.1	25.4	25.4	26.8	25.4	26.8	26.8	26.8	25.4	25.4
50°	14.0	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	14.0	14.0
52.5°	11.3	11.3	11.3	11.3	11.3	9.9	9.9	9.9	9.9	8.4	8.4
55°	9.9	9.9	9.9	9.9	9.9	9.9	8.4	7.1	7.1	5.6	5.6
57.5°	8.4	9.9	9.9	9.9	9.9	8.4	8.4	7.1	5.6	4.2	4.2
60°	9.9	9.9	9.9	9.9	8.4	8.4	8.4	7.1	5.6	4.2	4.2
62.5°	9.9	9.9	9.9	9.9	9.9	8.4	8.4	7.1	5.6	4.2	4.2
65°	9.9	9.9	9.9	9.9	9.9	8.4	8.4	7.1	5.6	4.2	4.2
67.5°	9.9	9.9	9.9	9.9	9.9	8.4	8.4	7.1	5.6	5.6	4.2
70°	9.9	11.3	11.3	9.9	9.9	9.9	8.4	7.1	7.1	5.6	4.2
72.5°	9.9	11.3	11.3	9.9	9.9	9.9	8.4	7.1	7.1	5.6	4.2
75°	11.3	11.3	11.3	11.3	9.9	9.9	8.4	8.4	7.1	5.6	4.2
77.5°	11.3	11.3	11.3	11.3	9.9	9.9	8.4	8.4	7.1	5.6	4.2
80°	11.3	11.3	11.3	11.3	11.3	9.9	9.9	8.4	7.1	5.6	5.6
82.5°	11.3	11.3	11.3	11.3	11.3	9.9	9.9	8.4	7.1	5.6	5.6
85°	11.3	11.3	11.3	11.3	11.3	9.9	9.9	8.4	7.1	5.6	4.2
87.5°	11.3	11.3	11.3	11.3	9.9	9.9	8.4	8.4	7.1	5.6	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192832

CATALOG NUMBER: LDA6A75950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2	2008.2
2.5°	1383.6	1351.0	1336.9	1359.5	1348.3	1314.2	1321.4	1300.2
5°	825.3	775.9	744.7	759.0	713.8	672.7	672.7	643.0
7.5°	398.5	383.0	374.5	377.4	367.5	354.7	347.7	347.7
10°	279.8	274.1	275.6	275.6	284.1	282.7	286.8	285.4
12.5°	332.2	334.9	336.3	342.0	349.1	349.1	353.3	350.6
15°	425.4	422.7	431.1	432.5	443.8	445.1	450.7	445.1
17.5°	541.2	546.9	555.4	554.0	576.7	577.9	577.9	576.7
20°	696.7	701.0	709.5	712.3	739.1	742.0	751.8	753.3
22.5°	866.3	866.3	870.5	876.1	901.7	903.1	907.3	907.3
25°	924.2	915.7	917.2	924.2	938.4	932.7	936.9	934.1
27.5°	849.3	836.7	833.8	843.6	853.6	838.0	843.6	843.6
30°	689.6	678.3	675.6	685.5	692.5	675.6	681.2	684.0
32.5°	504.6	497.4	496.0	503.2	508.8	494.5	500.2	504.6
35°	340.5	337.8	334.9	336.3	344.9	333.6	339.2	342.0
37.5°	216.2	210.6	212.1	214.8	220.5	213.3	219.0	219.0
40°	132.8	129.9	129.9	132.8	135.6	129.9	132.8	134.3
42.5°	77.7	77.7	77.7	79.1	80.5	77.7	77.7	79.1
45°	45.2	43.8	43.8	45.2	46.7	43.8	45.2	45.2
47.5°	25.4	24.1	24.1	25.4	25.4	24.1	25.4	25.4
50°	14.0	12.8	12.8	14.0	14.0	12.8	12.8	12.8
52.5°	7.1	7.1	7.1	7.1	7.1	7.1	5.6	5.6
55°	4.2	4.2	2.7	2.7	2.7	2.7	2.7	1.5
57.5°	2.7	2.7	1.5	1.5	1.5	1.5	0.0	0.0
60°	2.7	2.7	1.5	1.5	1.5	0.0	0.0	0.0
62.5°	2.7	2.7	1.5	1.5	1.5	0.0	0.0	0.0
65°	2.7	2.7	1.5	1.5	1.5	0.0	0.0	0.0
67.5°	2.7	2.7	1.5	1.5	1.5	0.0	0.0	0.0
70°	4.2	2.7	2.7	1.5	1.5	1.5	0.0	0.0
72.5°	4.2	2.7	2.7	2.7	1.5	1.5	0.0	0.0
75°	4.2	2.7	2.7	2.7	1.5	1.5	0.0	0.0
77.5°	4.2	2.7	2.7	2.7	1.5	1.5	1.5	0.0
80°	4.2	2.7	2.7	2.7	1.5	1.5	1.5	1.5
82.5°	4.2	2.7	2.7	2.7	1.5	1.5	1.5	1.5
85°	4.2	2.7	2.7	2.7	1.5	1.5	1.5	0.0
87.5°	4.2	2.7	2.7	2.7	1.5	1.5	1.5	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)