

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204256

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1987.0 lumens
Efficiency: N/A
Efficacy: 139.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204256

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204256

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204256

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.3	5.5
10°-20°	282.9	14.2
20°-30°	370.0	18.6
30°-40°	391.8	19.7
40°-50°	365.4	18.4
50°-60°	276.8	13.9
60°-70°	149.9	7.5
70°-80°	40.2	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.2	38.4
0°-40°	1154.1	58.1
0°-60°	1796.3	90.4
0°-90°	1987.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1987.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1185	
5°	1168	109
15°	1011	283
25°	804	370
35°	626	392
45°	476	365
55°	311	277
65°	150	150
75°	35	40
85°	0	1
90°	0	



TEST NUMBER: P204256

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1185.0
2.5°	1180.8
5°	1167.6
7.5°	1139.4
10°	1102.4
12.5°	1059.0
15°	1011.1
17.5°	956.8
20°	908.9
22.5°	854.5
25°	804.5
27.5°	754.5
30°	706.6
32.5°	665.4
35°	626.2
37.5°	587.1
40°	550.1
42.5°	513.1
45°	476.2
47.5°	434.9
50°	393.6
52.5°	352.2
55°	311.0
57.5°	267.5
60°	226.1
62.5°	187.0
65°	150.0
67.5°	115.2
70°	84.8
72.5°	58.8
75°	34.8
77.5°	15.2
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)