

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192839

Luminaire Tested: **LDA6A75950D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75950D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7219.5 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192839

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192839

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	72741	72741	72741
5°	187805	67422	21076
10°	356267	51441	7081
15°	637041	33445	7055
20°	949224	22752	12864
25°	1083081	28375	80781
30°	1171300	23706	24156
35°	1230387	11538	7556
40°	1249842	4136	3843
45°	1113542	2744	2303
50°	715166	1936	1569
55°	188285	1338	803
60°	41992	1403	614
65°	4021	1660	726
70°	1346	2052	898
75°	318	2711	1504
80°	0	4420	2241
85°	0	8051	3522



TEST NUMBER: P1192839

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.1	2.2
10°-20°	841.0	11.6
20°-30°	1973.3	27.3
30°-40°	2269.7	31.4
40°-50°	1612.3	22.3
50°-60°	327.8	4.5
60°-70°	16.4	0.2
70°-80°	9.7	0.1
80°-90°	8.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2975.4	41.2
0°-40°	5245.2	72.7
0°-60°	7185.3	99.5
0°-90°	7219.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7219.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1327	1327	1327	1327	1327	
5°	3413	2469	1225	490	383	416
15°	11225	5046	589	133	124	3367
25°	17906	6078	469	1024	1336	8252
35°	18385	4268	172	127	113	11421
45°	14363	1518	35	38	30	10585
55°	1970	40	14	14	8	2657
65°	31	11	13	11	6	75
75°	2	7	13	11	7	3
85°	0	7	13	10	6	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192839

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9
2.5°	2286.4	2217.3	2183.3	2181.8	2082.9	2115.5	2082.9	2057.5	1965.6	1927.4	1864.0
5°	3412.8	3327.9	3260.2	3230.4	3060.9	3024.2	3007.3	2920.9	2728.8	2617.1	2468.8
7.5°	4741.0	4652.0	4540.3	4451.5	4205.4	4136.3	4091.0	3942.6	3658.5	3433.9	3156.9
10°	6400.1	6347.8	6166.9	6003.0	5630.0	5485.8	5350.2	5003.9	4632.4	4181.5	3823.9
12.5°	8634.3	8511.4	8189.3	7861.3	7276.3	7061.5	6836.8	6282.7	5714.8	5008.2	4417.5
15°	11224.6	11120.0	10624.0	10089.9	9257.6	8904.3	8552.3	7680.4	6807.0	5897.0	5046.4
17.5°	14206.3	14008.5	13515.3	12612.3	11447.9	10892.4	10236.7	9126.1	7865.5	6629.1	5572.0
20°	16271.0	16153.6	15736.9	14870.5	13545.0	12811.6	11997.6	10472.9	8748.8	7215.5	5916.9
22.5°	17400.0	17282.7	16970.4	16206.0	15119.3	14382.9	13437.6	11562.4	9415.7	7609.8	6079.3
25°	17905.9	17829.7	17658.6	17035.4	16029.3	15366.5	14472.0	12315.5	9832.7	7789.2	6078.0
27.5°	18373.8	18393.5	17971.0	17458.1	16531.0	15865.3	15017.5	12654.7	9914.6	7698.9	5883.0
30°	18503.7	18454.3	18269.3	17547.0	16683.6	15958.7	15049.9	12475.2	9595.4	7298.8	5495.7
32.5°	18423.3	18424.5	18250.8	17483.4	16468.8	15657.6	14635.9	11832.3	8973.4	6671.5	4893.6
35°	18385.1	18372.3	17921.6	17247.5	15958.7	15004.8	13717.4	10800.6	8111.5	5870.2	4267.7
37.5°	18006.2	17930.0	17605.0	16690.6	15004.8	13785.3	12398.9	9538.8	7050.2	5036.5	3626.1
40°	17465.0	17369.0	16840.5	15529.0	13374.0	12013.1	10635.4	8110.0	5939.4	4206.9	2911.1
42.5°	16355.8	16197.5	15396.3	13656.7	11274.0	10007.9	8866.1	6679.8	4855.6	3415.7	2235.7
45°	14363.2	14104.6	12995.3	11178.0	9100.6	8107.3	7142.1	5354.4	3887.6	2543.7	1517.8
47.5°	11532.7	11250.1	10243.9	8784.2	7125.1	6319.7	5499.9	3942.6	2629.8	1482.4	761.7
50°	8385.6	8190.5	7301.7	6070.9	4711.3	4035.9	3407.0	2198.9	1261.9	716.5	312.2
52.5°	4831.6	4691.6	4072.6	3195.1	2317.6	1940.2	1560.1	959.5	642.9	283.9	100.4
55°	1970.0	1889.4	1618.1	1370.7	1028.7	888.9	741.8	479.0	216.2	67.9	39.6
57.5°	963.8	953.9	795.6	637.3	469.1	378.7	285.4	96.2	52.4	33.9	25.4
60°	383.0	368.8	252.9	147.0	82.0	66.5	56.6	39.6	29.7	22.7	18.4
62.5°	66.5	65.0	55.1	46.7	38.2	33.9	31.0	24.1	19.8	15.5	14.0
65°	31.0	31.0	28.3	25.4	21.2	19.8	18.4	15.5	12.8	11.3	11.3
67.5°	15.5	15.5	14.0	12.8	11.3	11.3	9.9	9.9	8.4	8.4	8.4
70°	8.4	8.4	8.4	7.1	7.1	7.1	7.1	7.1	5.6	7.1	7.1
72.5°	5.6	5.6	5.6	4.2	2.7	4.2	4.2	4.2	5.6	7.1	7.1
75°	1.5	1.5	1.5	2.7	2.7	2.7	4.2	4.2	5.6	7.1	7.1
77.5°	1.5	1.5	1.5	1.5	2.7	2.7	2.7	4.2	5.6	7.1	7.1
80°	0.0	1.5	1.5	1.5	2.7	2.7	2.7	4.2	5.6	7.1	7.1
82.5°	0.0	0.0	1.5	1.5	2.7	2.7	2.7	4.2	5.6	7.1	7.1
85°	0.0	0.0	1.5	1.5	2.7	2.7	2.7	4.2	5.6	7.1	7.1
87.5°	0.0	0.0	1.5	1.5	2.7	2.7	2.7	4.2	5.6	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192839

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9
2.5°	1835.7	1762.2	1714.1	1629.3	1594.0	1578.5	1500.8	1425.8	1353.8	1301.6	1221.1
5°	2355.7	2238.4	2059.0	1890.8	1817.2	1770.7	1618.1	1476.7	1342.5	1225.2	1085.2
7.5°	2915.3	2673.6	2392.4	2122.5	1995.3	1910.5	1674.5	1468.3	1276.2	1098.0	907.2
10°	3452.4	3072.2	2662.3	2276.6	2104.1	1976.9	1668.9	1404.6	1154.6	924.1	719.4
12.5°	3910.2	3418.4	2874.4	2374.0	2149.4	1986.9	1616.7	1294.4	990.6	743.3	565.1
15°	4296.0	3684.1	3014.2	2406.7	2136.6	1944.4	1514.9	1143.3	811.2	589.3	456.5
17.5°	4567.4	3812.5	3046.7	2351.5	2047.8	1825.8	1360.8	949.6	637.3	476.3	360.4
20°	4725.6	3829.6	2967.6	2217.3	1892.3	1657.6	1167.2	746.2	517.2	390.0	279.8
22.5°	4749.7	3746.3	2812.2	2036.4	1712.7	1486.6	972.3	624.6	470.6	364.6	274.1
25°	4633.7	3581.0	2610.2	1859.7	1550.2	1318.5	840.7	631.6	528.5	469.1	487.6
27.5°	4409.0	3308.1	2378.4	1678.9	1380.7	1146.1	794.1	661.3	576.5	586.6	620.3
30°	4064.2	2923.9	2044.8	1372.2	1057.0	873.4	631.6	476.3	395.6	374.5	376.0
32.5°	3556.9	2441.9	1605.3	952.4	710.8	589.3	399.9	265.7	267.2	247.3	245.9
35°	2977.5	1965.6	1201.2	638.8	491.8	409.9	236.0	186.5	179.4	172.4	162.6
37.5°	2403.8	1519.0	799.9	436.7	313.7	227.6	118.7	97.4	90.5	84.9	84.9
40°	1830.0	1062.7	494.5	228.9	127.2	93.3	70.6	59.3	57.8	57.8	56.6
42.5°	1328.4	627.4	268.4	90.5	70.6	62.2	49.5	43.8	43.8	43.8	43.8
45°	706.6	319.4	103.1	56.6	46.7	43.8	36.7	33.9	33.9	35.4	35.4
47.5°	326.5	120.1	52.4	38.2	32.4	32.4	28.3	26.8	26.8	28.3	28.3
50°	117.3	49.5	33.9	26.8	24.1	25.4	22.7	21.2	22.7	22.7	22.7
52.5°	45.2	31.0	24.1	21.2	18.4	19.8	17.0	17.0	18.4	18.4	18.4
55°	28.3	22.7	18.4	15.5	14.0	15.5	14.0	14.0	14.0	14.0	14.0
57.5°	19.8	17.0	14.0	12.8	11.3	12.8	12.8	12.8	12.8	12.8	12.8
60°	15.5	12.8	11.3	11.3	11.3	11.3	11.3	11.3	11.3	12.8	12.8
62.5°	12.8	11.3	11.3	11.3	11.3	11.3	11.3	11.3	12.8	12.8	12.8
65°	11.3	9.9	11.3	11.3	9.9	11.3	11.3	11.3	12.8	12.8	14.0
67.5°	8.4	8.4	8.4	9.9	9.9	9.9	11.3	11.3	12.8	12.8	12.8
70°	8.4	8.4	9.9	9.9	9.9	9.9	11.3	11.3	12.8	12.8	12.8
72.5°	8.4	8.4	9.9	9.9	9.9	11.3	11.3	11.3	12.8	12.8	12.8
75°	8.4	8.4	9.9	9.9	9.9	11.3	11.3	11.3	12.8	12.8	12.8
77.5°	8.4	8.4	9.9	9.9	9.9	11.3	11.3	12.8	12.8	12.8	12.8
80°	8.4	9.9	9.9	11.3	11.3	11.3	11.3	12.8	12.8	14.0	14.0
82.5°	8.4	9.9	9.9	11.3	11.3	11.3	11.3	12.8	12.8	14.0	14.0
85°	8.4	9.9	9.9	11.3	11.3	11.3	11.3	12.8	12.8	12.8	12.8
87.5°	8.4	9.9	9.9	11.3	11.3	11.3	11.3	11.3	12.8	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192839

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9
2.5°	1167.2	1098.0	1028.7	995.0	965.2	922.8	869.0	825.2	778.6	754.6	699.5
5°	975.0	856.4	756.1	708.0	671.2	620.3	565.1	525.7	490.4	470.6	435.2
7.5°	754.6	641.6	554.0	517.2	490.4	439.4	398.5	357.6	320.8	294.0	258.5
10°	583.6	496.0	423.9	388.6	358.9	305.3	255.8	217.7	178.2	151.3	140.0
12.5°	463.5	381.6	308.0	272.8	241.6	186.5	149.9	142.7	135.6	132.8	128.6
15°	356.1	281.2	203.5	168.1	155.5	148.4	140.0	138.5	132.8	132.8	128.6
17.5°	267.2	183.8	155.5	152.6	151.3	148.4	144.1	142.7	141.2	141.2	140.0
20°	192.2	178.2	173.8	176.7	178.2	180.9	179.4	179.4	185.0	197.8	195.1
22.5°	269.9	292.6	316.6	325.0	356.1	387.2	415.5	450.7	534.1	630.3	652.9
25°	534.1	602.1	664.2	698.0	748.9	818.3	884.7	966.7	1024.5	1072.6	1127.6
27.5°	664.2	689.6	679.7	684.0	678.3	668.4	671.2	688.2	679.7	654.3	664.2
30°	392.9	412.6	401.3	407.0	391.5	391.5	387.2	395.6	390.0	380.1	377.4
32.5°	255.8	267.2	265.7	265.7	260.0	257.1	247.3	244.5	234.5	216.2	212.1
35°	154.0	147.0	140.0	135.6	132.8	132.8	131.4	131.4	127.2	123.0	121.6
37.5°	83.4	84.9	84.9	84.9	84.9	87.6	86.1	86.1	86.1	83.4	83.4
40°	57.8	60.7	60.7	60.7	62.2	62.2	62.2	63.5	62.2	62.2	62.2
42.5°	45.2	46.7	45.2	45.2	46.7	46.7	46.7	48.0	48.0	48.0	46.7
45°	36.7	36.7	35.4	36.7	36.7	38.2	38.2	38.2	38.2	36.7	36.7
47.5°	29.7	29.7	29.7	29.7	31.0	31.0	31.0	31.0	31.0	31.0	31.0
50°	24.1	24.1	24.1	25.4	25.4	25.4	24.1	25.4	25.4	25.4	24.1
52.5°	18.4	18.4	18.4	18.4	18.4	17.0	17.0	17.0	17.0	17.0	15.5
55°	14.0	14.0	14.0	14.0	14.0	15.5	14.0	15.5	14.0	14.0	12.8
57.5°	12.8	12.8	12.8	12.8	14.0	14.0	12.8	12.8	12.8	11.3	11.3
60°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8	11.3	9.9	9.9
62.5°	14.0	14.0	12.8	12.8	12.8	12.8	11.3	11.3	11.3	9.9	9.9
65°	14.0	14.0	12.8	14.0	14.0	12.8	12.8	11.3	11.3	9.9	9.9
67.5°	14.0	14.0	14.0	14.0	14.0	14.0	12.8	12.8	11.3	11.3	9.9
70°	14.0	14.0	14.0	14.0	14.0	14.0	12.8	12.8	11.3	11.3	9.9
72.5°	14.0	14.0	14.0	14.0	14.0	14.0	12.8	12.8	12.8	11.3	9.9
75°	14.0	14.0	14.0	14.0	14.0	12.8	12.8	12.8	11.3	11.3	9.9
77.5°	14.0	14.0	14.0	14.0	14.0	12.8	12.8	12.8	11.3	11.3	9.9
80°	14.0	14.0	14.0	14.0	14.0	14.0	12.8	12.8	11.3	11.3	9.9
82.5°	14.0	14.0	14.0	14.0	14.0	12.8	12.8	12.8	11.3	11.3	9.9
85°	14.0	12.8	12.8	12.8	12.8	12.8	11.3	11.3	9.9	9.9	8.4
87.5°	12.8	12.8	12.8	12.8	12.8	11.3	11.3	9.9	8.4	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192839

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9	1326.9
2.5°	699.5	686.7	681.1	671.2	662.8	658.6	642.9	661.3
5°	428.2	412.6	408.4	399.9	390.0	384.3	373.0	383.0
7.5°	244.5	226.1	217.7	210.6	200.7	192.2	182.3	187.9
10°	137.1	131.4	132.8	128.6	127.2	125.7	124.3	127.2
12.5°	127.2	123.0	124.3	121.6	120.1	120.1	118.7	120.1
15°	128.6	124.3	127.2	124.3	123.0	123.0	121.6	124.3
17.5°	140.0	137.1	140.0	137.1	138.5	137.1	138.5	140.0
20°	196.4	200.7	209.1	203.5	207.7	213.3	220.5	220.5
22.5°	691.1	781.5	792.7	838.0	953.9	949.6	1027.4	1030.1
25°	1206.8	1212.4	1263.4	1246.4	1247.9	1307.2	1301.6	1335.5
27.5°	693.8	692.3	702.4	684.0	689.6	693.8	678.3	696.7
30°	387.2	380.1	384.3	374.5	374.5	377.4	373.0	381.6
32.5°	214.8	209.1	209.1	202.1	200.7	199.3	195.1	199.3
35°	123.0	118.7	120.1	117.3	114.4	112.9	111.7	112.9
37.5°	84.9	82.0	83.4	80.5	77.7	76.3	74.9	76.3
40°	62.2	60.7	60.7	57.8	56.6	55.1	53.7	53.7
42.5°	46.7	45.2	45.2	42.3	41.1	39.6	38.2	39.6
45°	35.4	33.9	33.9	32.4	31.0	29.7	29.7	29.7
47.5°	31.0	29.7	31.0	29.7	28.3	28.3	28.3	28.3
50°	24.1	24.1	24.1	22.7	21.2	21.2	19.8	18.4
52.5°	15.5	14.0	14.0	12.8	12.8	11.3	11.3	11.3
55°	12.8	11.3	11.3	9.9	9.9	8.4	8.4	8.4
57.5°	9.9	9.9	8.4	8.4	7.1	7.1	7.1	7.1
60°	8.4	8.4	8.4	7.1	7.1	5.6	5.6	5.6
62.5°	8.4	7.1	7.1	7.1	5.6	5.6	5.6	5.6
65°	8.4	7.1	7.1	7.1	5.6	5.6	5.6	5.6
67.5°	8.4	7.1	7.1	7.1	5.6	5.6	5.6	5.6
70°	9.9	8.4	8.4	7.1	7.1	7.1	5.6	5.6
72.5°	9.9	8.4	8.4	8.4	7.1	7.1	7.1	7.1
75°	9.9	8.4	8.4	8.4	7.1	7.1	7.1	7.1
77.5°	9.9	8.4	8.4	8.4	7.1	7.1	7.1	7.1
80°	9.9	8.4	8.4	8.4	7.1	7.1	7.1	7.1
82.5°	8.4	8.4	8.4	7.1	7.1	7.1	7.1	7.1
85°	8.4	7.1	7.1	7.1	5.6	5.6	5.6	5.6
87.5°	5.6	5.6	4.2	4.2	4.2	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)