

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192842

Luminaire Tested: **LDA6A75950D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75950D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5824.8 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192842

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192842

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	91890	91890	91890
5°	145971	90760	58948
10°	219023	87089	39567
15°	313855	82532	29274
20°	414296	77176	24403
25°	497273	75222	35645
30°	555642	75417	53850
35°	571269	67532	45969
40°	550489	53701	34193
45°	485167	39880	26297
50°	378342	29526	18191
55°	218821	21610	11756
60°	102262	15032	5263
65°	47839	8250	2205
70°	22199	3638	1587
75°	9277	2393	1779
80°	4041	2652	2241
85°	943	4466	3522

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192842

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.3	3.0
10°-20°	636.2	10.9
20°-30°	1259.6	21.6
30°-40°	1628.6	28.0
40°-50°	1338.2	23.0
50°-60°	618.6	10.6
60°-70°	141.3	2.4
70°-80°	23.1	0.4
80°-90°	5.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2069.1	35.5
0°-40°	3697.7	63.5
0°-60°	5654.6	97.1
0°-90°	5824.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5824.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1676	1676	1676	1676	1676	
5°	2653	2281	1649	1193	1071	293
15°	5530	3698	1454	652	516	1615
25°	8221	4602	1244	611	589	3785
35°	8536	4212	1009	670	687	5285
45°	6258	2844	514	342	339	4762
55°	2290	1107	226	146	123	2152
65°	369	226	64	24	17	423
75°	44	25	11	10	8	58
85°	2	4	7	7	6	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192842

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2
2.5°	2128.4	2095.9	2115.8	2125.7	2074.7	2086.0	2091.6	2052.0	2040.8	2019.6	1957.4
5°	2652.6	2614.5	2630.2	2630.2	2555.2	2559.4	2556.6	2481.6	2440.8	2386.9	2281.1
7.5°	3270.4	3232.2	3234.9	3220.9	3114.9	3107.7	3062.5	2970.8	2890.1	2791.2	2633.0
10°	3934.6	3912.0	3897.7	3862.6	3722.6	3698.4	3632.1	3486.6	3353.8	3202.5	2979.1
12.5°	4714.7	4669.5	4628.4	4571.8	4389.5	4344.5	4251.1	4040.6	3845.6	3633.6	3338.1
15°	5530.1	5494.8	5428.5	5339.4	5106.2	5034.1	4912.5	4629.9	4386.8	4077.3	3698.4
17.5°	6374.0	6308.7	6211.3	6085.6	5804.3	5702.5	5551.3	5189.6	4867.3	4481.6	4023.7
20°	7101.6	7050.8	6916.6	6754.1	6431.8	6296.2	6118.1	5674.2	5279.9	4822.1	4283.7
22.5°	7733.4	7665.5	7500.3	7303.9	6943.5	6775.2	6574.5	6078.5	5598.0	5066.6	4474.4
25°	8221.1	8170.1	7973.6	7744.8	7349.0	7154.1	6932.1	6369.6	5836.9	5253.1	4601.6
27.5°	8618.2	8532.1	8312.8	8054.3	7627.5	7399.9	7165.4	6549.1	5972.4	5347.8	4649.6
30°	8777.8	8688.8	8457.1	8170.1	7717.9	7467.7	7226.1	6568.8	5962.6	5315.3	4591.7
32.5°	8748.1	8647.9	8400.5	8096.6	7634.5	7367.4	7122.9	6440.3	5821.3	5168.4	4434.8
35°	8536.2	8452.8	8197.0	7879.0	7418.3	7137.1	6881.3	6205.7	5585.2	4940.8	4211.6
37.5°	8216.7	8098.1	7859.2	7539.8	7052.2	6790.8	6537.8	5870.8	5264.4	4625.7	3933.2
40°	7692.4	7549.7	7310.8	7032.5	6568.8	6308.7	6078.5	5455.3	4858.9	4262.3	3601.0
42.5°	7032.5	6920.9	6699.0	6412.0	5986.7	5738.0	5531.6	4932.3	4403.8	3851.2	3234.9
45°	6258.0	6150.6	5961.2	5702.5	5318.2	5102.0	4912.5	4379.8	3903.4	3399.0	2843.6
47.5°	5419.9	5313.9	5148.5	4921.0	4577.6	4391.0	4225.7	3789.0	3339.5	2898.6	2411.0
50°	4436.2	4290.6	4200.4	4009.4	3722.6	3564.3	3437.1	3045.5	2713.5	2358.8	1953.1
52.5°	3311.3	3264.7	3134.6	3000.4	2798.2	2680.9	2597.5	2346.0	2070.5	1813.2	1503.7
55°	2289.5	2247.1	2168.0	2086.0	1950.2	1890.9	1828.7	1676.2	1492.4	1317.2	1106.6
57.5°	1447.2	1478.4	1427.4	1380.7	1298.8	1277.6	1229.6	1140.6	1027.4	917.2	785.8
60°	932.7	949.6	917.2	890.3	845.1	828.2	805.5	751.8	684.0	620.5	531.4
62.5°	590.7	599.2	580.8	565.3	539.8	532.9	517.2	486.2	445.2	407.0	350.6
65°	368.8	376.0	363.2	353.3	337.8	339.2	325.0	306.8	282.7	258.5	226.1
67.5°	227.6	231.7	223.4	217.7	207.7	207.7	199.3	187.9	172.4	158.2	137.1
70°	138.5	140.0	134.3	131.4	124.5	123.0	118.8	110.2	100.4	90.5	77.7
72.5°	80.5	82.0	77.7	74.9	70.6	70.6	67.9	63.6	59.3	51.0	43.8
75°	43.8	45.2	42.3	41.1	38.2	39.6	36.7	35.4	31.0	28.3	25.4
77.5°	22.7	24.1	22.7	21.2	21.2	21.2	19.8	18.4	18.4	15.5	15.5
80°	12.8	12.8	12.8	12.8	12.8	11.3	11.3	11.3	11.3	11.3	9.9
82.5°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	5.6
85°	1.5	1.5	2.7	2.7	2.7	2.7	2.7	2.7	2.7	4.2	4.2
87.5°	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.7	2.7	2.7	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192842

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2
2.5°	1939.0	1937.6	1872.5	1844.4	1821.8	1786.4	1761.0	1734.0	1710.1	1666.3	1629.5
5°	2227.3	2187.6	2080.3	2012.5	1970.2	1913.6	1851.3	1789.3	1728.5	1649.3	1584.3
7.5°	2529.8	2444.9	2283.8	2170.9	2105.7	2026.6	1922.1	1824.5	1725.6	1616.8	1523.6
10°	2818.2	2679.7	2474.7	2302.2	2213.2	2111.4	1967.3	1831.6	1701.5	1564.5	1448.6
12.5°	3112.0	2914.2	2647.0	2423.8	2310.7	2184.9	1999.7	1831.6	1670.4	1512.3	1375.1
15°	3403.2	3141.7	2809.6	2532.6	2395.5	2245.7	2022.4	1821.8	1632.4	1454.2	1301.7
17.5°	3652.0	3328.2	2928.3	2607.6	2446.4	2276.8	2021.0	1792.0	1581.4	1389.2	1226.7
20°	3845.6	3462.5	3011.7	2645.7	2464.7	2279.7	1998.5	1748.2	1523.6	1322.9	1156.1
22.5°	3977.0	3550.1	3054.1	2652.6	2459.1	2264.1	1963.0	1704.5	1471.2	1270.5	1103.6
25°	4058.9	3593.9	3066.9	2642.7	2439.3	2237.2	1930.6	1666.3	1437.3	1243.6	1088.2
27.5°	4074.4	3581.3	3041.4	2601.9	2392.6	2189.1	1883.9	1629.5	1407.7	1228.1	1088.2
30°	3998.2	3499.2	2955.2	2509.9	2305.1	2105.7	1806.1	1563.0	1355.3	1191.4	1064.2
32.5°	3852.5	3348.1	2812.5	2374.3	2175.1	1988.6	1700.2	1468.5	1267.8	1116.4	1002.0
35°	3642.1	3145.9	2627.2	2203.3	2009.7	1835.8	1551.7	1339.8	1149.0	1009.1	903.1
37.5°	3386.2	2902.8	2411.0	2008.2	1824.5	1662.1	1390.7	1191.4	1014.8	883.3	788.5
40°	3075.3	2640.0	2168.0	1793.5	1618.1	1471.2	1221.1	1028.9	862.1	750.4	664.2
42.5°	2750.3	2346.0	1909.3	1553.1	1397.7	1257.9	1035.9	863.5	715.2	623.2	555.5
45°	2415.2	2019.6	1638.0	1321.4	1204.0	1047.3	842.4	702.4	582.3	514.4	460.8
47.5°	2038.0	1703.0	1351.2	1072.7	949.6	843.6	672.7	559.7	481.9	422.7	381.6
50°	1632.4	1365.2	1070.0	832.5	730.7	650.0	524.3	446.6	387.2	346.2	315.1
52.5°	1255.0	1044.4	805.5	610.6	546.9	486.2	408.4	354.7	312.4	281.2	258.5
55°	932.7	761.7	579.4	452.2	407.0	367.5	320.8	278.5	247.3	226.1	207.7
57.5°	657.2	531.4	407.0	327.9	303.9	278.5	243.0	214.8	193.6	176.7	162.6
60°	439.6	361.8	286.8	240.3	223.4	206.3	183.8	163.9	148.4	137.1	123.0
62.5°	295.5	243.0	200.7	172.4	161.1	149.9	134.3	120.1	108.8	97.4	86.1
65°	189.4	161.1	135.6	117.3	108.8	103.1	91.8	82.0	73.5	63.6	55.1
67.5°	115.9	100.4	84.9	73.5	69.2	65.0	58.0	51.0	45.2	38.2	32.4
70°	67.9	59.3	51.0	43.8	42.3	39.6	33.9	29.7	26.8	22.7	19.8
72.5°	39.6	35.4	29.7	26.8	25.4	22.7	21.2	18.4	15.5	14.0	12.8
75°	22.7	19.8	17.0	15.5	15.5	14.0	12.8	12.8	11.3	11.3	9.9
77.5°	14.0	12.8	11.3	11.3	11.3	9.9	9.9	9.9	9.9	8.4	8.4
80°	9.9	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
82.5°	5.6	5.6	5.6	5.6	5.6	7.1	7.1	7.1	7.1	7.1	8.4
85°	4.2	5.6	5.6	5.6	5.6	5.6	7.1	7.1	7.1	7.1	7.1
87.5°	4.2	5.6	5.6	5.6	5.6	5.6	7.1	7.1	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192842

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2
2.5°	1608.3	1585.7	1516.4	1540.3	1496.6	1461.4	1458.5	1437.3	1400.6	1380.7	1370.8
5°	1534.9	1484.0	1399.1	1404.8	1353.9	1298.8	1269.2	1240.9	1192.8	1163.1	1143.3
7.5°	1444.4	1375.1	1274.8	1267.8	1214.1	1147.6	1105.1	1065.6	1013.4	975.2	951.1
10°	1349.7	1264.8	1147.6	1139.1	1082.5	1010.5	962.4	917.2	863.5	825.3	799.9
12.5°	1262.0	1164.5	1047.3	1026.2	970.8	897.5	845.1	797.1	744.7	712.3	682.7
15°	1178.7	1072.7	948.4	928.5	874.8	801.3	743.5	701.0	651.5	620.5	593.6
17.5°	1095.3	986.5	863.5	840.9	790.0	719.4	668.4	623.2	577.9	548.4	524.3
20°	1023.3	914.5	794.1	771.6	725.0	657.2	610.6	568.0	527.2	498.9	479.0
22.5°	976.5	870.7	761.7	742.0	698.2	637.4	593.6	556.8	521.6	494.7	479.0
25°	973.8	881.9	784.4	773.0	736.3	685.5	654.4	631.8	610.6	589.3	583.6
27.5°	990.7	915.7	833.8	831.1	801.3	767.4	753.3	746.2	734.9	727.8	737.8
30°	980.8	917.2	848.0	848.0	825.3	801.3	794.1	791.4	784.4	785.8	797.1
32.5°	928.5	870.7	804.2	805.5	791.4	764.6	760.4	759.0	750.4	749.1	757.5
35°	833.8	780.1	725.0	726.4	715.2	689.6	684.0	681.2	669.9	664.2	669.9
37.5°	725.0	681.2	628.9	628.9	617.6	597.8	592.2	586.6	579.4	573.8	573.8
40°	613.4	577.9	535.6	534.1	525.7	506.1	500.3	496.0	489.0	479.0	481.9
42.5°	518.6	486.2	452.2	449.5	443.8	426.8	421.2	415.5	408.4	400.0	400.0
45°	431.1	409.9	380.1	378.9	373.2	358.9	354.7	347.7	342.0	333.6	333.6
47.5°	358.9	342.0	318.0	316.6	312.4	299.6	295.5	289.7	284.1	278.5	278.5
50°	301.1	284.1	264.3	262.8	260.0	250.2	244.5	240.3	236.0	231.7	229.0
52.5°	247.3	233.2	217.7	216.2	213.3	203.5	199.3	196.4	192.2	185.2	185.2
55°	199.3	187.9	173.9	172.4	169.5	161.1	156.9	151.3	145.6	138.5	137.1
57.5°	155.5	145.6	134.3	132.8	128.6	121.6	114.4	108.8	103.1	97.4	94.7
60°	117.3	106.0	96.2	93.3	90.5	80.5	74.9	69.2	63.6	59.3	56.6
62.5°	79.1	72.1	60.7	59.3	56.6	51.0	43.8	41.1	38.2	35.4	33.9
65°	49.5	43.8	38.2	36.7	33.9	29.7	26.8	25.4	24.1	22.7	21.2
67.5°	29.7	26.8	22.7	22.7	21.2	19.8	17.0	17.0	15.5	15.5	14.0
70°	18.4	17.0	15.5	14.0	14.0	14.0	12.8	12.8	12.8	12.8	12.8
72.5°	12.8	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
75°	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
77.5°	9.9	9.9	8.4	9.9	9.9	9.9	9.9	8.4	9.9	8.4	8.4
80°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
82.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	7.1	7.1	7.1	7.1
85°	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	5.6
87.5°	7.1	7.1	7.1	7.1	7.1	5.6	5.6	5.6	5.6	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192842

CATALOG NUMBER: LDA6A75950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2	1676.2
2.5°	1373.7	1334.1	1349.7	1327.0	1320.0	1314.2	1305.9	1332.8
5°	1134.8	1092.4	1102.4	1079.7	1070.0	1059.9	1050.1	1071.2
7.5°	937.0	896.1	900.2	880.5	870.7	859.4	849.3	866.3
10°	782.9	744.7	746.2	727.8	717.9	706.6	698.2	710.8
12.5°	665.7	630.3	630.3	616.3	607.7	594.9	588.0	597.8
15°	576.7	545.5	545.5	531.4	524.3	512.9	506.1	515.8
17.5°	508.8	480.5	480.5	470.6	463.5	453.6	448.0	456.5
20°	463.5	439.6	440.9	431.1	425.4	414.0	411.3	418.3
22.5°	467.7	445.2	448.0	440.9	435.2	426.8	423.9	434.0
25°	585.1	568.0	577.9	577.9	580.8	568.0	573.8	589.3
27.5°	751.8	743.5	759.0	753.3	764.6	764.6	770.2	790.0
30°	812.7	805.5	822.4	821.2	832.5	829.6	832.5	850.7
32.5°	768.9	761.7	775.9	774.5	782.9	775.9	777.2	792.9
35°	675.6	668.4	678.3	677.0	682.7	674.1	678.3	686.9
37.5°	576.7	569.5	575.2	573.8	575.2	565.3	571.0	575.2
40°	484.7	476.3	484.7	479.0	480.5	470.6	472.1	477.8
42.5°	405.7	395.6	402.8	402.8	402.8	395.6	397.1	402.8
45°	337.8	330.7	334.9	333.6	334.9	329.3	333.6	339.2
47.5°	279.8	274.1	277.1	275.6	275.6	269.9	271.3	271.3
50°	230.3	224.6	226.1	224.6	220.5	213.3	212.1	213.3
52.5°	182.3	175.2	175.2	172.4	169.5	163.9	163.9	165.4
55°	134.3	128.6	128.6	127.2	124.5	120.1	120.1	123.0
57.5°	90.5	86.1	87.6	86.1	86.1	80.5	83.4	83.4
60°	55.1	52.4	52.4	51.0	48.0	46.7	45.2	48.0
62.5°	32.4	31.0	31.0	29.7	29.7	28.3	28.3	28.3
65°	21.2	19.8	19.8	18.4	18.4	17.0	15.5	17.0
67.5°	14.0	12.8	12.8	12.8	12.8	11.3	11.3	11.3
70°	12.8	11.3	11.3	11.3	11.3	9.9	9.9	9.9
72.5°	11.3	9.9	11.3	9.9	9.9	9.9	9.9	9.9
75°	9.9	9.9	9.9	8.4	8.4	8.4	8.4	8.4
77.5°	8.4	8.4	8.4	8.4	8.4	7.1	7.1	7.1
80°	8.4	7.1	7.1	7.1	7.1	7.1	7.1	7.1
82.5°	7.1	7.1	7.1	7.1	7.1	5.6	5.6	5.6
85°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
87.5°	4.2	4.2	4.2	4.2	4.2	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)