

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192843

Luminaire Tested: **LDA6A75950D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75950D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8173.4 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192843

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1192843

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	66	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	53	49		59	53	49		57	52	48
8	69	57	49	44	67	56	49	44		55	49	44		54	48	44		53	47	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	43	39
10	60	48	41	36	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83974	83974	83974
5°	230491	77377	31576
10°	505090	63331	12035
15°	771531	48201	14120
20°	893884	35855	21935
25°	975105	29494	35391
30°	1088895	26738	36138
35°	1107891	18344	24775
40°	1127362	8702	12538
45°	1129195	3621	5473
50°	954630	1569	1689
55°	307392	1080	258
60°	61048	1239	0
65°	6226	1466	0
70°	673	2052	0
75°	0	2711	0
80°	0	4420	474
85°	0	8806	943

TEST NUMBER: P1192843

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.9	2.5
10°-20°	1075.4	13.2
20°-30°	2059.2	25.2
30°-40°	2426.0	29.7
40°-50°	1905.6	23.3
50°-60°	464.4	5.7
60°-70°	19.9	0.2
70°-80°	7.5	0.1
80°-90°	7.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3342.5	40.9
0°-40°	5768.5	70.6
0°-60°	8138.5	99.6
0°-90°	8173.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8173.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1532	1532	1532	1532	1532	
5°	4188	3031	1406	736	574	554
15°	13594	6982	849	243	249	3795
25°	16121	8490	488	510	585	7514
35°	16555	5367	274	353	370	10381
45°	14565	1659	47	65	71	10943
55°	3216	61	11	7	3	3828
65°	48	7	11	7	0	127
75°	0	7	13	8	0	1
85°	0	8	14	8	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1192843

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8
2.5°	2625.7	2620.0	2581.7	2617.1	2509.7	2505.5	2457.4	2436.2	2374.0	2314.7	2229.9
5°	4188.5	4096.7	4021.7	4024.6	3818.3	3780.1	3672.7	3563.9	3397.1	3241.8	3031.2
7.5°	6384.5	6275.7	6117.4	6051.0	5656.7	5540.8	5319.1	5029.2	4666.1	4304.4	3914.5
10°	9073.6	9090.5	8885.7	8696.4	8100.0	7865.5	7506.5	6935.6	6247.4	5567.7	4876.7
12.5°	11779.8	11768.4	11524.0	11237.2	10502.3	10171.6	9694.0	8981.8	8070.3	7016.2	5935.2
15°	13594.3	13674.8	13571.6	13342.8	12715.1	12336.5	11798.2	10831.5	9720.9	8440.5	6982.2
17.5°	14733.2	14809.5	14772.8	14593.4	14039.4	13635.1	13185.8	12394.5	11110.0	9500.4	7807.5
20°	15322.4	15442.5	15425.7	15230.6	14812.4	14477.5	13981.4	13248.0	12136.0	10236.6	8341.6
22.5°	15715.3	15807.2	15832.6	15612.2	15179.7	14861.8	14498.6	13755.4	12709.5	10686.1	8553.7
25°	16120.8	16283.4	16123.7	15852.4	15455.2	15150.1	14762.9	14050.6	12983.8	10869.7	8490.0
27.5°	16618.3	16696.1	16334.3	16087.0	15646.2	15315.5	14904.1	14221.7	13031.8	10722.7	8126.9
30°	17201.9	16879.8	16626.9	16136.5	15636.1	15314.0	14895.7	14114.4	12778.9	10235.3	7423.1
32.5°	17105.9	16810.5	16523.6	16005.0	15510.4	15191.1	14724.7	13756.7	12181.0	9419.8	6452.3
35°	16554.7	16618.3	16308.8	15879.2	15319.7	14990.5	14481.7	13248.0	11166.6	8295.0	5367.0
37.5°	16089.8	16229.7	16027.5	15630.5	15062.4	14617.3	13930.6	12431.2	9842.5	6867.8	4338.4
40°	15753.5	15798.7	15690.0	15244.7	14562.2	13919.3	13125.0	10964.4	8234.3	5391.2	3424.1
42.5°	15232.0	15352.2	15160.0	14673.9	13639.5	12911.7	11761.5	9270.1	6395.7	4117.9	2577.5
45°	14565.1	14679.5	14442.1	13633.9	12195.2	11128.2	9725.0	7228.1	4731.1	3035.3	1659.0
47.5°	13476.9	13547.6	13088.4	11970.6	9879.1	8874.3	7435.9	5039.1	3048.1	1697.2	806.9
50°	11193.4	11159.4	10212.7	8837.6	6607.7	5553.5	4425.9	2731.6	1369.3	804.0	504.4
52.5°	7214.1	7136.3	6199.3	4948.7	3346.3	2553.6	1919.1	1178.5	713.5	449.3	199.3
55°	3216.2	3186.7	2608.7	2026.3	1369.3	1178.5	900.2	577.9	380.1	156.9	60.7
57.5°	1192.8	1165.7	1027.4	862.1	661.3	549.6	436.7	277.1	97.4	52.4	32.4
60°	556.8	555.4	488.9	402.8	279.8	212.1	123.0	65.0	41.1	28.3	18.4
62.5°	178.2	173.8	121.6	89.0	63.5	55.1	43.8	32.4	21.2	15.5	11.3
65°	48.0	48.0	43.8	36.7	29.7	25.4	21.2	15.5	9.9	8.4	7.1
67.5°	18.4	18.4	17.0	15.5	11.3	9.9	8.4	7.1	5.6	7.1	7.1
70°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.6	5.6	7.1
72.5°	0.0	0.0	1.5	1.5	2.7	2.7	4.2	4.2	5.6	7.1	7.1
75°	0.0	0.0	1.5	1.5	2.7	2.7	4.2	4.2	5.6	7.1	7.1
77.5°	0.0	0.0	1.5	1.5	2.7	2.7	4.2	4.2	5.6	7.1	7.1
80°	0.0	0.0	1.5	1.5	2.7	2.7	4.2	4.2	5.6	7.1	7.1
82.5°	0.0	0.0	1.5	2.7	2.7	2.7	4.2	5.6	5.6	7.1	8.4
85°	0.0	0.0	1.5	2.7	2.7	4.2	4.2	5.6	5.6	7.1	8.4
87.5°	0.0	0.0	1.5	2.7	2.7	4.2	4.2	5.6	5.6	7.1	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192843

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8
2.5°	2167.8	2074.5	1945.8	1870.9	1852.7	1813.0	1743.9	1640.6	1555.9	1474.0	1425.8
5°	2853.0	2632.7	2385.3	2211.6	2140.8	2046.3	1878.0	1704.2	1544.6	1406.1	1297.3
7.5°	3579.4	3216.2	2816.3	2494.1	2378.2	2228.5	1954.3	1695.7	1476.7	1284.5	1138.9
10°	4301.4	3716.5	3173.9	2707.6	2518.2	2314.7	1953.0	1617.9	1360.8	1137.7	976.5
12.5°	5023.6	4182.9	3436.7	2836.1	2590.2	2333.1	1895.0	1499.4	1213.9	986.3	832.3
15°	5690.6	4554.4	3614.7	2879.9	2583.2	2279.3	1777.7	1355.2	1059.9	849.3	706.6
17.5°	6188.1	4749.5	3655.8	2813.4	2471.5	2135.1	1598.3	1185.6	912.8	727.8	582.2
20°	6432.6	4780.6	3558.2	2624.2	2279.3	1930.3	1401.9	1023.0	787.1	614.6	491.8
22.5°	6432.6	4633.6	3346.3	2386.8	2039.1	1694.4	1212.4	888.9	688.2	535.6	432.5
25°	6188.1	4341.1	3062.2	2112.7	1774.9	1461.2	1048.6	788.5	611.9	487.6	401.3
27.5°	5713.2	3937.0	2697.6	1807.4	1514.9	1253.5	918.5	696.7	553.9	439.4	440.9
30°	5060.4	3441.0	2279.3	1485.1	1247.9	1030.1	773.0	583.6	443.7	422.4	435.2
32.5°	4305.8	2847.4	1806.0	1151.7	966.7	811.2	587.8	412.6	353.3	356.1	370.2
35°	3531.3	2241.2	1359.4	853.5	719.2	587.8	385.7	271.3	268.4	274.1	283.9
37.5°	2788.1	1677.4	983.6	624.6	483.3	361.7	207.7	186.5	186.5	192.2	197.8
40°	2088.6	1189.9	676.8	370.2	234.5	165.4	131.4	121.6	120.1	121.6	128.6
42.5°	1434.4	753.2	402.8	148.4	112.9	96.2	83.4	76.3	74.9	76.3	80.5
45°	805.5	463.5	156.9	79.1	67.9	60.7	52.4	48.0	46.7	46.7	49.5
47.5°	504.4	183.8	70.6	49.5	42.3	39.6	33.9	31.0	29.7	29.7	31.0
50°	193.6	72.1	43.8	32.4	28.3	25.4	22.7	19.8	18.4	18.4	19.8
52.5°	66.5	42.3	28.3	21.2	18.4	17.0	14.0	12.8	12.8	12.8	12.8
55°	36.7	25.4	17.0	12.8	11.3	11.3	11.3	11.3	11.3	11.3	11.3
57.5°	22.7	15.5	11.3	9.9	9.9	9.9	9.9	9.9	9.9	11.3	11.3
60°	12.8	9.9	8.4	8.4	8.4	8.4	9.9	9.9	9.9	11.3	11.3
62.5°	8.4	8.4	8.4	8.4	8.4	8.4	9.9	9.9	11.3	11.3	11.3
65°	7.1	7.1	7.1	8.4	8.4	8.4	9.9	9.9	11.3	11.3	11.3
67.5°	7.1	7.1	8.4	8.4	8.4	9.9	9.9	11.3	11.3	11.3	11.3
70°	7.1	8.4	8.4	9.9	9.9	9.9	11.3	11.3	11.3	12.8	12.8
72.5°	7.1	8.4	8.4	9.9	9.9	9.9	11.3	11.3	12.8	12.8	12.8
75°	8.4	8.4	8.4	9.9	9.9	9.9	11.3	12.8	12.8	12.8	12.8
77.5°	8.4	8.4	9.9	9.9	9.9	11.3	11.3	12.8	12.8	12.8	12.8
80°	8.4	8.4	9.9	9.9	11.3	11.3	12.8	12.8	12.8	14.0	14.0
82.5°	8.4	8.4	9.9	11.3	11.3	11.3	12.8	12.8	14.0	14.0	14.0
85°	8.4	9.9	9.9	11.3	11.3	11.3	12.8	12.8	14.0	14.0	14.0
87.5°	8.4	9.9	9.9	11.3	11.3	11.3	12.8	12.8	14.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192843

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8
2.5°	1362.3	1303.0	1243.5	1199.7	1178.5	1157.3	1110.6	1049.9	1024.5	987.8	966.7
5°	1187.1	1086.7	1007.6	955.3	924.1	883.3	829.4	770.1	736.2	698.0	672.7
7.5°	1006.1	888.9	812.7	764.5	733.4	682.6	614.6	544.0	503.2	460.6	431.1
10°	847.8	736.2	650.0	594.9	555.4	496.0	428.2	378.7	343.4	306.6	277.1
12.5°	708.0	587.8	496.0	449.3	422.4	366.1	309.5	254.4	233.2	226.1	226.1
15°	573.8	465.0	387.2	347.7	319.4	258.5	247.3	244.5	243.0	241.6	244.5
17.5°	467.7	376.0	294.0	274.1	271.3	269.9	271.3	271.3	272.8	277.1	283.9
20°	392.9	308.0	302.4	303.9	303.9	309.5	316.6	322.3	327.9	334.9	347.7
22.5°	349.1	347.7	357.6	358.9	366.1	374.5	387.2	395.6	409.9	416.8	435.2
25°	402.8	412.6	431.1	436.7	448.0	462.1	481.9	493.1	510.1	518.6	539.8
27.5°	456.5	472.0	494.5	501.7	511.5	534.1	548.2	558.3	566.6	572.3	585.1
30°	452.2	466.2	488.9	490.4	504.4	520.1	528.5	537.1	542.7	541.2	548.2
32.5°	383.0	395.6	416.8	416.8	432.5	445.1	449.3	456.5	456.5	456.5	459.4
35°	294.0	302.4	316.6	320.8	333.4	342.0	344.8	353.3	353.3	350.4	350.4
37.5°	203.5	214.8	224.6	227.6	236.0	241.6	248.8	250.2	247.3	248.8	248.8
40°	132.8	140.0	147.0	148.4	155.5	159.6	166.8	166.8	168.1	166.8	169.5
42.5°	82.0	87.6	91.8	94.7	97.4	100.4	104.5	106.0	107.4	106.0	108.8
45°	51.0	53.7	56.6	57.8	59.3	60.7	65.0	65.0	65.0	65.0	66.5
47.5°	31.0	32.4	33.9	33.9	35.4	36.7	38.2	38.2	38.2	38.2	39.6
50°	18.4	19.8	19.8	19.8	21.2	21.2	22.7	22.7	22.7	21.2	22.7
52.5°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8	12.8	11.3	12.8
55°	11.3	11.3	9.9	9.9	9.9	9.9	9.9	8.4	7.1	7.1	5.6
57.5°	9.9	9.9	9.9	9.9	9.9	8.4	8.4	7.1	7.1	5.6	4.2
60°	9.9	9.9	9.9	9.9	9.9	8.4	8.4	7.1	5.6	5.6	4.2
62.5°	11.3	9.9	9.9	9.9	9.9	8.4	8.4	7.1	5.6	5.6	4.2
65°	11.3	11.3	9.9	9.9	9.9	8.4	8.4	7.1	7.1	5.6	4.2
67.5°	11.3	11.3	11.3	9.9	11.3	9.9	8.4	8.4	7.1	5.6	5.6
70°	12.8	11.3	11.3	11.3	11.3	9.9	9.9	8.4	7.1	5.6	5.6
72.5°	12.8	12.8	11.3	11.3	11.3	9.9	9.9	8.4	7.1	7.1	5.6
75°	12.8	12.8	11.3	11.3	11.3	9.9	9.9	8.4	8.4	7.1	5.6
77.5°	12.8	12.8	12.8	11.3	11.3	11.3	9.9	9.9	8.4	7.1	5.6
80°	12.8	12.8	12.8	12.8	12.8	11.3	11.3	9.9	8.4	7.1	5.6
82.5°	14.0	12.8	12.8	12.8	12.8	11.3	11.3	9.9	8.4	7.1	7.1
85°	14.0	14.0	12.8	12.8	12.8	11.3	11.3	9.9	8.4	8.4	7.1
87.5°	14.0	12.8	12.8	12.8	12.8	11.3	11.3	9.9	8.4	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192843

CATALOG NUMBER: LDA6A75950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8	1531.8
2.5°	945.3	934.0	934.0	914.3	911.6	895.9	908.6	900.2
5°	644.4	626.0	620.3	600.6	593.4	575.2	580.8	573.8
7.5°	405.5	387.2	381.6	367.3	358.9	344.8	346.2	342.0
10°	247.3	230.3	226.1	221.9	217.7	216.2	217.7	216.2
12.5°	224.6	223.2	220.5	221.9	219.0	220.5	221.9	220.5
15°	244.5	247.3	244.5	245.9	244.5	247.3	248.8	248.8
17.5°	286.8	292.6	289.6	294.0	292.6	299.6	299.6	299.6
20°	351.8	361.7	358.9	364.6	364.6	373.0	373.0	376.0
22.5°	442.3	455.0	453.6	466.2	463.5	473.4	473.4	476.3
25°	551.1	563.9	565.1	573.8	572.3	582.2	582.2	585.1
27.5°	596.3	603.3	602.1	606.2	607.7	613.4	617.6	614.6
30°	559.5	565.1	563.9	566.6	566.6	570.9	575.2	570.9
32.5°	470.6	474.9	474.9	480.5	476.3	477.6	484.7	480.5
35°	360.4	363.2	360.4	363.2	364.6	364.6	371.7	370.2
37.5°	257.1	258.5	258.5	262.8	258.5	258.5	265.7	267.2
40°	172.4	173.8	172.4	178.2	175.2	175.2	179.4	175.2
42.5°	110.2	111.7	110.2	114.4	111.7	114.4	115.9	117.3
45°	67.9	67.9	66.5	69.2	67.9	69.2	70.6	70.6
47.5°	39.6	39.6	38.2	41.1	39.6	39.6	39.6	41.1
50°	21.2	21.2	21.2	22.7	21.2	21.2	21.2	19.8
52.5°	11.3	11.3	9.9	11.3	9.9	9.9	9.9	9.9
55°	5.6	4.2	4.2	4.2	2.7	2.7	2.7	2.7
57.5°	4.2	2.7	2.7	1.5	1.5	1.5	0.0	0.0
60°	2.7	2.7	1.5	1.5	0.0	0.0	0.0	0.0
62.5°	2.7	2.7	1.5	1.5	0.0	0.0	0.0	0.0
65°	2.7	2.7	1.5	1.5	0.0	0.0	0.0	0.0
67.5°	4.2	2.7	2.7	1.5	1.5	0.0	0.0	0.0
70°	4.2	2.7	2.7	1.5	1.5	0.0	0.0	0.0
72.5°	4.2	2.7	2.7	2.7	1.5	1.5	0.0	0.0
75°	4.2	4.2	2.7	2.7	1.5	1.5	0.0	0.0
77.5°	5.6	4.2	2.7	2.7	1.5	1.5	0.0	0.0
80°	5.6	4.2	2.7	2.7	2.7	1.5	1.5	1.5
82.5°	5.6	4.2	4.2	2.7	2.7	1.5	1.5	1.5
85°	5.6	4.2	4.2	2.7	2.7	1.5	1.5	1.5
87.5°	5.6	4.2	4.2	2.7	2.7	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)