

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204965

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1400.4 lumens
Efficiency: N/A
Efficacy: 141.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204965

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P204965

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	101	98		100	98	95		97	94	92		93	91	90
2	102	95	89	84		99	93	88	83		90	85	81		86	83	79		83	80	78
3	94	85	77	72		92	83	76	71		80	74	70		77	73	69		75	71	67
4	87	76	68	62		84	74	67	61		72	66	61		70	64	60		68	63	59
5	80	68	60	54		78	67	59	54		65	58	53		63	57	53		61	56	52
6	74	62	54	48		72	61	53	47		59	52	47		58	51	47		56	51	46
7	69	56	48	42		67	56	48	42		54	47	42		53	46	42		51	46	41
8	64	52	44	38		63	51	43	38		50	43	38		48	42	38		47	42	37
9	60	48	40	35		59	47	40	34		46	39	34		45	39	34		44	38	34
10	57	44	36	31		55	43	36	31		43	36	31		42	35	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204965

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	4.3
10°-20°	170.1	12.1
20°-30°	248.4	17.7
30°-40°	284.1	20.3
40°-50°	273.0	19.5
50°-60°	210.8	15.1
60°-70°	117.7	8.4
70°-80°	34.3	2.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.0	34.2
0°-40°	763.1	54.5
0°-60°	1247.0	89.0
0°-90°	1400.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1400.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	643	
5°	638	61
15°	603	170
25°	540	248
35°	455	284
45°	356	273
55°	236	211
65°	118	118
75°	30	34
85°	1	1
90°	0	



TEST NUMBER: P204965

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	643.1
2.5°	643.1
5°	637.6
7.5°	634.9
10°	625.9
12.5°	615.0
15°	603.2
17.5°	591.5
20°	574.2
22.5°	560.6
25°	539.9
27.5°	519.0
30°	498.1
32.5°	477.4
35°	454.6
37.5°	432.0
40°	405.8
42.5°	382.2
45°	356.0
47.5°	326.1
50°	298.0
52.5°	267.2
55°	236.4
57.5°	204.8
60°	174.8
62.5°	144.9
65°	117.8
67.5°	92.4
70°	68.9
72.5°	48.0
75°	29.9
77.5°	15.4
80°	5.4
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)