

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204862

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1263.6 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204862

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204862

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39		
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35		
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204862

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	4.0
10°-20°	143.8	11.4
20°-30°	216.1	17.1
30°-40°	256.4	20.3
40°-50°	253.8	20.1
50°-60°	199.4	15.8
60°-70°	111.8	8.8
70°-80°	31.4	2.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	410.4	32.5
0°-40°	666.8	52.8
0°-60°	1120.0	88.6
0°-90°	1263.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1263.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	534	
5°	533	50
15°	510	144
25°	469	216
35°	411	256
45°	331	254
55°	225	199
65°	111	112
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P204862

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	533.5
2.5°	531.8
5°	532.6
7.5°	528.1
10°	522.8
12.5°	516.4
15°	510.0
17.5°	501.9
20°	491.0
22.5°	480.1
25°	469.2
27.5°	457.5
30°	442.1
32.5°	426.6
35°	411.2
37.5°	393.1
40°	372.4
42.5°	352.4
45°	330.6
47.5°	306.1
50°	280.9
52.5°	251.9
55°	224.6
57.5°	193.9
60°	164.9
62.5°	138.6
65°	111.4
67.5°	87.9
70°	65.2
72.5°	44.4
75°	27.1
77.5°	13.6
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)