

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203212

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 995.2 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203212

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203212

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	93	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	88	84	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		62
9	72	62	56	51	71	61	55	51	60	55	51		60	55	51		59
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203212

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	9.0
10°-20°	233.0	23.4
20°-30°	301.9	30.3
30°-40°	224.1	22.5
40°-50°	94.6	9.5
50°-60°	33.6	3.4
60°-70°	13.0	1.3
70°-80°	4.5	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.9	62.8
0°-40°	849.0	85.3
0°-60°	977.2	98.2
0°-90°	995.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	995.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	985	
5°	964	90
15°	831	233
25°	669	302
35°	355	224
45°	116	95
55°	36	34
65°	13	13
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P203212

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	984.9
2.5°	982.1
5°	963.6
7.5°	936.6
10°	903.9
12.5°	868.4
15°	831.4
17.5°	790.2
20°	753.2
22.5°	714.9
25°	669.4
27.5°	606.9
30°	533.0
32.5°	446.2
35°	355.2
37.5°	278.5
40°	211.8
42.5°	157.8
45°	116.5
47.5°	85.2
50°	62.5
52.5°	46.9
55°	35.5
57.5°	27.0
60°	21.4
62.5°	15.6
65°	12.8
67.5°	10.0
70°	7.1
72.5°	5.6
75°	4.2
77.5°	2.9
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)