

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203933

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBNB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 594.4 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.83
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203933

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P203933

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	107	111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	97	106	102	99	96		99	96	93			96	94	91			93
3	103	97	92	88	101	96	91	88		93	89	86			91	88	85			88
4	98	91	86	82	96	90	85	81		88	84	80			86	82	79			84
5	93	85	80	76	92	85	79	75		83	78	75			81	77	74			80
6	89	80	75	71	88	80	74	70		78	73	70			77	73	69			75
7	85	76	70	66	83	75	70	66		74	69	65			73	68	65			72
8	81	72	66	62	80	71	66	62		70	65	61			69	64	61			68
9	77	68	62	58	76	67	62	58		66	61	58			65	61	58			65
10	74	64	59	55	73	64	58	55		63	58	55			62	58	55			62

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203933

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.9	12.8
10°-20°	165.4	27.8
20°-30°	194.4	32.7
30°-40°	133.9	22.5
40°-50°	24.8	4.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.7	73.3
0°-40°	569.6	95.8
0°-60°	594.4	100.0
0°-90°	594.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	594.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	875	
5°	833	76
15°	588	165
25°	425	194
35°	215	134
45°	25	25
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203933

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	874.9
2.5°	867.1
5°	832.9
7.5°	784.6
10°	717.8
12.5°	650.8
15°	588.5
17.5°	535.5
20°	493.5
22.5°	457.8
25°	425.0
27.5°	392.4
30°	348.8
32.5°	286.5
35°	214.9
37.5°	149.5
40°	95.0
42.5°	52.9
45°	24.9
47.5°	7.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)