

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205269

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBNI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1082.5 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205269

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205269

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	94	91	103	97	93	90	95	91	89		93	90	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	87	83	79	86	82	78		84	81	78		83
6	92	84	79	75	90	83	78	75	82	77	74		80	76	74		79
7	88	80	74	71	87	79	74	71	78	73	70		77	73	70		76
8	84	76	71	67	83	75	70	67	74	70	67		73	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	61		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205269

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.9	18.9
10°-20°	367.8	34.0
20°-30°	297.4	27.5
30°-40°	171.3	15.8
40°-50°	36.2	3.3
50°-60°	3.1	0.3
60°-70°	1.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	870.2	80.4
0°-40°	1041.5	96.2
0°-60°	1080.8	99.8
0°-90°	1082.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1082.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2465	
5°	2296	205
15°	1336	368
25°	642	297
35°	272	171
45°	39	36
55°	3	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P205269

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2464.9
2.5°	2435.2
5°	2296.2
7.5°	2096.5
10°	1851.4
12.5°	1600.0
15°	1336.2
17.5°	1081.8
20°	896.0
22.5°	754.0
25°	641.6
27.5°	546.4
30°	460.5
32.5°	365.2
35°	271.6
37.5°	188.9
40°	123.4
42.5°	74.9
45°	39.0
47.5°	15.6
50°	4.6
52.5°	4.6
55°	3.1
57.5°	3.1
60°	1.5
62.5°	1.5
65°	1.5
67.5°	1.5
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)