

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204448

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1246.4 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204448

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSB1

Luminous Intensity Polar Plot






TEST NUMBER: P204448

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204448

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	4.2
10°-20°	147.2	11.8
20°-30°	219.0	17.6
30°-40°	254.9	20.4
40°-50°	248.4	19.9
50°-60°	191.1	15.3
60°-70°	105.6	8.5
70°-80°	28.0	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.2	33.6
0°-40°	673.1	54.0
0°-60°	1112.6	89.3
0°-90°	1246.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1246.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	550	
5°	547	52
15°	521	147
25°	476	219
35°	409	255
45°	322	248
55°	213	191
65°	106	106
75°	24	28
85°	0	0
90°	0	



TEST NUMBER: P204448

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	549.9
2.5°	549.9
5°	546.6
7.5°	541.9
10°	538.8
12.5°	529.2
15°	521.4
17.5°	513.5
20°	502.4
22.5°	491.4
25°	475.6
27.5°	459.8
30°	444.0
32.5°	426.6
35°	409.2
37.5°	387.1
40°	368.1
42.5°	347.6
45°	322.2
47.5°	298.6
50°	271.8
52.5°	243.4
55°	213.2
57.5°	184.9
60°	158.0
62.5°	131.1
65°	105.9
67.5°	82.1
70°	60.0
72.5°	41.1
75°	23.8
77.5°	11.0
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)