

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205187

Luminaire Tested: **LE_6B15D010 EC6B10209050 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209050 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1613.5 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205187

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P205187

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	97	91	86	81	88	84	80		86	82	79		83
4	93	85	78	73	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	42	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205187

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	6.0
10°-20°	292.3	18.1
20°-30°	440.5	27.3
30°-40°	450.9	27.9
40°-50°	262.7	16.3
50°-60°	60.4	3.7
60°-70°	7.4	0.5
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	830.1	51.4
0°-40°	1281.0	79.4
0°-60°	1604.1	99.4
0°-90°	1613.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1613.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1008	
5°	1013	97
15°	1035	292
25°	966	441
35°	732	451
45°	338	263
55°	58	60
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205187

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1007.9
2.5°	1006.1
5°	1013.4
7.5°	1020.8
10°	1029.9
12.5°	1031.8
15°	1035.4
17.5°	1031.8
20°	1022.5
22.5°	993.2
25°	965.9
27.5°	921.9
30°	865.2
32.5°	806.8
35°	731.8
37.5°	647.5
40°	554.2
42.5°	450.0
45°	338.4
47.5°	236.0
50°	155.5
52.5°	98.8
55°	58.5
57.5°	31.1
60°	16.5
62.5°	9.1
65°	5.5
67.5°	5.5
70°	3.6
72.5°	1.9
75°	1.9
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)