

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204139

Luminaire Tested: **LE_6B10D010 EC6B10208035 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208035 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1418.0 lumens
Efficiency: N/A
Efficacy: 143.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204139

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204139

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204139

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.5	4.9
10°-20°	188.8	13.3
20°-30°	262.2	18.5
30°-40°	286.1	20.2
40°-50°	266.9	18.8
50°-60°	202.6	14.3
60°-70°	110.9	7.8
70°-80°	30.5	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.5	36.7
0°-40°	806.6	56.9
0°-60°	1276.1	90.0
0°-90°	1418.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1418.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	742	
5°	735	69
15°	673	189
25°	570	262
35°	458	286
45°	347	267
55°	226	203
65°	111	111
75°	26	31
85°	0	0
90°	0	



TEST NUMBER: P204139

CATALOG NUMBER: LE_6B10D010 EC6B10208035 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	741.6
2.5°	741.6
5°	735.4
7.5°	726.0
10°	712.0
12.5°	693.2
15°	672.9
17.5°	647.9
20°	624.5
22.5°	596.4
25°	569.9
27.5°	543.4
30°	513.6
32.5°	485.5
35°	457.5
37.5°	429.4
40°	402.8
42.5°	374.8
45°	346.6
47.5°	318.5
50°	287.2
52.5°	257.6
55°	226.4
57.5°	196.8
60°	167.0
62.5°	137.4
65°	110.9
67.5°	85.9
70°	64.0
72.5°	43.8
75°	26.5
77.5°	12.5
80°	3.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)