

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204488

Luminaire Tested: **LE_6B30D010 EC6B30508050 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508050 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3500.4 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204488

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204488

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	105	101	98		100	98	95		97	94	93		93	91	90
2	102	95	89	84	100	93	88	83		90	85	81		86	83	79		84	80	78
3	94	84	77	72	91	83	76	71		80	74	70		77	73	69		75	71	67
4	86	76	68	62	84	74	67	61		72	65	60		70	64	60		68	63	59
5	80	68	60	54	78	67	59	53		65	58	53		63	57	52		61	56	52
6	74	62	53	47	72	61	53	47		59	52	47		57	51	46		56	50	46
7	69	56	48	42	67	55	48	42		54	47	42		52	46	41		51	45	41
8	64	51	43	38	63	51	43	38		49	42	37		48	42	37		47	41	37
9	60	47	39	34	59	47	39	34		46	39	34		45	38	34		44	38	34
10	56	44	36	31	55	43	36	31		42	36	31		41	35	31		40	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204488

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.7	4.2
10°-20°	413.5	11.8
20°-30°	615.1	17.6
30°-40°	715.8	20.4
40°-50°	697.7	19.9
50°-60°	536.6	15.3
60°-70°	296.6	8.5
70°-80°	78.5	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1174.4	33.6
0°-40°	1890.2	54.0
0°-60°	3124.6	89.3
0°-90°	3500.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3500.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1544	
5°	1535	146
15°	1464	414
25°	1336	615
35°	1149	716
45°	905	698
55°	599	537
65°	297	297
75°	66	79
85°	0	1
90°	0	



TEST NUMBER: P204488

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1544.2
2.5°	1544.2
5°	1535.4
7.5°	1522.0
10°	1513.1
12.5°	1486.5
15°	1464.4
17.5°	1442.1
20°	1411.1
22.5°	1380.0
25°	1335.6
27.5°	1291.2
30°	1246.9
32.5°	1198.1
35°	1149.2
37.5°	1087.1
40°	1033.9
42.5°	976.2
45°	905.2
47.5°	838.6
50°	763.2
52.5°	683.4
55°	599.0
57.5°	519.1
60°	443.8
62.5°	368.2
65°	297.2
67.5°	230.8
70°	168.6
72.5°	115.4
75°	66.5
77.5°	31.0
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)