

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204918

Luminaire Tested: **LE_6B40D010 EC6B30509030 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509030 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4138.9 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204918

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204918

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39		
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35		
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204918

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.3	4.0
10°-20°	470.9	11.4
20°-30°	707.9	17.1
30°-40°	840.0	20.3
40°-50°	831.3	20.1
50°-60°	653.0	15.8
60°-70°	366.1	8.8
70°-80°	102.8	2.5
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1344.2	32.5
0°-40°	2184.2	52.8
0°-60°	3668.4	88.6
0°-90°	4138.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4138.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1748	
5°	1745	165
15°	1670	471
25°	1537	708
35°	1347	840
45°	1083	831
55°	736	653
65°	365	366
75°	89	103
85°	0	2
90°	0	



TEST NUMBER: P204918

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1747.6
2.5°	1741.8
5°	1744.8
7.5°	1729.9
10°	1712.0
12.5°	1691.2
15°	1670.5
17.5°	1643.8
20°	1608.2
22.5°	1572.6
25°	1537.0
27.5°	1498.4
30°	1448.0
32.5°	1397.5
35°	1347.1
37.5°	1287.8
40°	1219.5
42.5°	1154.2
45°	1083.0
47.5°	1002.9
50°	919.9
52.5°	824.9
55°	735.9
57.5°	635.0
60°	540.0
62.5°	454.0
65°	365.0
67.5°	287.9
70°	213.6
72.5°	145.4
75°	89.0
77.5°	44.5
80°	11.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)