

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204765

Luminaire Tested: **LE_6B10D010 EC6B10209035 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209035 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1265.0 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204765

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204765

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87		
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74		
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63		
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55		
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48		
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42		
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37		
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33		
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30		
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204765

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	3.9
10°-20°	139.4	11.0
20°-30°	209.6	16.6
30°-40°	248.5	19.6
40°-50°	247.3	19.5
50°-60°	199.3	15.8
60°-70°	120.5	9.5
70°-80°	44.8	3.5
80°-90°	6.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.9	31.5
0°-40°	646.4	51.1
0°-60°	1093.0	86.4
0°-90°	1265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1265.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	514	49
15°	494	139
25°	455	210
35°	398	248
45°	322	247
55°	222	199
65°	121	121
75°	41	45
85°	5	7
90°	0	



TEST NUMBER: P204765

CATALOG NUMBER: LE_6B10D010 EC6B10209035 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	516.6
2.5°	516.6
5°	514.4
7.5°	512.9
10°	508.2
12.5°	500.5
15°	493.6
17.5°	486.0
20°	476.8
22.5°	467.6
25°	455.4
27.5°	442.2
30°	427.8
32.5°	414.0
35°	397.9
37.5°	381.0
40°	361.0
42.5°	341.9
45°	322.0
47.5°	299.8
50°	275.2
52.5°	249.9
55°	222.2
57.5°	197.8
60°	170.1
62.5°	145.6
65°	121.1
67.5°	98.1
70°	76.6
72.5°	57.5
75°	40.6
77.5°	26.1
80°	15.4
82.5°	9.2
85°	5.4
87.5°	2.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)