

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203277

Luminaire Tested: **LE_6B50D010R EC6B30508040 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B50D010R EC6B30508040 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5058.8 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203277

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203277

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	93	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	84	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		62
9	72	62	56	51	71	61	55	51	60	55	51		60	55	51		59
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203277

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	457.7	9.0
10°-20°	1184.2	23.4
20°-30°	1534.4	30.3
30°-40°	1139.1	22.5
40°-50°	480.9	9.5
50°-60°	170.8	3.4
60°-70°	65.9	1.3
70°-80°	22.8	0.5
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3176.3	62.8
0°-40°	4315.4	85.3
0°-60°	4967.1	98.2
0°-90°	5058.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5058.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5006	
5°	4898	458
15°	4226	1184
25°	3402	1534
35°	1806	1139
45°	592	481
55°	181	171
65°	65	66
75°	22	23
85°	0	3
90°	0	



TEST NUMBER: P203277

CATALOG NUMBER: LE_6B50D010R EC6B30508040 6LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	5006.2
2.5°	4991.8
5°	4897.9
7.5°	4760.6
10°	4594.5
12.5°	4413.9
15°	4226.0
17.5°	4016.5
20°	3828.8
22.5°	3633.6
25°	3402.5
27.5°	3084.6
30°	2709.0
32.5°	2268.4
35°	1806.0
37.5°	1415.9
40°	1076.4
42.5°	801.9
45°	592.4
47.5°	433.5
50°	317.9
52.5°	238.4
55°	180.6
57.5°	137.2
60°	108.4
62.5°	79.5
65°	65.0
67.5°	50.6
70°	36.1
72.5°	28.9
75°	21.6
77.5°	14.5
80°	7.2
82.5°	7.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)