

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202610

Luminaire Tested: **LE_6B15D010 EC6B10209027 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209027 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1181.1 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202610

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202610

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106		111	108	106	104		104	103	101			101	99	98			97
2	108	103	99	95		105	101	97	94		98	95	92			95	92	90			92
3	102	95	90	86		100	94	89	86		91	88	84			89	86	83			87
4	97	89	83	79		95	88	83	79		86	81	78			84	80	77			82
5	92	83	77	73		90	82	77	73		80	76	72			79	75	71			77
6	87	78	72	67		85	77	71	67		76	71	67			74	70	66			73
7	83	73	67	63		81	72	67	63		71	66	62			70	65	62			69
8	78	69	63	58		77	68	62	58		67	62	58			66	61	58			65
9	75	65	59	55		73	64	59	55		63	58	54			62	58	54			62
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			58

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202610

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	10.2
10°-20°	309.5	26.2
20°-30°	380.1	32.2
30°-40°	260.7	22.1
40°-50°	83.8	7.1
50°-60°	17.0	1.4
60°-70°	6.7	0.6
70°-80°	2.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	810.2	68.6
0°-40°	1070.8	90.7
0°-60°	1171.6	99.2
0°-90°	1181.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1181.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1314	
5°	1288	121
15°	1107	309
25°	839	380
35°	416	261
45°	99	84
55°	17	17
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P202610

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1313.6
2.5°	1305.5
5°	1288.5
7.5°	1256.5
10°	1213.4
12.5°	1160.2
15°	1107.1
17.5°	1048.0
20°	982.9
22.5°	914.8
25°	838.6
27.5°	754.5
30°	648.2
32.5°	531.0
35°	415.9
37.5°	310.6
40°	223.5
42.5°	152.2
45°	99.2
47.5°	61.1
50°	37.1
52.5°	23.0
55°	17.0
57.5°	13.0
60°	10.0
62.5°	8.0
65°	7.0
67.5°	5.0
70°	4.0
72.5°	3.0
75°	2.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)