

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203640

Luminaire Tested: **LE_6B15D010 EC6B10209027 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209027 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 947.1 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203640

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNH1

Luminous Intensity Polar Plot






TEST NUMBER: P203640

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203640

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.2	11.5
10°-20°	260.3	27.5
20°-30°	298.2	31.5
30°-40°	200.4	21.2
40°-50°	57.3	6.0
50°-60°	14.0	1.5
60°-70°	5.3	0.6
70°-80°	2.1	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	667.8	70.5
0°-40°	868.2	91.7
0°-60°	939.4	99.2
0°-90°	947.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1214	
5°	1180	109
15°	934	260
25°	651	298
35°	320	200
45°	66	57
55°	16	14
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203640

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1214.0
2.5°	1205.4
5°	1179.5
7.5°	1132.9
10°	1075.9
12.5°	1003.2
15°	934.2
17.5°	861.8
20°	789.1
22.5°	720.1
25°	651.0
27.5°	587.1
30°	512.9
32.5°	414.5
35°	319.5
37.5°	233.1
40°	160.6
42.5°	105.4
45°	65.6
47.5°	39.8
50°	24.1
52.5°	19.0
55°	15.5
57.5°	12.1
60°	8.6
62.5°	6.9
65°	5.1
67.5°	3.5
70°	3.5
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)