

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204052

Luminaire Tested: **LE_6B15D010 EC6B10209027 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209027 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1086.8 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204052

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204052

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	108	105	103	109	106	103	101		102	100	98			98	97	95			95
2	105	99	94	90	102	97	92	89		94	90	87			91	87	85			88
3	98	90	84	79	96	89	83	79		86	81	77			84	80	76			81
4	92	83	76	71	90	82	76	71		80	74	70			77	73	69			75
5	87	77	70	64	85	76	69	64		74	68	64			72	67	63			70
6	81	71	64	59	80	70	63	59		68	63	58			67	62	58			66
7	77	66	59	54	75	65	59	54		64	58	54			63	57	53			61
8	72	61	55	50	71	61	54	50		60	54	49			59	53	49			58
9	69	58	51	46	67	57	51	46		56	50	46			55	50	46			54
10	65	54	47	43	64	54	47	43		53	47	43			52	46	43			51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204052

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.8	7.6
10°-20°	219.4	20.2
20°-30°	292.9	26.9
30°-40°	236.3	21.7
40°-50°	113.2	10.4
50°-60°	67.1	6.2
60°-70°	44.7	4.1
70°-80°	23.9	2.2
80°-90°	6.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.0	54.7
0°-40°	831.3	76.5
0°-60°	1011.6	93.1
0°-90°	1086.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1086.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	891	
5°	881	83
15°	781	219
25°	641	293
35°	378	236
45°	140	113
55°	74	67
65°	45	45
75°	22	24
85°	5	7
90°	0	



TEST NUMBER: P204052

CATALOG NUMBER: LE_6B15D010 EC6B10209027 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	891.2
2.5°	891.2
5°	880.9
7.5°	863.6
10°	839.4
12.5°	813.5
15°	780.8
17.5°	749.6
20°	715.1
22.5°	678.8
25°	640.8
27.5°	601.1
30°	544.1
32.5°	464.6
35°	378.2
37.5°	298.8
40°	231.5
42.5°	179.6
45°	139.9
47.5°	110.5
50°	93.2
52.5°	82.9
55°	74.2
57.5°	67.4
60°	58.8
62.5°	51.9
65°	44.9
67.5°	38.0
70°	32.9
72.5°	27.6
75°	22.5
77.5°	17.2
80°	13.9
82.5°	10.4
85°	5.1
87.5°	1.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)