

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203233

Luminaire Tested: **LE_6B15D010 EC6B10209727 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209727 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 956.6 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203233

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMH1

Luminous Intensity Polar Plot






TEST NUMBER: P203233

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	93	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		62
9	72	62	56	51	71	61	55	51	60	55	51		60	55	51		59
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203233

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.6	9.0
10°-20°	223.9	23.4
20°-30°	290.1	30.3
30°-40°	215.4	22.5
40°-50°	90.9	9.5
50°-60°	32.3	3.4
60°-70°	12.4	1.3
70°-80°	4.4	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.6	62.8
0°-40°	816.0	85.3
0°-60°	939.2	98.2
0°-90°	956.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	956.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	947	
5°	926	87
15°	799	224
25°	643	290
35°	342	215
45°	112	91
55°	34	32
65°	12	12
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P203233

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	946.6
2.5°	943.9
5°	926.1
7.5°	900.2
10°	868.8
12.5°	834.6
15°	799.1
17.5°	759.5
20°	724.0
22.5°	687.1
25°	643.4
27.5°	583.2
30°	512.2
32.5°	428.9
35°	341.5
37.5°	267.8
40°	203.5
42.5°	151.6
45°	112.0
47.5°	82.0
50°	60.1
52.5°	45.1
55°	34.1
57.5°	26.0
60°	20.5
62.5°	15.0
65°	12.2
67.5°	9.5
70°	6.9
72.5°	5.5
75°	4.1
77.5°	2.8
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)