

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202615

Luminaire Tested: **LE_6B15D010 EC6B10209727 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209727 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1026.8 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202615

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202615

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	111	108	106		111	108	106	104		104	103	101			101	99	98			93
2	108	103	99	95		105	101	97	94		98	95	92			95	92	90			86
3	102	95	90	86		100	94	89	86		91	88	84			89	86	83			80
4	97	89	83	79		95	88	83	79		86	81	78			84	80	77			74
5	92	83	77	73		90	82	77	73		80	76	72			79	75	71			69
6	87	78	72	67		85	77	71	67		76	71	67			74	70	66			64
7	83	73	67	63		81	72	67	63		71	66	62			70	65	62			60
8	78	69	63	58		77	68	62	58		67	62	58			66	61	58			56
9	75	65	59	55		73	64	59	55		63	58	54			62	58	54			53
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202615

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	10.2
10°-20°	269.0	26.2
20°-30°	330.4	32.2
30°-40°	226.6	22.1
40°-50°	72.8	7.1
50°-60°	14.8	1.4
60°-70°	5.8	0.6
70°-80°	2.2	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.2	68.6
0°-40°	930.8	90.6
0°-60°	1018.4	99.2
0°-90°	1026.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1142	
5°	1120	105
15°	962	269
25°	729	330
35°	361	227
45°	86	73
55°	15	15
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P202615

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1141.8
2.5°	1134.8
5°	1120.0
7.5°	1092.1
10°	1054.6
12.5°	1008.5
15°	962.4
17.5°	911.0
20°	854.4
22.5°	795.1
25°	729.0
27.5°	655.8
30°	563.5
32.5°	461.6
35°	361.4
37.5°	270.0
40°	194.2
42.5°	132.4
45°	86.2
47.5°	53.1
50°	32.2
52.5°	20.0
55°	14.8
57.5°	11.4
60°	8.8
62.5°	7.0
65°	6.1
67.5°	4.4
70°	3.5
72.5°	2.6
75°	1.8
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)