

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203842

Luminaire Tested: **LE_6B15D010 EC6B10208035 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208035 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 944.7 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203842

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203842

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203842

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.0	11.0
10°-20°	256.4	27.1
20°-30°	310.7	32.9
30°-40°	211.7	22.4
40°-50°	50.4	5.3
50°-60°	7.9	0.8
60°-70°	2.8	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	671.0	71.0
0°-40°	882.8	93.4
0°-60°	941.1	99.6
0°-90°	944.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	944.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1148	
5°	1116	104
15°	918	256
25°	679	311
35°	338	212
45°	54	50
55°	9	8
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203842

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1148.5
2.5°	1142.0
5°	1116.1
7.5°	1081.6
10°	1032.1
12.5°	976.1
15°	917.9
17.5°	857.6
20°	797.2
22.5°	736.9
25°	678.8
27.5°	624.9
30°	547.2
32.5°	446.0
35°	338.2
37.5°	241.4
40°	159.5
42.5°	99.1
45°	53.9
47.5°	28.0
50°	15.1
52.5°	10.8
55°	8.6
57.5°	6.5
60°	4.2
62.5°	4.2
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)