

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204151

Luminaire Tested: **LE_6B15D010 EC6B10208035 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208035 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1956.4 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204151

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSH1

Luminous Intensity Polar Plot






TEST NUMBER: P204151

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101	108	105	102	99		101	98	96		97	95	93		93	92	90
2	102	96	90	85	100	94	88	84		90	86	82		87	83	80		84	81	79
3	95	85	78	73	92	84	77	72		81	75	71		78	74	70		76	72	69
4	87	77	69	63	85	75	68	63		73	67	62		71	65	61		69	64	60
5	81	69	61	55	79	68	61	55		66	60	55		64	59	54		63	58	53
6	75	63	55	49	73	62	54	49		60	54	49		59	53	48		57	52	48
7	70	58	50	44	68	57	49	44		55	49	44		54	48	43		53	47	43
8	65	53	45	40	64	52	45	40		51	44	39		50	44	39		49	43	39
9	61	49	41	36	60	48	41	36		47	40	36		46	40	36		45	40	35
10	58	45	38	33	56	45	38	33		44	37	33		43	37	33		42	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204151

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.8	4.9
10°-20°	260.5	13.3
20°-30°	361.8	18.5
30°-40°	394.8	20.2
40°-50°	368.3	18.8
50°-60°	279.5	14.3
60°-70°	153.1	7.8
70°-80°	42.1	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	718.1	36.7
0°-40°	1112.9	56.9
0°-60°	1760.7	90.0
0°-90°	1956.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1956.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1023	
5°	1015	96
15°	928	260
25°	786	362
35°	631	395
45°	478	368
55°	312	280
65°	153	153
75°	37	42
85°	0	1
90°	0	



TEST NUMBER: P204151

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1023.2
2.5°	1023.2
5°	1014.6
7.5°	1001.6
10°	982.2
12.5°	956.4
15°	928.4
17.5°	894.0
20°	861.6
22.5°	822.9
25°	786.2
27.5°	749.6
30°	708.8
32.5°	669.9
35°	631.1
37.5°	592.4
40°	555.8
42.5°	517.0
45°	478.2
47.5°	439.4
50°	396.4
52.5°	355.4
55°	312.4
57.5°	271.4
60°	230.5
62.5°	189.5
65°	153.0
67.5°	118.5
70°	88.4
72.5°	60.4
75°	36.6
77.5°	17.2
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)