

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204254

Luminaire Tested: **LE_6B15D010 EC6B10208035 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208035 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1967.2 lumens
Efficiency: N/A
Efficacy: 137.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204254

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204254

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73		93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64		86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56		79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45		69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41		65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37		61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34		57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204254

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	5.5
10°-20°	280.1	14.2
20°-30°	366.3	18.6
30°-40°	387.9	19.7
40°-50°	361.8	18.4
50°-60°	274.1	13.9
60°-70°	148.4	7.5
70°-80°	39.8	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.6	38.4
0°-40°	1142.5	58.1
0°-60°	1778.4	90.4
0°-90°	1967.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1967.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1173	
5°	1156	108
15°	1001	280
25°	796	366
35°	620	388
45°	471	362
55°	308	274
65°	148	148
75°	34	40
85°	0	1
90°	0	



TEST NUMBER: P204254

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1173.2
2.5°	1168.9
5°	1156.0
7.5°	1128.0
10°	1091.4
12.5°	1048.4
15°	1001.0
17.5°	947.1
20°	899.8
22.5°	846.0
25°	796.5
27.5°	747.0
30°	699.6
32.5°	658.8
35°	620.0
37.5°	581.2
40°	544.6
42.5°	508.0
45°	471.4
47.5°	430.5
50°	389.6
52.5°	348.8
55°	307.9
57.5°	264.8
60°	223.9
62.5°	185.1
65°	148.5
67.5°	114.1
70°	84.0
72.5°	58.1
75°	34.5
77.5°	15.1
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)