

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202812

Luminaire Tested: **LE_6B15D010 EC6B10208035 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208035 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1717.4 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202812

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202812

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	107	104	110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	96	92	104	98	94	91		95	92	89		92	89	87		89	87	85
3	99	92	86	81	97	90	85	81		88	83	79		85	81	78		83	80	77
4	93	84	78	73	91	83	77	72		81	76	71		79	74	71		77	73	70
5	87	77	71	66	85	76	70	65		75	69	65		73	68	64		71	67	63
6	82	71	64	59	80	71	64	59		69	63	59		67	62	58		66	61	58
7	77	66	59	54	75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	54	49	71	61	54	49		59	53	49		58	53	49		57	52	49
9	68	57	50	45	67	56	50	45		55	49	45		54	49	45		53	48	45
10	64	53	46	42	63	53	46	42		52	46	42		51	45	42		50	45	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202812

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.5	6.0
10°-20°	304.9	17.8
20°-30°	459.0	26.7
30°-40°	469.3	27.3
40°-50°	285.0	16.6
50°-60°	80.3	4.7
60°-70°	12.2	0.7
70°-80°	3.9	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	866.4	50.4
0°-40°	1335.8	77.8
0°-60°	1701.0	99.0
0°-90°	1717.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1717.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1067	
5°	1071	103
15°	1080	305
25°	1002	459
35°	761	469
45°	366	285
55°	80	80
65°	11	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P202812

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBWWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1066.8
2.5°	1066.8
5°	1071.0
7.5°	1077.5
10°	1077.5
12.5°	1081.9
15°	1079.6
17.5°	1075.4
20°	1060.2
22.5°	1038.8
25°	1002.1
27.5°	961.1
30°	905.1
32.5°	838.4
35°	760.8
37.5°	674.5
40°	575.4
42.5°	472.0
45°	366.4
47.5°	271.5
50°	191.8
52.5°	129.2
55°	79.8
57.5°	47.4
60°	23.8
62.5°	15.1
65°	10.8
67.5°	8.6
70°	6.5
72.5°	4.2
75°	4.2
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)