

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204466

Luminaire Tested: **LE_6B15D010 EC6B10209035 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209035 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1453.3 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204466

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSB1

Luminous Intensity Polar Plot






TEST NUMBER: P204466

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	105	101	98		100	98	95		97	94	93		93	91	90
2	102	95	89	84	100	93	88	83		90	85	81		86	83	79		84	80	78
3	94	84	77	72	91	83	76	71		80	74	70		77	73	68		75	71	67
4	86	76	68	62	84	74	67	61		72	65	60		70	64	60		68	63	59
5	80	68	60	54	78	67	59	53		65	58	53		63	57	52		61	56	52
6	74	62	53	47	72	61	53	47		59	52	47		57	51	46		56	50	46
7	69	56	48	42	67	55	48	42		54	47	42		52	46	41		51	45	41
8	64	51	43	38	63	51	43	38		49	42	37		48	42	37		47	41	37
9	60	47	39	34	59	47	39	34		46	39	34		45	38	34		44	38	34
10	56	44	36	31	55	43	36	31		42	36	31		41	35	31		40	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204466

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.5	4.2
10°-20°	171.7	11.8
20°-30°	255.4	17.6
30°-40°	297.2	20.4
40°-50°	289.7	19.9
50°-60°	222.8	15.3
60°-70°	123.2	8.5
70°-80°	32.6	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	487.6	33.6
0°-40°	784.8	54.0
0°-60°	1297.3	89.3
0°-90°	1453.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1453.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	641	
5°	637	61
15°	608	172
25°	554	255
35°	477	297
45°	376	290
55°	249	223
65°	123	123
75°	28	33
85°	0	0
90°	0	



TEST NUMBER: P204466

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	641.1
2.5°	641.1
5°	637.4
7.5°	631.9
10°	628.2
12.5°	617.1
15°	608.0
17.5°	598.8
20°	585.9
22.5°	573.0
25°	554.5
27.5°	536.1
30°	517.6
32.5°	497.4
35°	477.1
37.5°	451.4
40°	429.2
42.5°	405.2
45°	375.9
47.5°	348.2
50°	316.9
52.5°	283.8
55°	248.8
57.5°	215.5
60°	184.2
62.5°	152.9
65°	123.4
67.5°	95.8
70°	70.0
72.5°	47.9
75°	27.6
77.5°	12.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)