

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204363

Luminaire Tested: **LE_6B15D010 EC6B10209035 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209035 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1517.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204363

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P204363

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	102	99	101	98	96		97	95	93		93
2	102	95	89	84	100	93	88	83	90	85	82		87	83	80		84
3	94	85	78	72	92	83	77	71	80	75	70		78	73	69		75
4	87	76	68	62	85	75	67	62	72	66	61		70	65	60		68
5	80	68	60	54	78	67	60	54	65	59	53		63	58	53		62
6	74	62	54	48	73	61	53	48	59	52	47		58	52	47		56
7	69	57	48	43	68	56	48	43	54	47	42		53	47	42		52
8	65	52	44	38	63	51	44	38	50	43	38		49	42	38		48
9	60	48	40	35	59	47	40	35	46	39	35		45	39	34		44
10	57	44	37	32	56	44	36	32	43	36	31		42	36	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204363

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.3	4.4
10°-20°	186.2	12.3
20°-30°	271.6	17.9
30°-40°	309.7	20.4
40°-50°	297.1	19.6
50°-60°	227.5	15.0
60°-70°	124.9	8.2
70°-80°	33.2	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.1	34.6
0°-40°	833.8	55.0
0°-60°	1358.4	89.5
0°-90°	1517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	704	
5°	699	66
15°	661	186
25°	590	272
35°	495	310
45°	386	297
55°	255	228
65°	126	125
75°	29	33
85°	0	0
90°	0	



TEST NUMBER: P204363

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	704.5
2.5°	702.8
5°	699.1
7.5°	693.6
10°	686.4
12.5°	673.6
15°	660.9
17.5°	646.2
20°	629.9
22.5°	609.9
25°	589.9
27.5°	569.9
30°	544.4
32.5°	520.6
35°	495.2
37.5°	469.8
40°	444.2
42.5°	416.9
45°	386.0
47.5°	355.0
50°	322.2
52.5°	287.6
55°	254.9
57.5°	222.1
60°	187.5
62.5°	154.8
65°	125.6
67.5°	96.5
70°	71.0
72.5°	47.4
75°	29.1
77.5°	12.8
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)