

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205185

Luminaire Tested: **LE_6B15D010 EC6B10209035 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209035 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1604.4 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205185

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P205185

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	104	110	107	105	103		103	101	99			100	98	97			96
2	106	101	96	92	104	99	95	91		95	92	89			92	90	87			90
3	100	92	87	82	97	91	86	81		88	84	80			86	82	79			83
4	93	85	78	73	92	84	78	73		81	76	72			79	75	71			77
5	88	78	71	66	86	77	71	66		75	70	65			73	69	65			72
6	82	72	65	60	81	71	65	60		70	64	59			68	63	59			67
7	77	67	60	55	76	66	59	55		65	59	54			63	58	54			62
8	73	62	55	50	71	61	55	50		60	54	50			59	54	50			58
9	69	57	51	46	67	57	50	46		56	50	46			55	50	46			54
10	65	54	47	43	64	53	47	42		52	46	42			51	46	42			51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205185

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.7	6.0
10°-20°	290.6	18.1
20°-30°	438.1	27.3
30°-40°	448.4	27.9
40°-50°	261.2	16.3
50°-60°	60.0	3.7
60°-70°	7.4	0.5
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	825.4	51.4
0°-40°	1273.8	79.4
0°-60°	1595.0	99.4
0°-90°	1604.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1604.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1002	
5°	1008	97
15°	1030	291
25°	960	438
35°	728	448
45°	336	261
55°	58	60
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205185

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1002.2
2.5°	1000.4
5°	1007.6
7.5°	1015.0
10°	1024.0
12.5°	1025.9
15°	1029.5
17.5°	1025.9
20°	1016.8
22.5°	987.6
25°	960.4
27.5°	916.8
30°	860.4
32.5°	802.1
35°	727.6
37.5°	643.9
40°	551.1
42.5°	447.5
45°	336.5
47.5°	234.6
50°	154.6
52.5°	98.2
55°	58.2
57.5°	30.9
60°	16.4
62.5°	9.1
65°	5.5
67.5°	5.5
70°	3.6
72.5°	1.9
75°	1.9
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)