

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212548

Luminaire Tested: **LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3313.4 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212548

CATALOG NUMBER: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212548

CATALOG NUMBER: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40274	40274	40274
5°	78038	38375	12944
10°	132585	33586	5810
15°	204307	26785	9240
20°	295756	17434	16078
25°	433926	16822	20670
30°	504542	15939	15840
35°	510680	8441	8373
40°	422803	3181	3513
45°	319325	1084	1285
50°	218478	395	395
55°	30394	345	53
60°	792	344	0
65°	194	469	0
70°	88	579	0
75°	0	765	0
80°	0	1314	174
85°	0	2618	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212548

CATALOG NUMBER: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	3.0
10°-20°	414.8	12.5
20°-30°	946.3	28.6
30°-40°	1095.1	33.0
40°-50°	660.4	19.9
50°-60°	89.7	2.7
60°-70°	2.9	0.1
70°-80°	3.2	0.1
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1459.2	44.0
0°-40°	2554.3	77.1
0°-60°	3304.4	99.7
0°-90°	3313.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3313.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	935	935	935	935	935	
5°	1806	1478	888	486	300	210
15°	4584	2576	601	185	207	1357
25°	9134	3053	354	426	435	4134
35°	9716	2328	161	164	159	5855
45°	5244	634	18	22	21	4101
55°	405	5	5	3	1	794
65°	2	3	5	3	0	3
75°	0	3	5	3	0	0
85°	0	3	5	3	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212548

CATALOG NUMBER: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4
2.5°	1352.7	1340.2	1345.4	1331.6	1296.8	1289.5	1288.8	1279.7	1250.0	1227.0	1199.4
5°	1805.6	1805.0	1808.3	1778.6	1717.4	1698.3	1689.1	1666.7	1595.0	1539.7	1478.5
7.5°	2371.0	2367.1	2363.1	2309.1	2213.1	2176.2	2152.5	2071.5	1972.8	1874.7	1765.5
10°	3032.6	3030.6	3015.5	2920.7	2766.6	2698.8	2652.7	2524.4	2365.7	2226.2	2040.6
12.5°	3800.8	3783.0	3756.0	3617.1	3405.8	3332.1	3230.7	3027.3	2783.8	2569.8	2310.5
15°	4583.5	4557.8	4509.8	4331.4	4069.4	3943.6	3817.9	3550.0	3219.6	2908.8	2576.4
17.5°	5349.0	5320.7	5208.1	4905.3	4649.3	4495.9	4356.4	3988.4	3600.0	3200.5	2779.2
20°	6454.9	6352.2	6156.0	5678.8	5202.9	4926.4	4763.2	4374.1	3893.6	3428.2	2923.3
22.5°	7932.0	7704.2	7286.2	6510.8	5830.9	5431.9	5164.7	4647.3	4104.9	3577.0	3012.2
25°	9134.0	9030.7	8555.4	7452.1	6391.1	5921.0	5549.1	4864.5	4258.9	3676.4	3053.0
27.5°	9908.7	9883.0	9340.1	8231.5	6848.6	6231.8	5816.4	5008.0	4333.3	3697.5	3033.2
30°	10148.4	10188.5	9667.1	8496.2	6980.8	6294.3	5840.0	5010.0	4276.0	3602.0	2906.9
32.5°	10130.6	10132.6	9493.4	8267.7	6765.6	6112.6	5642.6	4843.4	4064.7	3363.0	2666.6
35°	9715.9	9613.8	8891.1	7566.0	6264.6	5688.7	5251.6	4520.9	3716.5	3003.6	2327.6
37.5°	8805.5	8671.9	7829.3	6667.5	5671.6	5139.0	4786.2	4097.7	3301.8	2619.9	1977.4
40°	7522.5	7333.0	6637.9	5832.1	5022.5	4622.3	4326.0	3624.3	2858.2	2243.3	1649.0
42.5°	6238.3	6145.5	5686.1	5031.0	4476.8	4100.3	3790.9	3128.7	2431.6	1872.1	1233.6
45°	5244.3	5164.7	4856.0	4424.2	3880.4	3536.8	3238.6	2612.0	1889.2	1256.0	633.9
47.5°	4520.3	4455.8	4160.2	3706.6	3110.2	2734.4	2427.0	1712.8	1070.3	542.4	158.6
50°	3261.7	3195.8	2906.2	2380.9	1842.5	1527.8	1306.6	764.9	303.4	109.9	16.4
52.5°	1598.9	1544.9	1348.1	1009.1	677.4	487.2	356.2	143.5	34.9	11.9	7.9
55°	404.9	371.9	310.1	194.8	95.4	57.3	36.9	13.1	8.6	6.6	4.6
57.5°	23.0	22.4	20.4	15.2	11.2	9.9	8.6	6.6	4.6	4.0	3.3
60°	9.2	8.6	7.9	6.6	5.3	4.6	4.6	3.3	2.6	2.6	2.6
62.5°	4.0	4.0	4.0	3.3	2.6	2.6	2.6	1.9	2.6	2.6	2.6
65°	1.9	1.9	1.9	1.4	1.4	1.4	1.9	1.9	1.9	2.6	2.6
67.5°	1.4	0.7	0.7	0.7	1.4	1.4	1.4	1.9	1.9	2.6	2.6
70°	0.7	0.7	0.7	0.7	1.4	1.4	1.4	1.9	1.9	2.6	3.3
72.5°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	1.9	1.9	2.6	3.3
75°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	1.9	2.6	2.6	3.3
77.5°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	1.9	2.6	2.6	3.3
80°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	1.9	2.6	2.6	3.3
82.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	1.9	2.6	2.6	3.3
85°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	1.9	2.6	2.6	3.3
87.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	1.9	1.9	2.6	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212548

CATALOG NUMBER: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4
2.5°	1163.8	1140.1	1105.2	1082.2	1059.8	1038.7	1003.9	984.1	948.5	915.7	887.4
5°	1404.8	1345.4	1273.8	1212.5	1173.0	1134.2	1063.8	1011.8	946.6	887.9	834.0
7.5°	1648.3	1543.6	1425.8	1325.1	1263.8	1203.9	1098.6	1014.4	922.2	838.6	759.0
10°	1869.5	1712.1	1545.6	1401.5	1318.5	1240.8	1101.9	990.1	871.5	768.2	668.1
12.5°	2074.9	1859.6	1642.4	1454.1	1351.4	1257.9	1088.1	951.2	810.3	687.9	571.4
15°	2257.8	1981.4	1712.8	1484.4	1363.9	1253.3	1055.8	896.5	737.9	600.9	453.5
17.5°	2396.7	2057.1	1743.7	1479.7	1341.5	1218.4	1000.6	828.1	660.9	495.0	328.4
20°	2481.0	2089.3	1737.2	1444.2	1293.5	1163.2	934.7	753.7	568.1	380.5	289.6
22.5°	2516.5	2086.7	1706.2	1390.9	1234.3	1102.6	871.5	681.3	470.6	344.3	302.2
25°	2522.4	2059.7	1662.8	1332.3	1175.6	1044.6	807.7	599.0	408.8	354.1	338.4
27.5°	2477.0	1996.5	1581.1	1248.1	1093.3	957.8	712.2	475.9	383.8	352.8	363.3
30°	2342.7	1852.3	1437.0	1100.0	950.5	814.9	508.8	373.3	318.6	320.6	323.2
32.5°	2106.5	1612.7	1205.3	883.4	720.2	537.1	316.7	249.5	242.3	242.3	240.9
35°	1791.2	1319.8	945.9	558.8	358.1	258.0	163.9	164.6	161.2	160.6	160.0
37.5°	1465.3	1041.3	599.0	231.1	155.3	108.0	96.8	98.0	96.8	98.7	97.5
40°	1155.2	643.2	218.5	73.7	54.7	52.6	54.0	55.3	55.3	56.6	56.6
42.5°	671.5	213.3	57.3	29.7	29.7	28.3	29.0	30.2	30.9	31.6	30.9
45°	199.5	44.1	18.5	16.4	16.4	15.8	15.8	16.4	17.1	17.8	17.8
47.5°	31.6	12.5	10.5	9.2	9.2	9.2	9.2	9.2	9.9	9.9	10.5
50°	9.9	7.9	6.6	5.9	5.9	5.3	5.3	5.9	5.9	5.9	6.6
52.5°	5.9	4.6	4.6	4.0	4.6	4.6	4.0	4.6	4.6	4.6	5.3
55°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.6	4.6	4.6
57.5°	3.3	3.3	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
60°	3.3	3.3	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.6
62.5°	3.3	3.3	4.0	4.0	4.0	4.0	4.0	4.0	4.6	4.6	4.6
65°	3.3	3.3	4.0	4.0	4.0	4.0	4.0	4.6	4.6	4.6	4.6
67.5°	3.3	4.0	4.0	4.0	4.0	4.6	4.6	4.6	4.6	4.6	4.6
70°	3.3	4.0	4.0	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
72.5°	3.3	4.0	4.0	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
75°	4.0	4.0	4.0	4.6	4.6	4.6	4.6	4.6	4.6	4.6	5.3
77.5°	4.0	4.0	4.6	4.6	4.6	4.6	4.6	4.6	5.3	5.3	5.3
80°	4.0	4.0	4.6	4.6	4.6	4.6	4.6	5.3	5.3	5.3	5.3
82.5°	4.0	4.0	4.6	4.6	4.6	4.6	4.6	5.3	5.3	5.3	5.3
85°	4.0	4.0	4.6	4.6	4.6	4.6	4.6	5.3	5.3	5.3	5.3
87.5°	4.0	4.0	4.6	4.6	4.6	4.6	4.6	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212548

CATALOG NUMBER: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4
2.5°	863.0	832.7	818.2	797.8	783.3	751.1	737.9	715.5	697.1	666.8	668.8
5°	788.0	730.7	691.8	661.5	640.5	589.2	554.9	518.7	485.8	444.9	429.9
7.5°	683.9	613.5	554.3	518.1	491.0	422.6	346.9	287.7	242.9	210.7	198.1
10°	579.9	488.4	394.3	338.4	299.5	233.7	200.2	184.3	169.8	152.0	140.2
12.5°	458.8	328.4	242.9	220.5	204.7	183.0	161.2	144.1	147.4	148.1	152.7
15°	313.4	236.3	209.3	194.2	177.1	164.6	171.9	176.4	185.0	185.7	191.6
17.5°	254.7	221.8	200.2	199.5	200.7	208.0	219.2	225.1	236.3	239.0	247.5
20°	254.7	235.7	254.1	254.1	257.3	267.3	281.8	290.3	302.8	307.4	317.9
22.5°	290.3	303.4	326.5	329.1	330.5	341.0	359.4	367.9	382.4	385.0	396.3
25°	354.1	366.0	387.1	389.0	389.7	397.6	411.4	416.1	425.9	420.6	427.2
27.5°	374.5	379.8	393.0	394.3	391.0	394.3	399.5	399.5	402.8	392.3	394.3
30°	329.1	330.5	337.0	337.7	330.5	331.7	332.4	331.7	331.1	319.9	319.9
32.5°	244.2	244.2	252.8	250.8	242.9	244.9	244.9	244.9	244.2	235.0	233.7
35°	161.9	162.6	169.8	168.5	162.6	163.9	163.9	165.9	163.9	158.6	157.4
37.5°	98.7	99.4	102.7	103.4	101.3	102.0	102.7	102.0	103.4	100.8	99.4
40°	57.3	58.5	61.2	61.9	61.2	61.2	61.9	62.5	65.2	61.9	60.6
42.5°	33.6	34.2	35.5	35.5	35.5	35.5	36.2	36.9	37.5	36.9	36.2
45°	19.1	19.7	20.4	20.4	21.1	20.4	21.1	21.1	21.7	21.1	21.1
47.5°	11.2	11.2	11.9	11.9	12.5	11.9	12.5	12.5	12.5	11.9	11.9
50°	6.6	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	6.6	6.6
52.5°	5.3	5.3	5.3	5.3	5.3	4.6	4.6	4.6	4.6	4.0	4.0
55°	4.6	4.6	4.6	4.6	4.6	4.6	4.0	3.3	3.3	2.6	2.6
57.5°	4.0	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	1.9	1.9
60°	4.6	4.6	4.6	4.6	4.0	4.0	4.0	3.3	2.6	1.9	1.9
62.5°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	1.9	1.9
65°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	1.9	1.9
67.5°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	2.6	1.9
70°	4.6	5.3	5.3	4.6	4.6	4.6	4.0	3.3	3.3	2.6	1.9
72.5°	4.6	5.3	5.3	4.6	4.6	4.6	4.0	3.3	3.3	2.6	1.9
75°	5.3	5.3	5.3	5.3	4.6	4.6	4.0	4.0	3.3	2.6	1.9
77.5°	5.3	5.3	5.3	5.3	4.6	4.6	4.0	4.0	3.3	2.6	1.9
80°	5.3	5.3	5.3	5.3	5.3	4.6	4.6	4.0	3.3	2.6	2.6
82.5°	5.3	5.3	5.3	5.3	5.3	4.6	4.6	4.0	3.3	2.6	2.6
85°	5.3	5.3	5.3	5.3	5.3	4.6	4.6	4.0	3.3	2.6	1.9
87.5°	5.3	5.3	5.3	5.3	4.6	4.6	4.0	4.0	3.3	2.6	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212548

CATALOG NUMBER: LDSQA6A40930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4
2.5°	644.4	629.3	622.7	633.2	628.0	612.2	615.4	605.6
5°	384.5	361.4	346.9	353.5	332.4	313.4	313.4	299.5
7.5°	185.7	178.4	174.5	175.7	171.2	165.2	161.9	161.9
10°	130.3	127.7	128.4	128.4	132.3	131.7	133.6	132.9
12.5°	154.7	156.0	156.7	159.3	162.6	162.6	164.6	163.3
15°	198.1	196.8	200.7	201.4	206.7	207.3	210.0	207.3
17.5°	252.1	254.7	258.7	258.0	268.5	269.2	269.2	268.5
20°	324.5	326.5	330.5	331.7	344.3	345.5	350.2	350.9
22.5°	403.5	403.5	405.5	408.1	420.0	420.6	422.6	422.6
25°	430.5	426.6	427.2	430.5	437.1	434.4	436.4	435.1
27.5°	395.6	389.7	388.3	393.0	397.6	390.4	393.0	393.0
30°	321.2	316.0	314.6	319.3	322.5	314.6	317.2	318.6
32.5°	235.0	231.7	231.1	234.4	237.0	230.4	233.0	235.0
35°	158.6	157.4	156.0	156.7	160.6	155.3	157.9	159.3
37.5°	100.8	98.0	98.7	100.1	102.7	99.4	102.0	102.0
40°	61.9	60.6	60.6	61.9	63.2	60.6	61.9	62.5
42.5°	36.2	36.2	36.2	36.9	37.5	36.2	36.2	36.9
45°	21.1	20.4	20.4	21.1	21.7	20.4	21.1	21.1
47.5°	11.9	11.2	11.2	11.9	11.9	11.2	11.9	11.9
50°	6.6	5.9	5.9	6.6	6.6	5.9	5.9	5.9
52.5°	3.3	3.3	3.3	3.3	3.3	3.3	2.6	2.6
55°	1.9	1.9	1.4	1.4	1.4	1.4	1.4	0.7
57.5°	1.4	1.4	0.7	0.7	0.7	0.7	0.0	0.0
60°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
62.5°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
65°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
67.5°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
70°	1.9	1.4	1.4	0.7	0.7	0.7	0.0	0.0
72.5°	1.9	1.4	1.4	1.4	0.7	0.7	0.0	0.0
75°	1.9	1.4	1.4	1.4	0.7	0.7	0.0	0.0
77.5°	1.9	1.4	1.4	1.4	0.7	0.7	0.7	0.0
80°	1.9	1.4	1.4	1.4	0.7	0.7	0.7	0.7
82.5°	1.9	1.4	1.4	1.4	0.7	0.7	0.7	0.7
85°	1.9	1.4	1.4	1.4	0.7	0.7	0.7	0.0
87.5°	1.9	1.4	1.4	1.4	0.7	0.7	0.7	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)