

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212552

Luminaire Tested: **LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3807.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212552

CATALOG NUMBER: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212552

CATALOG NUMBER: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30720	30720	30720
5°	84318	28305	11548
10°	184773	23167	4403
15°	282241	17634	5162
20°	327005	13118	8018
25°	356718	10789	12946
30°	398343	9784	13220
35°	405295	6712	9062
40°	412411	3181	4586
45°	413083	1321	2003
50°	349221	576	616
55°	112455	398	105
60°	22337	456	0
65°	2282	540	0
70°	239	743	0
75°	0	981	0
80°	0	1636	174
85°	0	3260	346

TEST NUMBER: P1212552

CATALOG NUMBER: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.8	2.5
10°-20°	500.9	13.2
20°-30°	959.1	25.2
30°-40°	1130.0	29.7
40°-50°	887.6	23.3
50°-60°	216.3	5.7
60°-70°	9.3	0.2
70°-80°	3.5	0.1
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1556.9	40.9
0°-40°	2686.9	70.6
0°-60°	3790.7	99.6
0°-90°	3807.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3807.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	714	714	714	714	714	
5°	1951	1412	655	343	267	258
15°	6332	3252	396	113	116	1768
25°	7509	3954	227	238	272	3500
35°	7711	2500	128	164	172	4835
45°	6784	773	22	30	33	5097
55°	1498	28	5	3	1	1783
65°	22	3	5	3	0	59
75°	0	3	6	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212552

CATALOG NUMBER: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5
2.5°	1223.0	1220.3	1202.6	1219.0	1169.0	1167.0	1144.6	1134.8	1105.8	1078.2	1038.6
5°	1950.9	1908.1	1873.3	1874.5	1778.5	1760.7	1710.7	1660.0	1582.3	1510.0	1411.8
7.5°	2973.7	2923.1	2849.4	2818.4	2634.8	2580.9	2477.5	2342.5	2173.4	2004.9	1823.2
10°	4226.3	4234.3	4138.8	4050.6	3772.8	3663.6	3496.3	3230.5	2909.9	2593.3	2271.5
12.5°	5486.8	5481.6	5367.7	5234.1	4891.8	4737.7	4515.3	4183.6	3759.0	3268.0	2764.5
15°	6331.9	6369.4	6321.4	6214.8	5922.5	5746.2	5495.4	5045.1	4527.8	3931.4	3252.2
17.5°	6862.5	6898.0	6880.9	6797.3	6539.2	6351.1	6141.7	5773.1	5174.8	4425.1	3636.6
20°	7136.9	7192.8	7185.0	7094.1	6899.3	6743.4	6512.3	6170.7	5652.6	4768.1	3885.3
22.5°	7319.9	7362.7	7374.5	7271.9	7070.4	6922.4	6753.2	6407.0	5919.9	4977.3	3984.1
25°	7508.8	7584.5	7510.2	7383.7	7198.8	7056.6	6876.3	6544.6	6047.5	5062.9	3954.5
27.5°	7740.5	7776.7	7608.2	7493.0	7287.6	7133.6	6942.1	6624.2	6070.0	4994.4	3785.4
30°	8012.3	7862.3	7744.4	7516.1	7283.1	7132.9	6938.1	6574.1	5952.1	4767.4	3457.5
32.5°	7967.6	7830.0	7696.4	7454.8	7224.4	7075.7	6858.5	6407.7	5673.7	4387.6	3005.3
35°	7710.9	7740.5	7596.3	7396.3	7135.6	6982.2	6745.3	6170.7	5201.1	3863.7	2499.9
37.5°	7494.3	7559.5	7465.3	7280.5	7015.8	6808.5	6488.6	5790.2	4584.4	3198.9	2020.7
40°	7337.6	7358.7	7308.1	7100.7	6782.8	6483.3	6113.4	5107.0	3835.4	2511.0	1594.9
42.5°	7094.8	7150.7	7061.3	6834.8	6353.0	6014.0	5478.3	4317.8	2979.0	1918.0	1200.5
45°	6784.1	6837.4	6726.8	6350.4	5680.3	5183.4	4529.8	3366.7	2203.6	1413.8	772.7
47.5°	6277.3	6310.2	6096.3	5575.7	4601.5	4133.5	3463.5	2347.2	1419.7	790.5	375.9
50°	5213.6	5197.9	4756.9	4116.4	3077.8	2586.8	2061.5	1272.3	637.8	374.5	234.9
52.5°	3360.1	3323.9	2887.6	2305.1	1558.6	1189.3	893.8	549.0	332.4	209.3	92.8
55°	1498.1	1484.3	1215.0	943.9	637.8	549.0	419.2	269.2	177.1	73.0	28.3
57.5°	555.5	543.0	478.6	401.5	308.1	256.1	203.3	129.0	45.4	24.3	15.2
60°	259.4	258.7	227.8	187.6	130.3	98.7	57.3	30.2	19.1	13.1	8.6
62.5°	83.0	81.0	56.6	41.4	29.7	25.7	20.4	15.2	9.9	7.2	5.3
65°	22.4	22.4	20.4	17.1	13.8	11.9	9.9	7.2	4.6	4.0	3.3
67.5°	8.6	8.6	7.9	7.2	5.3	4.6	4.0	3.3	2.6	3.3	3.3
70°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	3.3
72.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	3.3
75°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	3.3
77.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	3.3
80°	0.0	0.0	0.7	0.7	1.4	1.4	1.9	1.9	2.6	3.3	3.3
82.5°	0.0	0.0	0.7	1.4	1.4	1.4	1.9	2.6	2.6	3.3	4.0
85°	0.0	0.0	0.7	1.4	1.4	1.9	1.9	2.6	2.6	3.3	4.0
87.5°	0.0	0.0	0.7	1.4	1.4	1.9	1.9	2.6	2.6	3.3	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212552

CATALOG NUMBER: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5
2.5°	1009.7	966.3	906.3	871.4	862.9	844.5	812.2	764.2	724.7	686.5	664.1
5°	1328.9	1226.2	1111.1	1030.0	997.2	953.1	874.7	793.8	719.4	654.9	604.2
7.5°	1667.2	1498.1	1311.8	1161.7	1107.7	1038.0	910.3	789.8	687.8	598.3	530.5
10°	2003.6	1731.1	1478.4	1261.1	1172.9	1078.2	909.7	753.7	633.9	529.9	454.8
12.5°	2339.9	1948.3	1600.8	1321.0	1206.5	1086.7	882.6	698.3	565.4	459.4	387.7
15°	2650.6	2121.4	1683.6	1341.4	1203.2	1061.7	828.1	631.2	493.6	395.6	329.1
17.5°	2882.3	2212.2	1702.8	1310.5	1151.2	994.6	744.4	552.3	425.2	339.0	271.2
20°	2996.1	2226.7	1657.4	1222.3	1061.7	899.2	652.9	476.5	366.6	286.3	229.0
22.5°	2996.1	2158.2	1558.6	1111.7	949.8	789.2	564.7	414.0	320.5	249.4	201.4
25°	2882.3	2022.0	1426.3	984.1	826.7	680.5	488.4	367.3	285.0	227.1	186.9
27.5°	2661.1	1833.8	1256.5	841.9	705.6	583.9	427.8	324.5	258.0	204.7	205.4
30°	2357.0	1602.7	1061.7	691.8	581.2	479.8	360.0	271.8	206.7	196.8	202.8
32.5°	2005.5	1326.3	841.2	536.4	450.3	377.8	273.9	192.2	164.5	165.9	172.4
35°	1644.8	1044.0	633.2	397.5	335.0	273.9	179.7	126.4	125.1	127.7	132.3
37.5°	1298.6	781.3	458.1	291.0	225.1	168.5	96.8	86.8	86.8	89.5	92.2
40°	972.9	554.2	315.3	172.4	109.3	77.0	61.2	56.6	55.9	56.6	59.9
42.5°	668.1	350.9	187.6	69.1	52.6	44.7	38.8	35.5	34.9	35.5	37.5
45°	375.2	215.9	73.0	36.9	31.6	28.3	24.3	22.4	21.7	21.7	23.0
47.5°	234.9	85.6	32.9	23.0	19.7	18.5	15.8	14.5	13.8	13.8	14.5
50°	90.1	33.5	20.4	15.2	13.1	11.9	10.5	9.2	8.6	8.6	9.2
52.5°	30.9	19.7	13.1	9.9	8.6	7.9	6.6	5.9	5.9	5.9	5.9
55°	17.1	11.9	7.9	5.9	5.3	5.3	5.3	5.3	5.3	5.3	5.3
57.5°	10.5	7.2	5.3	4.6	4.6	4.6	4.6	4.6	4.6	5.3	5.3
60°	5.9	4.6	4.0	4.0	4.0	4.0	4.6	4.6	4.6	5.3	5.3
62.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.6	4.6	5.3	5.3	5.3
65°	3.3	3.3	3.3	4.0	4.0	4.0	4.6	4.6	5.3	5.3	5.3
67.5°	3.3	3.3	4.0	4.0	4.0	4.6	4.6	5.3	5.3	5.3	5.3
70°	3.3	4.0	4.0	4.6	4.6	4.6	5.3	5.3	5.3	5.9	5.9
72.5°	3.3	4.0	4.0	4.6	4.6	4.6	5.3	5.3	5.9	5.9	5.9
75°	4.0	4.0	4.0	4.6	4.6	4.6	5.3	5.9	5.9	5.9	5.9
77.5°	4.0	4.0	4.6	4.6	4.6	5.3	5.3	5.9	5.9	5.9	5.9
80°	4.0	4.0	4.6	4.6	5.3	5.3	5.9	5.9	5.9	6.6	6.6
82.5°	4.0	4.0	4.6	5.3	5.3	5.3	5.9	5.9	6.6	6.6	6.6
85°	4.0	4.6	4.6	5.3	5.3	5.3	5.9	5.9	6.6	6.6	6.6
87.5°	4.0	4.6	4.6	5.3	5.3	5.3	5.9	5.9	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212552

CATALOG NUMBER: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5
2.5°	634.5	606.8	579.2	558.8	549.0	539.0	517.4	489.1	477.2	460.1	450.3
5°	552.9	506.2	469.3	444.9	430.4	411.4	386.4	358.7	342.9	325.2	313.3
7.5°	468.6	414.0	378.5	356.1	341.6	317.9	286.3	253.4	234.4	214.5	200.7
10°	394.9	342.9	302.7	277.1	258.7	231.1	199.5	176.4	160.0	142.9	129.0
12.5°	329.8	273.9	231.1	209.3	196.8	170.5	144.1	118.4	108.6	105.3	105.3
15°	267.2	216.6	180.4	161.9	148.8	120.5	115.1	113.9	113.2	112.5	113.9
17.5°	217.8	175.0	136.9	127.7	126.4	125.7	126.4	126.4	127.0	129.0	132.3
20°	183.0	143.5	140.8	141.5	141.5	144.1	147.4	150.1	152.7	156.0	161.9
22.5°	162.6	161.9	166.5	167.2	170.5	174.5	180.4	184.3	190.9	194.2	202.8
25°	187.6	192.2	200.7	203.3	208.7	215.2	224.4	229.7	237.6	241.6	251.4
27.5°	212.6	219.9	230.4	233.7	238.3	248.8	255.4	260.0	263.9	266.6	272.5
30°	210.6	217.3	227.8	228.4	234.9	242.2	246.1	250.1	252.7	252.1	255.4
32.5°	178.4	184.3	194.2	194.2	201.4	207.3	209.3	212.6	212.6	212.6	213.9
35°	136.9	140.8	147.4	149.4	155.3	159.3	160.6	164.5	164.5	163.3	163.3
37.5°	94.8	100.1	104.6	106.0	109.9	112.5	115.8	116.5	115.1	115.8	115.8
40°	61.8	65.2	68.5	69.1	72.4	74.4	77.7	77.7	78.3	77.7	79.0
42.5°	38.2	40.8	42.8	44.1	45.4	46.8	48.7	49.4	50.0	49.4	50.7
45°	23.7	25.0	26.4	27.0	27.6	28.3	30.2	30.2	30.2	30.2	30.9
47.5°	14.5	15.2	15.8	15.8	16.4	17.1	17.8	17.8	17.8	17.8	18.5
50°	8.6	9.2	9.2	9.2	9.9	9.9	10.5	10.5	10.5	9.9	10.5
52.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.3	5.9
55°	5.3	5.3	4.6	4.6	4.6	4.6	4.6	4.0	3.3	3.3	2.6
57.5°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	3.3	3.3	2.6	1.9
60°	4.6	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	2.6	1.9
62.5°	5.3	4.6	4.6	4.6	4.6	4.0	4.0	3.3	2.6	2.6	1.9
65°	5.3	5.3	4.6	4.6	4.6	4.0	4.0	3.3	3.3	2.6	1.9
67.5°	5.3	5.3	5.3	4.6	5.3	4.6	4.0	4.0	3.3	2.6	2.6
70°	5.9	5.3	5.3	5.3	5.3	4.6	4.6	4.0	3.3	2.6	2.6
72.5°	5.9	5.9	5.3	5.3	5.3	4.6	4.6	4.0	3.3	3.3	2.6
75°	5.9	5.9	5.3	5.3	5.3	4.6	4.6	4.0	4.0	3.3	2.6
77.5°	5.9	5.9	5.9	5.3	5.3	5.3	4.6	4.6	4.0	3.3	2.6
80°	5.9	5.9	5.9	5.9	5.9	5.3	5.3	4.6	4.0	3.3	2.6
82.5°	6.6	5.9	5.9	5.9	5.9	5.3	5.3	4.6	4.0	3.3	3.3
85°	6.6	6.6	5.9	5.9	5.9	5.3	5.3	4.6	4.0	4.0	3.3
87.5°	6.6	5.9	5.9	5.9	5.9	5.3	5.3	4.6	4.0	3.3	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212552

CATALOG NUMBER: LDSQA6A40930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	713.5	713.5	713.5	713.5	713.5	713.5	713.5	713.5
2.5°	440.3	435.1	435.1	425.8	424.6	417.3	423.2	419.2
5°	300.1	291.5	288.9	279.8	276.5	267.9	270.5	267.2
7.5°	188.9	180.4	177.7	171.2	167.2	160.6	161.2	159.3
10°	115.1	107.3	105.3	103.4	101.3	100.7	101.3	100.7
12.5°	104.6	104.0	102.7	103.4	102.0	102.7	103.4	102.7
15°	113.9	115.1	113.9	114.6	113.9	115.1	115.8	115.8
17.5°	133.6	136.2	135.0	136.9	136.2	139.6	139.6	139.6
20°	163.9	168.5	167.2	169.8	169.8	173.8	173.8	175.0
22.5°	206.0	211.9	211.3	217.3	215.9	220.5	220.5	221.8
25°	256.7	262.7	263.2	267.2	266.6	271.2	271.2	272.5
27.5°	277.7	281.0	280.4	282.4	283.0	285.6	287.7	286.3
30°	260.6	263.2	262.7	263.9	263.9	265.9	267.9	265.9
32.5°	219.2	221.1	221.1	223.8	221.8	222.5	225.8	223.8
35°	167.8	169.1	167.8	169.1	169.8	169.8	173.1	172.4
37.5°	119.8	120.5	120.5	122.4	120.5	120.5	123.7	124.4
40°	80.3	81.0	80.3	83.0	81.6	81.6	83.6	81.6
42.5°	51.3	52.0	51.3	53.3	52.0	53.3	54.0	54.7
45°	31.6	31.6	30.9	32.3	31.6	32.3	32.9	32.9
47.5°	18.5	18.5	17.8	19.1	18.5	18.5	18.5	19.1
50°	9.9	9.9	9.9	10.5	9.9	9.9	9.9	9.2
52.5°	5.3	5.3	4.6	5.3	4.6	4.6	4.6	4.6
55°	2.6	1.9	1.9	1.9	1.4	1.4	1.4	1.4
57.5°	1.9	1.4	1.4	0.7	0.7	0.7	0.0	0.0
60°	1.4	1.4	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.4	1.4	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.4	1.4	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	1.9	1.4	1.4	0.7	0.7	0.0	0.0	0.0
70°	1.9	1.4	1.4	0.7	0.7	0.0	0.0	0.0
72.5°	1.9	1.4	1.4	1.4	0.7	0.7	0.0	0.0
75°	1.9	1.9	1.4	1.4	0.7	0.7	0.0	0.0
77.5°	2.6	1.9	1.4	1.4	0.7	0.7	0.0	0.0
80°	2.6	1.9	1.4	1.4	1.4	0.7	0.7	0.7
82.5°	2.6	1.9	1.9	1.4	1.4	0.7	0.7	0.7
85°	2.6	1.9	1.9	1.4	1.4	0.7	0.7	0.7
87.5°	2.6	1.9	1.9	1.4	1.4	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)