

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212554

Luminaire Tested: **LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3536.9 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212554

CATALOG NUMBER: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1212554

CATALOG NUMBER: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	50		59
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	61	50	43	38	60	49	43	38	48	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	42991	42991	42991
5°	83307	40968	13817
10°	141530	35850	6204
15°	218090	28595	9864
20°	315710	18607	17159
25°	463199	17958	22067
30°	538578	17013	16909
35°	545134	9014	8935
40°	451333	3400	3755
45°	340874	1151	1370
50°	233220	422	422
55°	32443	368	53
60°	853	370	0
65°	214	499	0
70°	88	617	0
75°	0	815	0
80°	0	1389	174
85°	0	2766	0



TEST NUMBER: P1212554

CATALOG NUMBER: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	3.0
10°-20°	442.8	12.5
20°-30°	1010.1	28.6
30°-40°	1168.9	33.0
40°-50°	705.0	19.9
50°-60°	95.8	2.7
60°-70°	3.1	0.1
70°-80°	3.3	0.1
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1557.7	44.0
0°-40°	2726.6	77.1
0°-60°	3527.3	99.7
0°-90°	3536.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3536.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	998	998	998	998	998	
5°	1928	1578	948	518	320	224
15°	4893	2750	642	198	221	1448
25°	9750	3259	378	455	464	4412
35°	10371	2485	172	175	170	6250
45°	5598	677	19	23	22	4377
55°	432	5	5	4	1	847
65°	2	3	5	3	0	3
75°	0	4	5	4	0	0
85°	0	4	6	4	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212554

CATALOG NUMBER: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5
2.5°	1444.0	1430.6	1436.2	1421.5	1384.3	1376.6	1375.8	1366.0	1334.3	1309.8	1280.2
5°	1927.5	1926.7	1930.3	1898.6	1833.3	1812.9	1803.0	1779.2	1702.6	1643.6	1578.2
7.5°	2531.0	2526.8	2522.6	2464.9	2362.4	2323.0	2297.7	2211.3	2105.9	2001.2	1884.6
10°	3237.2	3235.0	3218.9	3117.8	2953.4	2880.9	2831.7	2694.8	2525.4	2376.5	2178.2
12.5°	4057.2	4038.3	4009.4	3861.2	3635.6	3556.9	3448.7	3231.6	2971.6	2743.2	2466.4
15°	4892.7	4865.3	4814.0	4623.6	4343.9	4209.7	4075.5	3789.5	3436.7	3105.1	2750.2
17.5°	5709.9	5679.7	5559.5	5236.3	4962.9	4799.2	4650.2	4257.5	3842.9	3416.4	2966.7
20°	6890.4	6780.7	6571.3	6061.9	5553.9	5258.8	5084.5	4669.3	4156.3	3659.5	3120.6
22.5°	8467.2	8224.0	7777.8	6950.1	6224.2	5798.4	5513.2	4960.8	4381.9	3818.3	3215.4
25°	9750.2	9639.9	9132.6	7954.9	6822.2	6320.5	5923.5	5192.7	4546.3	3924.4	3259.0
27.5°	10577.3	10549.9	9970.2	8786.8	7310.6	6652.2	6208.8	5345.9	4625.7	3946.9	3237.9
30°	10833.0	10875.9	10319.4	9069.4	7451.8	6718.9	6234.1	5348.0	4564.5	3845.0	3103.0
32.5°	10814.1	10816.2	10133.9	8825.5	7222.0	6524.9	6023.3	5170.2	4339.0	3589.9	2846.5
35°	10371.4	10262.5	9490.9	8076.4	6687.3	6072.5	5605.9	4825.9	3967.3	3206.3	2484.6
37.5°	9399.6	9257.0	8357.5	7117.3	6054.2	5485.7	5109.1	4374.1	3524.5	2796.7	2110.8
40°	8030.1	7827.7	7085.7	6225.7	5361.4	4934.1	4618.0	3868.9	3051.0	2394.7	1760.1
42.5°	6659.2	6560.1	6069.7	5370.5	4778.8	4376.9	4046.7	3339.8	2595.6	1998.4	1316.8
45°	5598.2	5513.2	5183.6	4722.7	4142.2	3775.4	3457.1	2788.2	2016.6	1340.7	676.7
47.5°	4825.3	4756.4	4440.9	3956.7	3320.1	2918.9	2590.7	1828.3	1142.6	579.0	169.3
50°	3481.8	3411.4	3102.3	2541.5	1966.8	1630.9	1394.8	816.5	323.9	117.4	17.6
52.5°	1706.8	1649.2	1439.1	1077.2	723.1	520.0	380.1	153.2	37.3	12.7	8.4
55°	432.2	397.0	331.0	208.0	101.9	61.1	39.3	14.0	9.2	7.1	4.9
57.5°	24.6	23.9	21.7	16.1	12.0	10.5	9.2	7.1	4.9	4.3	3.5
60°	9.9	9.2	8.4	7.1	5.6	4.9	4.9	3.5	2.8	2.8	2.8
62.5°	4.3	4.3	4.3	3.5	2.8	2.8	2.8	2.1	2.8	2.8	2.8
65°	2.1	2.1	2.1	1.4	1.4	1.4	2.1	2.1	2.1	2.8	2.8
67.5°	1.4	0.7	0.7	0.7	1.4	1.4	1.4	2.1	2.1	2.8	2.8
70°	0.7	0.7	0.7	0.7	1.4	1.4	1.4	2.1	2.1	2.8	3.5
72.5°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	2.1	2.1	2.8	3.5
75°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	2.1	2.8	2.8	3.5
77.5°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	2.1	2.8	2.8	3.5
80°	0.0	0.7	0.7	0.7	1.4	1.4	1.4	2.1	2.8	2.8	3.5
82.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	2.1	2.8	2.8	3.5
85°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	2.1	2.8	2.8	3.5
87.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	2.1	2.1	2.8	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212554

CATALOG NUMBER: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5
2.5°	1242.3	1217.1	1179.8	1155.1	1131.3	1108.8	1071.6	1050.5	1012.6	977.4	947.2
5°	1499.5	1436.2	1359.6	1294.3	1252.1	1210.7	1135.5	1080.0	1010.4	947.9	890.3
7.5°	1759.5	1647.8	1521.9	1414.5	1349.1	1285.2	1172.7	1082.8	984.5	895.2	810.2
10°	1995.6	1827.7	1649.8	1495.9	1407.5	1324.5	1176.3	1056.8	930.4	820.0	713.2
12.5°	2214.8	1985.0	1753.2	1552.2	1442.6	1342.8	1161.5	1015.4	865.0	734.3	609.9
15°	2410.2	2115.1	1828.3	1584.5	1456.0	1337.9	1127.0	957.0	787.7	641.5	484.2
17.5°	2558.5	2195.8	1861.4	1579.6	1432.0	1300.6	1068.0	884.0	705.5	528.4	350.7
20°	2648.4	2230.3	1854.3	1541.6	1380.7	1241.6	997.8	804.6	606.4	406.1	309.2
22.5°	2686.3	2227.5	1821.3	1484.7	1317.5	1177.0	930.4	727.3	502.4	367.5	322.5
25°	2692.6	2198.6	1774.9	1422.2	1254.9	1115.2	862.2	639.4	436.3	378.0	361.2
27.5°	2644.1	2131.2	1687.8	1332.3	1167.1	1022.4	760.2	508.0	409.7	376.6	387.8
30°	2500.8	1977.3	1533.9	1174.2	1014.7	869.9	543.2	398.4	340.1	342.2	345.1
32.5°	2248.6	1721.5	1286.6	943.0	768.7	573.4	338.0	266.3	258.6	258.6	257.1
35°	1912.0	1408.8	1009.8	596.6	382.2	275.4	174.9	175.6	172.1	171.5	170.8
37.5°	1564.1	1111.6	639.4	246.6	165.9	115.2	103.3	104.7	103.3	105.4	104.0
40°	1233.2	686.5	233.3	78.7	58.3	56.2	57.6	59.0	59.0	60.5	60.5
42.5°	716.7	227.7	61.1	31.6	31.6	30.2	30.9	32.4	33.0	33.7	33.0
45°	212.9	47.0	19.7	17.6	17.6	16.9	16.9	17.6	18.3	18.9	18.9
47.5°	33.7	13.3	11.2	9.9	9.9	9.9	9.9	9.9	10.5	10.5	11.2
50°	10.5	8.4	7.1	6.3	6.3	5.6	5.6	6.3	6.3	6.3	7.1
52.5°	6.3	4.9	4.9	4.3	4.9	4.9	4.3	4.9	4.9	4.9	5.6
55°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.9	4.9	4.9
57.5°	3.5	3.5	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
60°	3.5	3.5	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.9
62.5°	3.5	3.5	4.3	4.3	4.3	4.3	4.3	4.3	4.9	4.9	4.9
65°	3.5	3.5	4.3	4.3	4.3	4.3	4.3	4.9	4.9	4.9	4.9
67.5°	3.5	4.3	4.3	4.3	4.3	4.9	4.9	4.9	4.9	4.9	4.9
70°	3.5	4.3	4.3	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
72.5°	3.5	4.3	4.3	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
75°	4.3	4.3	4.3	4.9	4.9	4.9	4.9	4.9	4.9	4.9	5.6
77.5°	4.3	4.3	4.9	4.9	4.9	4.9	4.9	4.9	5.6	5.6	5.6
80°	4.3	4.3	4.9	4.9	4.9	4.9	4.9	5.6	5.6	5.6	5.6
82.5°	4.3	4.3	4.9	4.9	4.9	4.9	4.9	5.6	5.6	5.6	5.6
85°	4.3	4.3	4.9	4.9	4.9	4.9	4.9	5.6	5.6	5.6	5.6
87.5°	4.3	4.3	4.9	4.9	4.9	4.9	4.9	5.6	5.6	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212554

CATALOG NUMBER: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5
2.5°	921.2	888.9	873.5	851.6	836.2	801.8	787.7	763.8	744.1	711.8	713.9
5°	841.1	779.9	738.5	706.1	683.7	628.9	592.4	553.7	518.5	475.0	458.8
7.5°	730.1	654.9	591.7	553.0	524.2	451.1	370.3	307.1	259.3	224.9	211.5
10°	619.0	521.4	420.9	361.2	319.7	249.4	213.6	196.8	181.3	162.3	149.6
12.5°	489.8	350.7	259.3	235.4	218.5	195.3	172.1	153.9	157.4	158.1	163.1
15°	334.4	252.2	223.4	207.3	189.0	175.6	183.4	188.3	197.5	198.1	204.5
17.5°	271.9	236.8	213.6	212.9	214.4	222.1	234.0	240.3	252.2	255.0	264.2
20°	271.9	251.5	271.3	271.3	274.7	285.3	300.7	309.9	323.2	328.2	339.4
22.5°	309.9	323.9	348.5	351.3	352.8	364.0	383.7	392.8	408.2	411.0	423.0
25°	378.0	390.7	413.2	415.3	416.0	424.4	439.1	444.1	454.6	449.0	456.0
27.5°	399.8	405.4	419.5	420.9	417.4	420.9	426.5	426.5	430.1	418.8	420.9
30°	351.3	352.8	359.7	360.5	352.8	354.1	354.8	354.1	353.5	341.5	341.5
32.5°	260.7	260.7	269.8	267.7	259.3	261.4	261.4	261.4	260.7	250.9	249.4
35°	172.8	173.6	181.3	179.9	173.6	174.9	174.9	177.1	174.9	169.3	167.9
37.5°	105.4	106.1	109.6	110.3	108.2	108.9	109.6	108.9	110.3	107.5	106.1
40°	61.1	62.5	65.3	66.1	65.3	65.3	66.1	66.8	69.6	66.1	64.6
42.5°	35.8	36.5	38.0	38.0	38.0	38.0	38.6	39.3	40.1	39.3	38.6
45°	20.4	21.1	21.7	21.7	22.5	21.7	22.5	22.5	23.2	22.5	22.5
47.5°	12.0	12.0	12.7	12.7	13.3	12.7	13.3	13.3	13.3	12.7	12.7
50°	7.1	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.1	7.1
52.5°	5.6	5.6	5.6	5.6	5.6	4.9	4.9	4.9	4.9	4.3	4.3
55°	4.9	4.9	4.9	4.9	4.9	4.9	4.3	3.5	3.5	2.8	2.8
57.5°	4.3	4.9	4.9	4.9	4.9	4.3	4.3	3.5	2.8	2.1	2.1
60°	4.9	4.9	4.9	4.9	4.3	4.3	4.3	3.5	2.8	2.1	2.1
62.5°	4.9	4.9	4.9	4.9	4.9	4.3	4.3	3.5	2.8	2.1	2.1
65°	4.9	4.9	4.9	4.9	4.9	4.3	4.3	3.5	2.8	2.1	2.1
67.5°	4.9	4.9	4.9	4.9	4.9	4.3	4.3	3.5	2.8	2.8	2.1
70°	4.9	5.6	5.6	4.9	4.9	4.9	4.3	3.5	3.5	2.8	2.1
72.5°	4.9	5.6	5.6	4.9	4.9	4.9	4.3	3.5	3.5	2.8	2.1
75°	5.6	5.6	5.6	5.6	4.9	4.9	4.3	4.3	3.5	2.8	2.1
77.5°	5.6	5.6	5.6	5.6	4.9	4.9	4.3	4.3	3.5	2.8	2.1
80°	5.6	5.6	5.6	5.6	5.6	4.9	4.9	4.3	3.5	2.8	2.8
82.5°	5.6	5.6	5.6	5.6	5.6	4.9	4.9	4.3	3.5	2.8	2.8
85°	5.6	5.6	5.6	5.6	5.6	4.9	4.9	4.3	3.5	2.8	2.1
87.5°	5.6	5.6	5.6	5.6	4.9	4.9	4.3	4.3	3.5	2.8	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212554

CATALOG NUMBER: LDSQA6A40935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	998.5	998.5	998.5	998.5	998.5	998.5	998.5	998.5
2.5°	687.9	671.8	664.7	676.0	670.3	653.5	657.0	646.4
5°	410.4	385.7	370.3	377.3	354.8	334.4	334.4	319.7
7.5°	198.1	190.4	186.2	187.6	182.7	176.4	172.8	172.8
10°	139.1	136.3	137.0	137.0	141.2	140.6	142.7	141.9
12.5°	165.1	166.5	167.2	170.0	173.6	173.6	175.6	174.3
15°	211.5	210.1	214.4	215.0	220.6	221.3	224.1	221.3
17.5°	269.1	271.9	276.2	275.4	286.7	287.4	287.4	286.7
20°	346.4	348.5	352.8	354.1	367.5	368.9	373.8	374.5
22.5°	430.7	430.7	432.9	435.7	448.3	449.0	451.1	451.1
25°	459.5	455.4	456.0	459.5	466.6	463.8	465.9	464.5
27.5°	422.3	416.0	414.6	419.5	424.4	416.6	419.5	419.5
30°	342.9	337.3	335.9	340.8	344.3	335.9	338.7	340.1
32.5°	250.9	247.3	246.6	250.2	253.0	245.9	248.7	250.9
35°	169.3	167.9	166.5	167.2	171.5	165.9	168.7	170.0
37.5°	107.5	104.7	105.4	106.8	109.6	106.1	108.9	108.9
40°	66.1	64.6	64.6	66.1	67.4	64.6	66.1	66.8
42.5°	38.6	38.6	38.6	39.3	40.1	38.6	38.6	39.3
45°	22.5	21.7	21.7	22.5	23.2	21.7	22.5	22.5
47.5°	12.7	12.0	12.0	12.7	12.7	12.0	12.7	12.7
50°	7.1	6.3	6.3	7.1	7.1	6.3	6.3	6.3
52.5°	3.5	3.5	3.5	3.5	3.5	3.5	2.8	2.8
55°	2.1	2.1	1.4	1.4	1.4	1.4	1.4	0.7
57.5°	1.4	1.4	0.7	0.7	0.7	0.7	0.0	0.0
60°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
62.5°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
65°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
67.5°	1.4	1.4	0.7	0.7	0.7	0.0	0.0	0.0
70°	2.1	1.4	1.4	0.7	0.7	0.7	0.0	0.0
72.5°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
75°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
77.5°	2.1	1.4	1.4	1.4	0.7	0.7	0.7	0.0
80°	2.1	1.4	1.4	1.4	0.7	0.7	0.7	0.7
82.5°	2.1	1.4	1.4	1.4	0.7	0.7	0.7	0.7
85°	2.1	1.4	1.4	1.4	0.7	0.7	0.7	0.0
87.5°	2.1	1.4	1.4	1.4	0.7	0.7	0.7	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)