

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202814

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1734.9 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202814

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202814

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	71	64	59	80	71	64	59	69	63	59		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	54	49	71	61	54	49	59	53	49		58	53	49		57
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53
10	64	53	46	42	63	53	46	42	52	46	42		51	45	42		50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202814

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	6.0
10°-20°	308.0	17.8
20°-30°	463.6	26.7
30°-40°	474.0	27.3
40°-50°	287.9	16.6
50°-60°	81.1	4.7
60°-70°	12.3	0.7
70°-80°	4.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	875.2	50.4
0°-40°	1349.2	77.8
0°-60°	1718.2	99.0
0°-90°	1734.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1734.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1078	
5°	1082	104
15°	1091	308
25°	1012	464
35°	768	474
45°	370	288
55°	80	81
65°	11	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P202814

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1077.5
2.5°	1077.5
5°	1081.9
7.5°	1088.4
10°	1088.4
12.5°	1092.8
15°	1090.6
17.5°	1086.2
20°	1071.0
22.5°	1049.2
25°	1012.2
27.5°	970.9
30°	914.2
32.5°	846.8
35°	768.4
37.5°	681.4
40°	581.2
42.5°	476.8
45°	370.1
47.5°	274.2
50°	193.8
52.5°	130.6
55°	80.5
57.5°	47.9
60°	24.0
62.5°	15.2
65°	10.9
67.5°	8.8
70°	6.5
72.5°	4.4
75°	4.4
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)