

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219625

Luminaire Tested: **LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4244.8 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219625

CATALOG NUMBER: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219625

CATALOG NUMBER: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	96	89	84	80		87	82	78			84	80	77			82
4	92	83	76	71	90	82	76	71		79	74	70			77	73	69			75
5	86	76	69	64	84	75	68	63		73	67	63			71	66	62			69
6	80	69	62	57	79	69	62	57		67	61	56			65	60	56			64
7	75	64	56	51	73	63	56	51		62	55	51			60	55	50			59
8	70	59	51	46	69	58	51	46		57	50	46			56	50	46			54
9	66	54	47	42	64	53	47	42		52	46	42			51	46	42			50
10	61	50	43	38	60	49	43	38		48	42	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	51594	51594	51594
5°	99972	49167	16588
10°	169852	43020	7450
15°	261733	34318	11839
20°	378895	22332	20596
25°	555904	21549	26480
30°	646363	20419	20294
35°	654230	10812	10722
40°	541660	4080	4508
45°	409089	1388	1638
50°	279887	509	509
55°	38929	443	60
60°	1016	439	0
65°	255	601	0
70°	101	743	0
75°	0	981	0
80°	0	1686	198
85°	0	3359	0



TEST NUMBER: P1219625

CATALOG NUMBER: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	3.0
10°-20°	531.4	12.5
20°-30°	1212.3	28.6
30°-40°	1402.9	33.0
40°-50°	846.0	19.9
50°-60°	114.9	2.7
60°-70°	3.7	0.1
70°-80°	4.0	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1869.4	44.0
0°-40°	3272.3	77.1
0°-60°	4233.3	99.7
0°-90°	4244.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4244.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1198	1198	1198	1198	1198	
5°	2313	1894	1138	622	384	269
15°	5872	3301	770	237	266	1738
25°	11702	3911	454	546	557	5296
35°	12447	2982	206	210	204	7501
45°	6718	812	23	28	27	5253
55°	519	6	6	4	1	1017
65°	2	3	6	3	0	4
75°	0	4	6	4	0	0
85°	0	4	7	4	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1219625

CATALOG NUMBER: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3
2.5°	1733.0	1716.9	1723.6	1705.9	1661.3	1652.0	1651.2	1639.5	1601.4	1571.9	1536.5
5°	2313.1	2312.3	2316.5	2278.5	2200.2	2175.7	2163.9	2135.2	2043.3	1972.5	1894.0
7.5°	3037.6	3032.5	3027.4	2958.3	2835.1	2787.9	2757.6	2653.9	2527.4	2401.7	2261.8
10°	3885.0	3882.4	3863.1	3741.7	3544.3	3457.5	3398.4	3234.1	3030.8	2852.0	2614.1
12.5°	4869.2	4846.4	4811.8	4633.9	4363.2	4268.8	4138.9	3878.3	3566.3	3292.2	2959.9
15°	5871.8	5839.0	5777.4	5548.8	5213.2	5052.1	4891.1	4547.9	4124.6	3726.5	3300.8
17.5°	6852.6	6816.4	6672.1	6284.2	5956.2	5759.7	5581.0	5109.5	4612.0	4100.1	3560.4
20°	8269.4	8137.8	7886.4	7275.1	6665.4	6311.2	6102.1	5603.7	4988.0	4391.9	3745.0
22.5°	10161.7	9869.9	9334.4	8341.0	7469.9	6958.8	6616.5	5953.7	5258.8	4582.4	3858.9
25°	11701.6	11569.2	10960.4	9547.0	8187.5	7585.3	7108.9	6232.0	5456.2	4709.7	3911.1
27.5°	12694.0	12661.2	11965.5	10545.4	8773.6	7983.5	7451.4	6415.8	5551.3	4736.8	3885.9
30°	13001.0	13052.5	12384.5	10884.3	8943.1	8063.5	7481.7	6418.4	5478.0	4614.6	3724.0
32.5°	12978.3	12980.9	12162.0	10591.8	8667.4	7830.8	7228.7	6205.0	5207.3	4308.4	3416.2
35°	12447.0	12316.3	11390.4	9692.8	8025.7	7287.7	6727.8	5791.8	4761.2	3847.9	2981.9
37.5°	11280.7	11109.5	10030.1	8541.7	7265.9	6583.6	6131.5	5249.5	4229.9	3356.4	2533.2
40°	9637.2	9394.2	8503.8	7471.6	6434.3	5921.6	5542.2	4643.2	3661.5	2873.9	2112.4
42.5°	7991.9	7873.0	7284.4	6445.3	5735.2	5252.8	4856.6	4008.2	3115.1	2398.3	1580.4
45°	6718.5	6616.5	6221.0	5667.8	4971.2	4531.0	4149.0	3346.2	2420.3	1609.0	812.1
47.5°	5790.9	5708.2	5329.6	4748.5	3984.7	3503.0	3109.3	2194.2	1371.2	694.9	203.2
50°	4178.5	4094.3	3723.2	3050.2	2360.4	1957.3	1674.0	979.9	388.8	140.8	21.1
52.5°	2048.4	1979.2	1727.0	1292.7	867.8	624.0	456.2	183.9	44.6	15.2	10.1
55°	518.6	476.4	397.2	249.6	122.3	73.3	47.3	16.8	11.0	8.4	5.9
57.5°	29.4	28.7	26.2	19.3	14.2	12.7	11.0	8.4	5.9	5.1	4.2
60°	11.8	11.0	10.1	8.4	6.8	5.9	5.9	4.2	3.4	3.4	3.4
62.5°	5.1	5.1	5.1	4.2	3.4	3.4	3.4	2.5	3.4	3.4	3.4
65°	2.5	2.5	2.5	1.7	1.7	1.7	2.5	2.5	2.5	3.4	3.4
67.5°	1.7	0.8	0.8	0.8	1.7	1.7	1.7	2.5	2.5	3.4	3.4
70°	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.5	2.5	3.4	4.2
72.5°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.5	2.5	3.4	4.2
75°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.5	3.4	3.4	4.2
77.5°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.5	3.4	3.4	4.2
80°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.5	3.4	3.4	4.2
82.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.5	3.4	3.4	4.2
85°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.5	3.4	3.4	4.2
87.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.5	2.5	3.4	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219625

CATALOG NUMBER: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3
2.5°	1490.9	1460.6	1415.9	1386.4	1357.7	1330.8	1286.1	1260.7	1215.2	1173.0	1136.8
5°	1799.6	1723.6	1631.9	1553.3	1502.7	1453.1	1362.8	1296.2	1212.6	1137.6	1068.4
7.5°	2111.5	1977.6	1826.6	1697.6	1619.1	1542.4	1407.4	1299.6	1181.4	1074.3	972.3
10°	2394.9	2193.4	1980.1	1795.4	1689.1	1589.6	1411.7	1268.3	1116.4	984.0	856.0
12.5°	2658.0	2382.2	2103.9	1862.8	1731.2	1611.5	1394.0	1218.5	1038.0	881.3	732.0
15°	2892.4	2538.3	2194.2	1901.6	1747.3	1605.7	1352.6	1148.6	945.4	769.9	581.0
17.5°	3070.5	2635.3	2233.9	1895.7	1718.6	1560.9	1281.8	1060.8	846.7	634.1	420.8
20°	3178.3	2676.6	2225.5	1850.2	1657.1	1490.1	1197.5	965.6	727.8	487.4	371.1
22.5°	3224.0	2673.2	2185.8	1781.9	1581.1	1412.4	1116.4	872.8	603.0	441.1	387.1
25°	3231.6	2638.7	2130.1	1706.8	1506.1	1338.4	1034.8	767.4	523.7	453.6	433.5
27.5°	3173.2	2557.8	2025.6	1598.8	1400.7	1227.0	912.4	609.6	491.6	452.0	465.5
30°	3001.3	2373.1	1840.9	1409.2	1217.7	1044.1	651.9	478.2	408.2	410.7	414.1
32.5°	2698.5	2066.1	1544.1	1131.6	922.5	688.1	405.6	319.6	310.3	310.3	308.7
35°	2294.7	1690.7	1211.8	715.9	458.7	330.5	210.0	210.8	206.6	205.7	205.0
37.5°	1877.1	1334.1	767.4	296.0	199.1	138.3	124.0	125.6	124.0	126.5	124.8
40°	1480.0	823.9	280.0	94.4	70.0	67.5	69.2	70.8	70.8	72.6	72.6
42.5°	860.2	273.2	73.3	38.0	38.0	36.3	37.0	38.8	39.7	40.5	39.7
45°	255.5	56.5	23.6	21.1	21.1	20.3	20.3	21.1	21.8	22.8	22.8
47.5°	40.5	16.0	13.5	11.8	11.8	11.8	11.8	11.8	12.7	12.7	13.5
50°	12.7	10.1	8.4	7.6	7.6	6.8	6.8	7.6	7.6	7.6	8.4
52.5°	7.6	5.9	5.9	5.1	5.9	5.9	5.1	5.9	5.9	5.9	6.8
55°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.9	5.9	5.9
57.5°	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
60°	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.9
62.5°	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1	5.9	5.9	5.9
65°	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.9	5.9	5.9	5.9
67.5°	4.2	5.1	5.1	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9
70°	4.2	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
72.5°	4.2	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
75°	5.1	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.8
77.5°	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8
80°	5.1	5.1	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8
82.5°	5.1	5.1	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8
85°	5.1	5.1	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8
87.5°	5.1	5.1	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219625

CATALOG NUMBER: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3
2.5°	1105.6	1066.7	1048.2	1022.0	1003.5	962.2	945.4	916.7	893.0	854.3	856.8
5°	1009.4	936.0	886.3	847.5	820.5	754.7	710.8	664.6	622.3	570.1	550.7
7.5°	876.2	785.9	710.1	663.7	629.2	541.4	444.4	368.6	311.2	269.9	253.9
10°	743.0	625.8	505.1	433.5	383.8	299.4	256.3	236.1	217.6	194.8	179.7
12.5°	587.8	420.8	311.2	282.5	262.3	234.4	206.6	184.7	188.9	189.8	195.6
15°	401.4	302.7	268.2	248.9	226.8	210.8	220.2	226.0	236.9	237.8	245.4
17.5°	326.4	284.2	256.3	255.5	257.2	266.6	280.8	288.4	302.7	306.1	317.1
20°	326.4	301.9	325.4	325.4	329.8	342.4	361.0	371.9	387.9	393.8	407.3
22.5°	371.9	388.8	418.3	421.7	423.3	436.8	460.5	471.3	489.9	493.4	507.6
25°	453.6	468.8	495.9	498.4	499.2	509.3	527.0	532.9	545.6	538.9	547.4
27.5°	479.9	486.5	503.5	505.1	501.0	505.1	511.9	511.9	516.2	502.6	505.1
30°	421.7	423.3	431.8	432.5	423.3	424.9	425.9	424.9	424.2	409.8	409.8
32.5°	312.8	312.8	323.9	321.3	311.2	313.7	313.7	313.7	312.8	301.1	299.4
35°	207.5	208.2	217.6	215.8	208.2	210.0	210.0	212.6	210.0	203.2	201.6
37.5°	126.5	127.3	131.5	132.4	129.9	130.7	131.5	130.7	132.4	129.0	127.3
40°	73.3	75.1	78.4	79.2	78.4	78.4	79.2	80.2	83.4	79.2	77.6
42.5°	43.0	43.9	45.6	45.6	45.6	45.6	46.4	47.3	48.0	47.3	46.4
45°	24.4	25.3	26.2	26.2	26.9	26.2	26.9	26.9	27.8	26.9	26.9
47.5°	14.2	14.2	15.2	15.2	16.0	15.2	16.0	16.0	16.0	15.2	15.2
50°	8.4	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	8.4	8.4
52.5°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	5.9	5.9	5.1	5.1
55°	5.9	5.9	5.9	5.9	5.9	5.9	5.1	4.2	4.2	3.4	3.4
57.5°	5.1	5.9	5.9	5.9	5.9	5.1	5.1	4.2	3.4	2.5	2.5
60°	5.9	5.9	5.9	5.9	5.1	5.1	5.1	4.2	3.4	2.5	2.5
62.5°	5.9	5.9	5.9	5.9	5.9	5.1	5.1	4.2	3.4	2.5	2.5
65°	5.9	5.9	5.9	5.9	5.9	5.1	5.1	4.2	3.4	2.5	2.5
67.5°	5.9	5.9	5.9	5.9	5.9	5.1	5.1	4.2	3.4	3.4	2.5
70°	5.9	6.8	6.8	5.9	5.9	5.9	5.1	4.2	4.2	3.4	2.5
72.5°	5.9	6.8	6.8	5.9	5.9	5.9	5.1	4.2	4.2	3.4	2.5
75°	6.8	6.8	6.8	6.8	5.9	5.9	5.1	5.1	4.2	3.4	2.5
77.5°	6.8	6.8	6.8	6.8	5.9	5.9	5.1	5.1	4.2	3.4	2.5
80°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	5.1	4.2	3.4	3.4
82.5°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	5.1	4.2	3.4	3.4
85°	6.8	6.8	6.8	6.8	6.8	5.9	5.9	5.1	4.2	3.4	2.5
87.5°	6.8	6.8	6.8	6.8	5.9	5.9	5.1	5.1	4.2	3.4	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219625

CATALOG NUMBER: LDSQA6A45950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3
2.5°	825.6	806.2	797.7	811.2	804.5	784.3	788.5	775.8
5°	492.4	463.0	444.4	452.9	425.9	401.4	401.4	383.8
7.5°	237.8	228.5	223.4	225.2	219.2	211.6	207.5	207.5
10°	167.0	163.6	164.5	164.5	169.5	168.7	171.2	170.4
12.5°	198.1	199.9	200.6	204.0	208.2	208.2	210.8	209.1
15°	253.9	252.1	257.2	258.0	264.8	265.6	269.0	265.6
17.5°	322.9	326.4	331.4	330.5	344.0	345.0	345.0	344.0
20°	415.7	418.3	423.3	424.9	441.1	442.8	448.7	449.5
22.5°	516.9	516.9	519.4	522.8	538.0	538.9	541.4	541.4
25°	551.5	546.5	547.4	551.5	560.0	556.6	559.1	557.4
27.5°	506.8	499.2	497.5	503.5	509.3	500.0	503.5	503.5
30°	411.5	404.8	403.1	409.0	413.2	403.1	406.5	408.2
32.5°	301.1	296.9	296.0	300.1	303.6	295.2	298.5	301.1
35°	203.2	201.6	199.9	200.6	205.7	199.1	202.4	204.0
37.5°	129.0	125.6	126.5	128.2	131.5	127.3	130.7	130.7
40°	79.2	77.6	77.6	79.2	80.9	77.6	79.2	80.2
42.5°	46.4	46.4	46.4	47.3	48.0	46.4	46.4	47.3
45°	26.9	26.2	26.2	26.9	27.8	26.2	26.9	26.9
47.5°	15.2	14.2	14.2	15.2	15.2	14.2	15.2	15.2
50°	8.4	7.6	7.6	8.4	8.4	7.6	7.6	7.6
52.5°	4.2	4.2	4.2	4.2	4.2	4.2	3.4	3.4
55°	2.5	2.5	1.7	1.7	1.7	1.7	1.7	0.8
57.5°	1.7	1.7	0.8	0.8	0.8	0.8	0.0	0.0
60°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
62.5°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
65°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
67.5°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.5	1.7	1.7	0.8	0.8	0.8	0.0	0.0
72.5°	2.5	1.7	1.7	1.7	0.8	0.8	0.0	0.0
75°	2.5	1.7	1.7	1.7	0.8	0.8	0.0	0.0
77.5°	2.5	1.7	1.7	1.7	0.8	0.8	0.8	0.0
80°	2.5	1.7	1.7	1.7	0.8	0.8	0.8	0.8
82.5°	2.5	1.7	1.7	1.7	0.8	0.8	0.8	0.8
85°	2.5	1.7	1.7	1.7	0.8	0.8	0.8	0.0
87.5°	2.5	1.7	1.7	1.7	0.8	0.8	0.8	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)