

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P252775

Luminaire Tested: **LE_6B15D010 EC6B10209050 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209050 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2031.2 lumens
Efficiency: N/A
Efficacy: 141.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252775

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252775

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	97	91	87	101	95	90	86	91	87	84		88	85	82		85
3	96	87	81	76	94	86	80	75	83	78	74		81	76	72		78
4	90	80	72	67	88	78	72	66	76	70	66		74	69	65		72
5	84	73	65	60	82	72	65	60	70	64	59		68	63	58		66
6	78	67	60	54	77	66	59	54	65	58	54		63	57	53		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		53
9	65	54	46	42	64	53	46	42	52	46	41		51	45	41		50
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90893
5°	90055
10°	88075
15°	85279
20°	81841
25°	76822
30°	66474
35°	51761
40°	39338
45°	30669
50°	25435
55°	22840
60°	20773
65°	19173
70°	17625
75°	16334
80°	14728
85°	13474



TEST NUMBER: P252775

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	6.4
10°-20°	354.7	17.5
20°-30°	483.1	23.8
30°-40°	408.8	20.1
40°-50°	262.3	12.9
50°-60°	180.5	8.9
60°-70°	123.3	6.1
70°-80°	68.6	3.4
80°-90°	20.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	967.7	47.6
0°-40°	1376.5	67.8
0°-60°	1819.3	89.6
0°-90°	2031.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2031.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1393	
5°	1375	130
15°	1263	355
25°	1067	483
35°	650	409
45°	332	262
55°	201	181
65°	124	123
75°	65	69
85°	18	20
90°	0	



TEST NUMBER: P252775

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1393.2
2.5°	1387.9
5°	1375.1
7.5°	1355.0
10°	1329.5
12.5°	1297.6
15°	1262.6
17.5°	1222.2
20°	1178.8
22.5°	1129.9
25°	1067.2
27.5°	982.2
30°	882.4
32.5°	767.8
35°	649.9
37.5°	546.9
40°	461.9
42.5°	390.8
45°	332.4
47.5°	286.8
50°	250.6
52.5°	223.0
55°	200.8
57.5°	179.5
60°	159.2
62.5°	141.2
65°	124.2
67.5°	107.2
70°	92.4
72.5°	77.5
75°	64.8
77.5°	52.0
80°	39.2
82.5°	28.6
85°	18.0
87.5°	7.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)