

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219629

Luminaire Tested: **LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4877.2 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219629

CATALOG NUMBER: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219629

CATALOG NUMBER: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	66	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	53	49		59	53	49		57	52	48
8	69	57	49	44	67	56	49	44		55	49	44		54	48	44		53	47	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	43	39
10	60	48	41	36	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39357	39357	39357
5°	108020	36262	14799
10°	236712	29677	5640
15°	361579	22590	6615
20°	418927	16806	10277
25°	456990	13820	16585
30°	510319	12534	16933
35°	519221	8599	11611
40°	528340	4080	5873
45°	529200	1693	2563
50°	447391	737	790
55°	144065	510	128
60°	28615	586	0
65°	2924	693	0
70°	315	957	0
75°	0	1264	0
80°	0	2083	198
85°	0	4150	395

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P1219629

CATALOG NUMBER: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	2.5
10°-20°	641.7	13.2
20°-30°	1228.7	25.2
30°-40°	1447.6	29.7
40°-50°	1137.1	23.3
50°-60°	277.1	5.7
60°-70°	11.9	0.2
70°-80°	4.5	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1994.5	40.9
0°-40°	3442.2	70.6
0°-60°	4856.3	99.6
0°-90°	4877.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4877.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	914	914	914	914	914	
5°	2499	1809	839	439	342	330
15°	8112	4166	507	145	148	2265
25°	9620	5066	291	304	349	4484
35°	9878	3203	164	211	221	6194
45°	8691	990	28	39	42	6530
55°	1919	36	7	4	2	2284
65°	29	4	7	4	0	76
75°	0	4	8	5	0	0
85°	0	5	8	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219629

CATALOG NUMBER: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	1566.8	1563.3	1540.6	1561.7	1497.6	1495.0	1466.4	1453.7	1416.7	1381.2	1330.6
5°	2499.3	2444.5	2399.8	2401.6	2278.4	2255.7	2191.6	2126.6	2027.1	1934.4	1808.8
7.5°	3809.7	3744.7	3650.3	3610.8	3375.4	3306.3	3173.9	3001.1	2784.4	2568.5	2335.7
10°	5414.3	5424.5	5302.2	5189.2	4833.3	4693.4	4479.2	4138.6	3728.0	3322.4	2909.9
12.5°	7029.2	7022.4	6876.5	6705.4	6266.8	6069.5	5784.6	5359.5	4815.6	4186.6	3541.6
15°	8111.8	8159.8	8098.4	7961.7	7587.3	7361.3	7040.1	6463.3	5800.5	5036.6	4166.4
17.5°	8791.5	8837.0	8815.1	8708.0	8377.4	8136.3	7868.1	7396.0	6629.4	5669.0	4658.9
20°	9143.1	9214.8	9204.6	9088.2	8838.6	8638.9	8342.9	7905.2	7241.6	6108.3	4977.5
22.5°	9377.5	9432.4	9447.6	9315.9	9057.9	8868.2	8651.6	8208.0	7584.0	6376.4	5104.0
25°	9619.5	9716.5	9621.2	9459.3	9222.4	9040.2	8809.2	8384.2	7747.6	6486.2	5066.0
27.5°	9916.3	9962.8	9746.8	9599.3	9336.2	9138.9	8893.6	8486.2	7776.3	6398.4	4849.4
30°	10264.6	10072.4	9921.4	9628.8	9330.4	9138.1	8888.5	8422.2	7625.3	6107.5	4429.5
32.5°	10207.3	10031.0	9859.8	9550.3	9255.3	9064.7	8786.4	8208.8	7268.7	5621.0	3850.2
35°	9878.4	9916.3	9731.6	9475.3	9141.5	8944.9	8641.5	7905.2	6663.2	4949.8	3202.6
37.5°	9600.9	9684.5	9563.8	9326.9	8988.0	8722.4	8312.5	7417.8	5873.1	4098.1	2588.7
40°	9400.2	9427.3	9362.3	9096.7	8689.4	8305.8	7831.9	6542.5	4913.5	3216.9	2043.1
42.5°	9089.1	9160.8	9046.1	8756.1	8138.8	7704.5	7018.1	5531.6	3816.5	2457.2	1538.1
45°	8691.1	8759.4	8617.8	8135.4	7277.0	6640.4	5803.1	4313.1	2823.1	1811.3	990.0
47.5°	8041.9	8084.0	7810.0	7142.9	5894.9	5295.5	4437.1	3007.0	1818.9	1012.8	481.4
50°	6679.2	6659.0	6094.0	5273.5	3942.8	3313.9	2641.0	1630.0	817.1	479.8	301.1
52.5°	4304.7	4258.3	3699.3	2953.1	1996.7	1523.7	1145.0	703.2	425.8	268.1	118.9
55°	1919.2	1901.5	1556.6	1209.2	817.1	703.2	537.1	344.9	226.8	93.6	36.3
57.5°	711.7	695.7	613.1	514.3	394.6	328.0	260.5	165.3	58.1	31.2	19.3
60°	332.3	331.3	291.8	240.3	167.0	126.5	73.3	38.8	24.4	16.8	11.0
62.5°	106.2	103.7	72.6	53.1	38.0	32.9	26.2	19.3	12.7	9.3	6.8
65°	28.7	28.7	26.2	21.8	17.7	15.2	12.7	9.3	5.9	5.1	4.2
67.5°	11.0	11.0	10.1	9.3	6.8	5.9	5.1	4.2	3.4	4.2	4.2
70°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
72.5°	0.0	0.0	0.8	0.8	1.7	1.7	2.5	2.5	3.4	4.2	4.2
75°	0.0	0.0	0.8	0.8	1.7	1.7	2.5	2.5	3.4	4.2	4.2
77.5°	0.0	0.0	0.8	0.8	1.7	1.7	2.5	2.5	3.4	4.2	4.2
80°	0.0	0.0	0.8	0.8	1.7	1.7	2.5	2.5	3.4	4.2	4.2
82.5°	0.0	0.0	0.8	1.7	1.7	1.7	2.5	3.4	3.4	4.2	5.1
85°	0.0	0.0	0.8	1.7	1.7	2.5	2.5	3.4	3.4	4.2	5.1
87.5°	0.0	0.0	0.8	1.7	1.7	2.5	2.5	3.4	3.4	4.2	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219629

CATALOG NUMBER: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	1293.6	1237.9	1161.2	1116.4	1105.5	1081.9	1040.5	979.0	928.4	879.4	850.7
5°	1702.5	1570.9	1423.3	1319.7	1277.4	1221.0	1120.7	1016.9	921.6	839.0	774.2
7.5°	2136.0	1919.2	1680.5	1488.3	1419.2	1329.7	1166.2	1011.8	881.2	766.6	679.6
10°	2566.8	2217.7	1893.9	1615.6	1502.6	1381.2	1165.3	965.5	812.0	678.8	582.7
12.5°	2997.7	2496.0	2050.7	1692.4	1545.6	1392.1	1130.8	894.6	724.4	588.5	496.6
15°	3395.7	2717.7	2157.1	1718.5	1541.5	1360.1	1060.8	808.6	632.4	506.8	421.6
17.5°	3692.5	2834.1	2181.4	1678.9	1474.8	1274.2	953.7	707.5	544.6	434.3	347.5
20°	3838.3	2852.6	2123.3	1565.8	1360.1	1151.8	836.5	610.5	469.7	366.8	293.5
22.5°	3838.3	2764.9	1996.7	1424.3	1216.8	1011.1	723.4	530.4	410.7	319.6	258.0
25°	3692.5	2590.4	1827.3	1260.7	1059.1	871.8	625.7	470.6	365.1	290.9	239.5
27.5°	3409.2	2349.3	1609.7	1078.5	904.0	748.0	548.1	415.7	330.5	262.2	263.1
30°	3019.5	2053.3	1360.1	886.3	744.5	614.7	461.2	348.2	264.8	252.1	259.7
32.5°	2569.3	1699.2	1077.6	687.2	576.8	484.0	350.7	246.2	210.8	212.5	220.9
35°	2107.2	1337.3	811.2	509.3	429.2	350.7	230.3	161.9	160.2	163.6	169.5
37.5°	1663.7	1000.9	586.9	372.7	288.4	215.8	123.9	111.3	111.3	114.7	118.0
40°	1246.2	710.0	403.9	220.9	140.0	98.6	78.4	72.6	71.7	72.6	76.8
42.5°	855.9	449.5	240.3	88.5	67.5	57.4	49.8	45.6	44.6	45.6	48.0
45°	480.7	276.6	93.6	47.3	40.5	36.3	31.2	28.7	27.8	27.8	29.4
47.5°	301.1	109.6	42.1	29.4	25.3	23.6	20.3	18.6	17.7	17.7	18.6
50°	115.5	43.0	26.2	19.3	16.8	15.2	13.5	11.8	11.0	11.0	11.8
52.5°	39.7	25.3	16.8	12.7	11.0	10.1	8.4	7.6	7.6	7.6	7.6
55°	21.8	15.2	10.1	7.6	6.8	6.8	6.8	6.8	6.8	6.8	6.8
57.5°	13.5	9.3	6.8	5.9	5.9	5.9	5.9	5.9	5.9	6.8	6.8
60°	7.6	5.9	5.1	5.1	5.1	5.1	5.9	5.9	5.9	6.8	6.8
62.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.9	5.9	6.8	6.8	6.8
65°	4.2	4.2	4.2	5.1	5.1	5.1	5.9	5.9	6.8	6.8	6.8
67.5°	4.2	4.2	5.1	5.1	5.1	5.9	5.9	6.8	6.8	6.8	6.8
70°	4.2	5.1	5.1	5.9	5.9	5.9	6.8	6.8	6.8	7.6	7.6
72.5°	4.2	5.1	5.1	5.9	5.9	5.9	6.8	6.8	7.6	7.6	7.6
75°	5.1	5.1	5.1	5.9	5.9	5.9	6.8	7.6	7.6	7.6	7.6
77.5°	5.1	5.1	5.9	5.9	5.9	6.8	6.8	7.6	7.6	7.6	7.6
80°	5.1	5.1	5.9	5.9	6.8	6.8	7.6	7.6	7.6	8.4	8.4
82.5°	5.1	5.1	5.9	6.8	6.8	6.8	7.6	7.6	8.4	8.4	8.4
85°	5.1	5.9	5.9	6.8	6.8	6.8	7.6	7.6	8.4	8.4	8.4
87.5°	5.1	5.9	5.9	6.8	6.8	6.8	7.6	7.6	8.4	8.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219629

CATALOG NUMBER: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	812.9	777.4	742.0	715.8	703.2	690.6	662.8	626.5	611.3	589.4	576.8
5°	708.2	648.4	601.2	570.0	551.5	527.0	494.9	459.6	439.3	416.6	401.4
7.5°	600.4	530.4	484.8	456.1	437.6	407.3	366.8	324.7	300.1	274.9	257.2
10°	506.0	439.3	387.9	355.1	331.3	296.0	255.5	226.0	205.0	182.9	165.3
12.5°	422.4	350.7	296.0	268.1	252.1	218.4	184.7	151.8	139.0	134.9	134.9
15°	342.4	277.4	231.0	207.5	190.5	154.2	147.6	145.9	145.0	144.1	145.9
17.5°	279.1	224.3	175.3	163.6	161.9	161.1	161.9	161.9	162.8	165.3	169.5
20°	234.4	183.9	180.4	181.3	181.3	184.7	188.9	192.3	195.6	199.9	207.5
22.5°	208.2	207.5	213.3	214.1	218.4	223.4	231.0	236.1	244.5	248.7	259.7
25°	240.3	246.2	257.2	260.5	267.3	275.7	287.6	294.3	304.4	309.5	322.1
27.5°	272.4	281.6	295.0	299.4	305.2	318.8	327.2	333.0	338.1	341.5	349.1
30°	269.8	278.3	291.8	292.6	301.1	310.2	315.3	320.4	323.8	322.9	327.2
32.5°	228.5	236.1	248.7	248.7	258.0	265.6	268.1	272.4	272.4	272.4	274.1
35°	175.3	180.4	188.9	191.5	199.0	204.0	205.7	210.8	210.8	209.1	209.1
37.5°	121.4	128.2	134.1	135.8	140.8	144.1	148.4	149.3	147.6	148.4	148.4
40°	79.2	83.4	87.8	88.5	92.8	95.4	99.5	99.5	100.4	99.5	101.2
42.5°	48.9	52.2	54.9	56.5	58.1	59.9	62.4	63.2	64.1	63.2	65.0
45°	30.4	32.0	33.8	34.5	35.4	36.3	38.8	38.8	38.8	38.8	39.7
47.5°	18.6	19.3	20.3	20.3	21.1	21.8	22.8	22.8	22.8	22.8	23.6
50°	11.0	11.8	11.8	11.8	12.7	12.7	13.5	13.5	13.5	12.7	13.5
52.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	6.8	7.6
55°	6.8	6.8	5.9	5.9	5.9	5.9	5.9	5.1	4.2	4.2	3.4
57.5°	5.9	5.9	5.9	5.9	5.9	5.1	5.1	4.2	4.2	3.4	2.5
60°	5.9	5.9	5.9	5.9	5.9	5.1	5.1	4.2	3.4	3.4	2.5
62.5°	6.8	5.9	5.9	5.9	5.9	5.1	5.1	4.2	3.4	3.4	2.5
65°	6.8	6.8	5.9	5.9	5.9	5.1	5.1	4.2	4.2	3.4	2.5
67.5°	6.8	6.8	6.8	5.9	6.8	5.9	5.1	5.1	4.2	3.4	3.4
70°	7.6	6.8	6.8	6.8	6.8	5.9	5.9	5.1	4.2	3.4	3.4
72.5°	7.6	7.6	6.8	6.8	6.8	5.9	5.9	5.1	4.2	4.2	3.4
75°	7.6	7.6	6.8	6.8	6.8	5.9	5.9	5.1	5.1	4.2	3.4
77.5°	7.6	7.6	7.6	6.8	6.8	6.8	5.9	5.9	5.1	4.2	3.4
80°	7.6	7.6	7.6	7.6	7.6	6.8	6.8	5.9	5.1	4.2	3.4
82.5°	8.4	7.6	7.6	7.6	7.6	6.8	6.8	5.9	5.1	4.2	4.2
85°	8.4	8.4	7.6	7.6	7.6	6.8	6.8	5.9	5.1	5.1	4.2
87.5°	8.4	7.6	7.6	7.6	7.6	6.8	6.8	5.9	5.1	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219629

CATALOG NUMBER: LDSQA6A45950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	564.1	557.4	557.4	545.6	543.9	534.6	542.2	537.1
5°	384.5	373.6	370.1	358.3	354.1	343.1	346.5	342.4
7.5°	242.0	231.0	227.7	219.2	214.1	205.7	206.5	204.0
10°	147.6	137.4	134.9	132.4	129.9	129.0	129.9	129.0
12.5°	134.1	133.2	131.5	132.4	130.7	131.5	132.4	131.5
15°	145.9	147.6	145.9	146.6	145.9	147.6	148.4	148.4
17.5°	171.2	174.6	172.8	175.3	174.6	178.8	178.8	178.8
20°	210.0	215.8	214.1	217.6	217.6	222.7	222.7	224.3
22.5°	264.0	271.5	270.7	278.3	276.6	282.5	282.5	284.2
25°	328.8	336.4	337.3	342.4	341.5	347.5	347.5	349.1
27.5°	355.9	360.0	359.2	361.7	362.6	366.0	368.6	366.8
30°	333.9	337.3	336.4	338.1	338.1	340.6	343.1	340.6
32.5°	280.8	283.3	283.3	286.7	284.2	285.0	289.2	286.7
35°	215.1	216.7	215.1	216.7	217.6	217.6	221.7	220.9
37.5°	153.5	154.2	154.2	156.9	154.2	154.2	158.5	159.4
40°	102.9	103.7	102.9	106.2	104.5	104.5	107.1	104.5
42.5°	65.7	66.7	65.7	68.3	66.7	68.3	69.2	70.0
45°	40.5	40.5	39.7	41.3	40.5	41.3	42.1	42.1
47.5°	23.6	23.6	22.8	24.4	23.6	23.6	23.6	24.4
50°	12.7	12.7	12.7	13.5	12.7	12.7	12.7	11.8
52.5°	6.8	6.8	5.9	6.8	5.9	5.9	5.9	5.9
55°	3.4	2.5	2.5	2.5	1.7	1.7	1.7	1.7
57.5°	2.5	1.7	1.7	0.8	0.8	0.8	0.0	0.0
60°	1.7	1.7	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.7	1.7	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.7	1.7	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.5	1.7	1.7	0.8	0.8	0.0	0.0	0.0
70°	2.5	1.7	1.7	0.8	0.8	0.0	0.0	0.0
72.5°	2.5	1.7	1.7	1.7	0.8	0.8	0.0	0.0
75°	2.5	2.5	1.7	1.7	0.8	0.8	0.0	0.0
77.5°	3.4	2.5	1.7	1.7	0.8	0.8	0.0	0.0
80°	3.4	2.5	1.7	1.7	1.7	0.8	0.8	0.8
82.5°	3.4	2.5	2.5	1.7	1.7	0.8	0.8	0.8
85°	3.4	2.5	2.5	1.7	1.7	0.8	0.8	0.8
87.5°	3.4	2.5	2.5	1.7	1.7	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)