

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212596

Luminaire Tested: **LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4047.5 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212596

CATALOG NUMBER: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212596

CATALOG NUMBER: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	50		59
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	61	50	43	38	60	49	43	38	48	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	49195	49195	49195
5°	95331	46881	15810
10°	161956	41022	7100
15°	249568	32722	11286
20°	361277	21297	19638
25°	530056	20551	25250
30°	616314	19469	19350
35°	623813	10313	10228
40°	516469	3884	4288
45°	390067	1321	1565
50°	266879	482	482
55°	37120	428	60
60°	964	413	0
65°	245	581	0
70°	101	718	0
75°	0	948	0
80°	0	1612	198
85°	0	3211	0



TEST NUMBER: P1212596

CATALOG NUMBER: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.9	3.0
10°-20°	506.7	12.5
20°-30°	1155.9	28.6
30°-40°	1337.6	33.0
40°-50°	806.7	19.9
50°-60°	109.6	2.7
60°-70°	3.6	0.1
70°-80°	3.9	0.1
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1782.5	44.0
0°-40°	3120.1	77.1
0°-60°	4036.4	99.7
0°-90°	4047.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4047.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1143	1143	1143	1143	1143	
5°	2206	1806	1085	593	366	257
15°	5599	3147	734	226	253	1658
25°	11158	3729	433	520	532	5049
35°	11868	2843	196	200	195	7152
45°	6406	774	22	27	26	5009
55°	494	6	6	4	1	969
65°	2	3	6	3	0	4
75°	0	4	6	4	0	0
85°	0	4	6	4	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212596

CATALOG NUMBER: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6
2.5°	1652.4	1637.1	1643.5	1626.6	1584.0	1575.2	1574.4	1563.1	1526.9	1498.8	1465.1
5°	2205.7	2204.8	2208.8	2172.6	2097.8	2074.6	2063.2	2036.0	1948.3	1880.8	1806.0
7.5°	2896.3	2891.5	2886.6	2820.7	2703.4	2658.3	2629.4	2530.4	2409.8	2290.0	2156.6
10°	3704.4	3702.0	3683.5	3567.7	3379.5	3296.7	3240.4	3083.7	2889.8	2719.4	2492.6
12.5°	4642.8	4621.1	4588.1	4418.4	4160.3	4070.3	3946.4	3698.0	3400.5	3139.2	2822.3
15°	5598.9	5567.5	5508.8	5290.9	4970.9	4817.2	4663.7	4336.4	3932.8	3553.2	3147.2
17.5°	6534.0	6499.4	6361.9	5992.0	5679.2	5491.8	5321.4	4872.0	4397.5	3909.5	3394.9
20°	7884.9	7759.4	7519.8	6936.9	6355.5	6017.8	5818.3	5343.2	4756.1	4187.7	3570.9
22.5°	9689.2	9411.0	8900.4	7953.2	7122.6	6635.3	6308.9	5676.9	5014.3	4369.4	3679.5
25°	11157.5	11031.2	10450.7	9103.0	7806.9	7232.7	6778.4	5942.1	5202.4	4490.8	3729.4
27.5°	12103.8	12072.5	11409.2	10055.0	8365.7	7612.3	7104.9	6117.5	5293.2	4516.6	3705.2
30°	12396.6	12445.6	11808.7	10378.3	8527.3	7688.6	7133.8	6119.8	5223.3	4400.0	3550.9
32.5°	12374.9	12377.3	11596.4	10099.3	8264.4	7466.7	6892.6	5916.4	4965.2	4108.1	3257.4
35°	11868.3	11743.6	10860.7	9242.1	7652.4	6948.9	6415.0	5522.4	4539.8	3669.0	2843.2
37.5°	10756.2	10593.0	9563.8	8144.6	6928.0	6277.5	5846.5	5005.4	4033.2	3200.3	2415.5
40°	9189.0	8957.5	8108.4	7124.1	6135.2	5646.3	5284.4	4427.2	3491.4	2740.3	2014.3
42.5°	7620.3	7506.9	6945.7	6145.6	5468.6	5008.6	4630.7	3821.8	2970.3	2286.8	1506.9
45°	6406.1	6308.9	5931.7	5404.3	4740.1	4320.3	3956.1	3190.6	2307.7	1534.2	774.3
47.5°	5521.7	5442.9	5081.8	4527.8	3799.2	3340.1	2964.6	2092.3	1307.4	662.6	193.8
50°	3984.3	3903.8	3550.0	2908.3	2250.6	1866.3	1596.1	934.3	370.6	134.3	20.1
52.5°	1953.1	1887.2	1646.8	1232.6	827.4	595.1	435.1	175.3	42.6	14.5	9.7
55°	494.5	454.3	378.8	238.0	116.6	70.0	45.1	16.0	10.5	8.0	5.7
57.5°	28.1	27.4	24.9	18.5	13.7	12.0	10.5	8.0	5.7	4.8	4.0
60°	11.2	10.5	9.7	8.0	6.5	5.7	5.7	4.0	3.2	3.2	3.2
62.5°	4.8	4.8	4.8	4.0	3.2	3.2	3.2	2.4	3.2	3.2	3.2
65°	2.4	2.4	2.4	1.7	1.7	1.7	2.4	2.4	2.4	3.2	3.2
67.5°	1.7	0.8	0.8	0.8	1.7	1.7	1.7	2.4	2.4	3.2	3.2
70°	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.4	2.4	3.2	4.0
72.5°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.4	2.4	3.2	4.0
75°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.4	3.2	3.2	4.0
77.5°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.4	3.2	3.2	4.0
80°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.4	3.2	3.2	4.0
82.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.4	3.2	3.2	4.0
85°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.4	3.2	3.2	4.0
87.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.4	2.4	3.2	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212596

CATALOG NUMBER: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6
2.5°	1421.7	1392.6	1350.0	1322.0	1294.6	1268.9	1226.3	1202.1	1158.6	1118.5	1083.9
5°	1716.0	1643.5	1555.9	1481.1	1432.9	1385.4	1299.4	1235.9	1156.3	1084.7	1018.8
7.5°	2013.4	1885.5	1741.7	1618.6	1543.8	1470.6	1342.0	1239.1	1126.5	1024.4	927.1
10°	2283.7	2091.4	1888.0	1711.9	1610.6	1515.7	1346.0	1209.4	1064.6	938.3	816.1
12.5°	2534.5	2271.5	2006.2	1776.3	1650.8	1536.6	1329.2	1161.9	989.8	840.3	698.0
15°	2758.0	2420.3	2092.3	1813.2	1666.0	1530.9	1289.7	1095.2	901.4	734.1	554.0
17.5°	2927.7	2512.8	2130.0	1807.5	1638.7	1488.3	1222.2	1011.5	807.4	604.6	401.2
20°	3030.6	2552.1	2122.0	1764.1	1580.0	1420.8	1141.8	920.6	694.0	464.8	353.8
22.5°	3074.0	2548.9	2084.2	1699.1	1507.7	1346.9	1064.6	832.3	574.9	420.6	369.1
25°	3081.2	2516.0	2031.1	1627.5	1436.1	1276.1	986.6	731.7	499.4	432.6	413.4
27.5°	3025.8	2438.8	1931.4	1524.6	1335.5	1170.0	870.0	581.4	468.8	430.9	443.8
30°	2861.7	2262.6	1755.4	1343.7	1161.1	995.4	621.5	456.0	389.2	391.6	394.8
32.5°	2573.1	1970.0	1472.3	1079.1	879.7	656.1	386.8	304.8	295.9	295.9	294.3
35°	2188.0	1612.2	1155.5	682.6	437.4	315.2	200.2	201.1	196.9	196.2	195.4
37.5°	1789.9	1272.0	731.7	282.3	189.7	131.9	118.2	119.8	118.2	120.6	119.1
40°	1411.2	785.6	266.9	90.0	66.8	64.3	66.0	67.5	67.5	69.1	69.1
42.5°	820.2	260.5	70.0	36.2	36.2	34.6	35.4	36.9	37.8	38.6	37.8
45°	243.7	53.9	22.5	20.1	20.1	19.4	19.4	20.1	20.9	21.7	21.7
47.5°	38.6	15.2	12.9	11.2	11.2	11.2	11.2	11.2	12.0	12.0	12.9
50°	12.0	9.7	8.0	7.2	7.2	6.5	6.5	7.2	7.2	7.2	8.0
52.5°	7.2	5.7	5.7	4.8	5.7	5.7	4.8	5.7	5.7	5.7	6.5
55°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	5.7	5.7	5.7
57.5°	4.0	4.0	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
60°	4.0	4.0	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	5.7
62.5°	4.0	4.0	4.8	4.8	4.8	4.8	4.8	4.8	5.7	5.7	5.7
65°	4.0	4.0	4.8	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7
67.5°	4.0	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7
70°	4.0	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
72.5°	4.0	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
75°	4.8	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7	5.7	6.5
77.5°	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7	6.5	6.5	6.5
80°	4.8	4.8	5.7	5.7	5.7	5.7	5.7	6.5	6.5	6.5	6.5
82.5°	4.8	4.8	5.7	5.7	5.7	5.7	5.7	6.5	6.5	6.5	6.5
85°	4.8	4.8	5.7	5.7	5.7	5.7	5.7	6.5	6.5	6.5	6.5
87.5°	4.8	4.8	5.7	5.7	5.7	5.7	5.7	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212596

CATALOG NUMBER: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6
2.5°	1054.2	1017.2	999.5	974.6	956.9	917.4	901.4	874.0	851.5	814.6	816.9
5°	962.5	892.6	845.1	808.1	782.3	719.7	677.8	633.7	593.4	543.5	525.1
7.5°	835.4	749.4	677.1	632.8	599.8	516.2	423.7	351.4	296.7	257.4	242.0
10°	708.4	596.6	481.7	413.4	365.8	285.4	244.5	225.1	207.4	185.7	171.2
12.5°	560.5	401.2	296.7	269.4	250.0	223.5	196.9	176.1	180.1	180.9	186.6
15°	382.8	288.6	255.7	237.2	216.3	201.1	209.9	215.5	226.0	226.8	234.0
17.5°	311.2	270.9	244.5	243.7	245.2	254.1	267.7	274.9	288.6	291.9	302.3
20°	311.2	287.9	310.3	310.3	314.4	326.5	344.2	354.6	369.9	375.5	388.3
22.5°	354.6	370.6	398.8	402.0	403.7	416.5	439.1	449.5	467.2	470.3	484.0
25°	432.6	447.1	472.8	475.2	476.0	485.7	502.6	508.2	520.3	513.8	521.8
27.5°	457.5	464.0	480.0	481.7	477.7	481.7	488.0	488.0	492.1	479.2	481.7
30°	402.0	403.7	411.7	412.5	403.7	405.2	406.0	405.2	404.5	390.8	390.8
32.5°	298.3	298.3	308.8	306.3	296.7	299.1	299.1	299.1	298.3	287.1	285.4
35°	197.8	198.6	207.4	205.8	198.6	200.2	200.2	202.6	200.2	193.8	192.2
37.5°	120.6	121.4	125.4	126.3	123.8	124.6	125.4	124.6	126.3	123.1	121.4
40°	70.0	71.5	74.8	75.6	74.8	74.8	75.6	76.3	79.6	75.6	74.0
42.5°	41.1	41.8	43.4	43.4	43.4	43.4	44.2	45.1	45.8	45.1	44.2
45°	23.4	24.1	24.9	24.9	25.7	24.9	25.7	25.7	26.6	25.7	25.7
47.5°	13.7	13.7	14.5	14.5	15.2	14.5	15.2	15.2	15.2	14.5	14.5
50°	8.0	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.0	8.0
52.5°	6.5	6.5	6.5	6.5	6.5	5.7	5.7	5.7	5.7	4.8	4.8
55°	5.7	5.7	5.7	5.7	5.7	5.7	4.8	4.0	4.0	3.2	3.2
57.5°	4.8	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	2.4	2.4
60°	5.7	5.7	5.7	5.7	4.8	4.8	4.8	4.0	3.2	2.4	2.4
62.5°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	2.4	2.4
65°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	2.4	2.4
67.5°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.0	3.2	3.2	2.4
70°	5.7	6.5	6.5	5.7	5.7	5.7	4.8	4.0	4.0	3.2	2.4
72.5°	5.7	6.5	6.5	5.7	5.7	5.7	4.8	4.0	4.0	3.2	2.4
75°	6.5	6.5	6.5	6.5	5.7	5.7	4.8	4.8	4.0	3.2	2.4
77.5°	6.5	6.5	6.5	6.5	5.7	5.7	4.8	4.8	4.0	3.2	2.4
80°	6.5	6.5	6.5	6.5	6.5	5.7	5.7	4.8	4.0	3.2	3.2
82.5°	6.5	6.5	6.5	6.5	6.5	5.7	5.7	4.8	4.0	3.2	3.2
85°	6.5	6.5	6.5	6.5	6.5	5.7	5.7	4.8	4.0	3.2	2.4
87.5°	6.5	6.5	6.5	6.5	5.7	5.7	4.8	4.8	4.0	3.2	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212596

CATALOG NUMBER: LDSQA6A50930D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6	1142.6
2.5°	787.2	768.7	760.6	773.5	767.1	747.8	751.8	739.7
5°	469.6	441.4	423.7	431.8	406.0	382.8	382.8	365.8
7.5°	226.8	217.9	213.1	214.6	209.1	201.8	197.8	197.8
10°	159.2	156.0	156.8	156.8	161.7	160.8	163.2	162.4
12.5°	188.9	190.6	191.4	194.6	198.6	198.6	201.1	199.4
15°	242.0	240.4	245.2	246.0	252.5	253.2	256.5	253.2
17.5°	308.0	311.2	316.0	315.2	328.0	328.9	328.9	328.0
20°	396.4	398.8	403.7	405.2	420.6	422.1	427.8	428.6
22.5°	492.9	492.9	495.4	498.6	513.1	513.8	516.2	516.2
25°	525.9	521.1	521.8	525.9	533.9	530.6	533.1	531.5
27.5°	483.2	476.0	474.4	480.0	485.7	476.8	480.0	480.0
30°	392.3	386.0	384.3	390.0	394.0	384.3	387.5	389.2
32.5°	287.1	283.1	282.3	286.3	289.5	281.4	284.6	287.1
35°	193.8	192.2	190.6	191.4	196.2	189.7	192.9	194.6
37.5°	123.1	119.8	120.6	122.2	125.4	121.4	124.6	124.6
40°	75.6	74.0	74.0	75.6	77.2	74.0	75.6	76.3
42.5°	44.2	44.2	44.2	45.1	45.8	44.2	44.2	45.1
45°	25.7	24.9	24.9	25.7	26.6	24.9	25.7	25.7
47.5°	14.5	13.7	13.7	14.5	14.5	13.7	14.5	14.5
50°	8.0	7.2	7.2	8.0	8.0	7.2	7.2	7.2
52.5°	4.0	4.0	4.0	4.0	4.0	4.0	3.2	3.2
55°	2.4	2.4	1.7	1.7	1.7	1.7	1.7	0.8
57.5°	1.7	1.7	0.8	0.8	0.8	0.8	0.0	0.0
60°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
62.5°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
65°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
67.5°	1.7	1.7	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.4	1.7	1.7	0.8	0.8	0.8	0.0	0.0
72.5°	2.4	1.7	1.7	1.7	0.8	0.8	0.0	0.0
75°	2.4	1.7	1.7	1.7	0.8	0.8	0.0	0.0
77.5°	2.4	1.7	1.7	1.7	0.8	0.8	0.8	0.0
80°	2.4	1.7	1.7	1.7	0.8	0.8	0.8	0.8
82.5°	2.4	1.7	1.7	1.7	0.8	0.8	0.8	0.8
85°	2.4	1.7	1.7	1.7	0.8	0.8	0.8	0.0
87.5°	2.4	1.7	1.7	1.7	0.8	0.8	0.8	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)