

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212602

Luminaire Tested: **LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4320.4 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212602

CATALOG NUMBER: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212602

CATALOG NUMBER: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52511	52511	52511
5°	101762	50045	16882
10°	172881	43794	7577
15°	266404	34929	12048
20°	385648	22731	20962
25°	565814	21934	26951
30°	657892	20781	20657
35°	665899	11006	10917
40°	551317	4154	4581
45°	416383	1407	1674
50°	284884	516	516
55°	39627	450	60
60°	1033	448	0
65°	265	611	0
70°	101	755	0
75°	0	998	0
80°	0	1686	198
85°	0	3359	0

TEST NUMBER: P1212602

CATALOG NUMBER: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	3.0
10°-20°	540.9	12.5
20°-30°	1233.9	28.6
30°-40°	1427.9	33.0
40°-50°	861.1	19.9
50°-60°	117.0	2.7
60°-70°	3.8	0.1
70°-80°	4.1	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1902.7	44.0
0°-40°	3330.6	77.1
0°-60°	4308.7	99.7
0°-90°	4320.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4320.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1220	1220	1220	1220	1220	
5°	2354	1928	1158	633	391	274
15°	5977	3360	784	241	270	1769
25°	11910	3981	462	555	567	5390
35°	12669	3035	209	214	208	7635
45°	6838	827	23	28	28	5347
55°	528	6	6	4	1	1035
65°	3	3	6	3	0	4
75°	0	4	6	4	0	0
85°	0	4	7	4	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212602

CATALOG NUMBER: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6
2.5°	1763.9	1747.6	1754.4	1736.4	1690.9	1681.5	1680.6	1668.6	1629.9	1600.0	1563.9
5°	2354.5	2353.5	2357.9	2319.2	2239.4	2214.5	2202.5	2173.3	2079.8	2007.7	1927.8
7.5°	3091.7	3086.5	3081.5	3011.0	2885.7	2837.7	2806.7	2701.1	2572.4	2444.5	2302.1
10°	3954.3	3951.7	3932.0	3808.4	3607.6	3519.1	3459.1	3291.7	3084.9	2902.9	2660.8
12.5°	4956.0	4932.9	4897.6	4716.6	4441.0	4344.9	4212.7	3947.5	3629.9	3351.0	3012.8
15°	5976.6	5943.1	5880.4	5647.8	5306.2	5142.3	4978.3	4629.0	4198.1	3793.0	3359.5
17.5°	6974.9	6937.9	6791.1	6396.3	6062.4	5862.4	5680.4	5200.6	4694.3	4173.2	3623.9
20°	8416.8	8282.9	8027.1	7404.9	6784.3	6423.8	6210.9	5703.6	5077.1	4470.2	3811.9
22.5°	10342.9	10045.9	9500.9	8489.7	7603.1	7083.0	6734.5	6059.8	5352.6	4664.2	3927.7
25°	11910.2	11775.5	11155.7	9717.2	8333.5	7720.7	7235.8	6343.1	5553.4	4793.8	3981.0
27.5°	12920.5	12887.0	12178.9	10733.4	8930.1	8125.8	7584.2	6530.2	5650.4	4821.2	3955.2
30°	13232.9	13285.3	12605.5	11078.5	9102.6	8207.4	7615.1	6532.7	5575.7	4696.8	3790.4
32.5°	13209.7	13212.3	12378.9	10780.6	8821.9	7970.4	7357.7	6315.6	5300.2	4385.2	3477.1
35°	12669.0	12536.0	11593.5	9865.6	8168.8	7417.7	6847.8	5895.0	4846.1	3916.5	3035.1
37.5°	11481.9	11307.7	10209.0	8694.0	7395.4	6701.0	6240.9	5343.2	4305.3	3416.2	2578.4
40°	9809.0	9561.8	8655.4	7604.9	6549.1	6027.2	5641.0	4726.0	3726.9	2925.2	2150.1
42.5°	8134.4	8013.4	7414.3	6560.2	5837.5	5346.6	4943.1	4079.6	3170.7	2441.1	1608.5
45°	6838.3	6734.5	6331.9	5768.9	5059.8	4611.8	4223.0	3405.8	2463.4	1637.7	826.6
47.5°	5894.2	5810.1	5424.7	4833.3	4055.7	3565.5	3164.6	2233.4	1395.7	707.3	206.9
50°	4253.1	4167.2	3789.6	3104.6	2402.5	1992.2	1703.8	997.3	395.7	143.4	21.5
52.5°	2084.9	2014.5	1757.8	1315.8	883.2	635.2	464.3	187.1	45.5	15.5	10.3
55°	527.9	485.0	404.3	254.1	124.5	74.7	48.0	17.1	11.2	8.6	6.0
57.5°	30.1	29.1	26.6	19.7	14.6	12.9	11.2	8.6	6.0	5.2	4.2
60°	12.0	11.2	10.3	8.6	6.8	6.0	6.0	4.2	3.4	3.4	3.4
62.5°	5.2	5.2	5.2	4.2	3.4	3.4	3.4	2.6	3.4	3.4	3.4
65°	2.6	2.6	2.6	1.8	1.8	1.8	2.6	2.6	2.6	3.4	3.4
67.5°	1.8	0.8	0.8	0.8	1.8	1.8	1.8	2.6	2.6	3.4	3.4
70°	0.8	0.8	0.8	0.8	1.8	1.8	1.8	2.6	2.6	3.4	4.2
72.5°	0.0	0.8	0.8	0.8	1.8	1.8	1.8	2.6	2.6	3.4	4.2
75°	0.0	0.8	0.8	0.8	1.8	1.8	1.8	2.6	3.4	3.4	4.2
77.5°	0.0	0.8	0.8	0.8	1.8	1.8	1.8	2.6	3.4	3.4	4.2
80°	0.0	0.8	0.8	0.8	1.8	1.8	1.8	2.6	3.4	3.4	4.2
82.5°	0.0	0.0	0.8	0.8	1.8	1.8	1.8	2.6	3.4	3.4	4.2
85°	0.0	0.0	0.8	0.8	1.8	1.8	1.8	2.6	3.4	3.4	4.2
87.5°	0.0	0.0	0.8	0.8	1.8	1.8	1.8	2.6	2.6	3.4	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212602

CATALOG NUMBER: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6
2.5°	1517.5	1486.7	1441.1	1411.0	1381.9	1354.4	1309.0	1283.2	1236.9	1193.9	1157.0
5°	1831.7	1754.4	1660.8	1581.1	1529.5	1478.9	1387.1	1319.2	1234.3	1157.9	1087.5
7.5°	2149.3	2012.8	1859.1	1727.9	1648.0	1569.9	1432.5	1322.7	1202.5	1093.5	989.7
10°	2437.6	2232.6	2015.3	1827.3	1719.3	1617.9	1436.9	1290.9	1136.5	1001.7	871.2
12.5°	2705.5	2424.8	2141.6	1896.0	1762.2	1640.3	1418.8	1240.3	1056.6	896.9	745.1
15°	2944.1	2583.6	2233.4	1935.6	1778.5	1634.3	1376.7	1169.0	962.2	783.6	591.4
17.5°	3125.2	2682.3	2273.7	1929.5	1749.2	1588.8	1304.6	1079.8	861.8	645.5	428.3
20°	3235.1	2724.4	2265.1	1883.2	1686.6	1516.7	1218.8	982.8	740.7	496.1	377.7
22.5°	3281.3	2721.0	2224.8	1813.7	1609.4	1437.7	1136.5	888.4	613.7	448.9	394.0
25°	3289.1	2685.7	2168.1	1737.3	1532.9	1362.2	1053.1	781.0	533.0	461.7	441.2
27.5°	3229.9	2603.3	2061.7	1627.5	1425.7	1248.9	928.7	620.6	500.4	460.1	473.8
30°	3054.8	2415.3	1873.7	1434.3	1239.5	1062.6	663.5	486.6	415.5	418.0	421.5
32.5°	2746.7	2102.9	1571.6	1151.9	939.0	700.4	412.9	325.3	315.9	315.9	314.1
35°	2335.6	1720.9	1233.5	728.8	466.9	336.4	213.7	214.5	210.3	209.4	208.6
37.5°	1910.7	1357.8	781.0	301.3	202.6	140.8	126.1	127.9	126.1	128.7	127.1
40°	1506.4	838.6	285.0	96.2	71.3	68.7	70.3	72.1	72.1	73.9	73.9
42.5°	875.4	278.1	74.7	38.6	38.6	36.9	37.8	39.5	40.4	41.2	40.4
45°	260.1	57.5	24.1	21.5	21.5	20.6	20.6	21.5	22.3	23.1	23.1
47.5°	41.2	16.3	13.7	12.0	12.0	12.0	12.0	12.0	12.9	12.9	13.7
50°	12.9	10.3	8.6	7.7	7.7	6.8	6.8	7.7	7.7	7.7	8.6
52.5°	7.7	6.0	6.0	5.2	6.0	6.0	5.2	6.0	6.0	6.0	6.8
55°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0
57.5°	4.2	4.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
60°	4.2	4.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.0
62.5°	4.2	4.2	5.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0
65°	4.2	4.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0
67.5°	4.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.0
70°	4.2	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
72.5°	4.2	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
75°	5.2	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.8
77.5°	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.0	6.8	6.8	6.8
80°	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8
82.5°	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8
85°	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8
87.5°	5.2	5.2	6.0	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212602

CATALOG NUMBER: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6
2.5°	1125.2	1085.8	1067.0	1040.3	1021.4	979.4	962.2	933.0	909.0	869.5	872.0
5°	1027.4	952.7	902.1	862.6	835.2	768.2	723.6	676.4	633.4	580.2	560.5
7.5°	891.8	799.9	722.8	675.6	640.3	551.1	452.3	375.1	316.7	274.7	258.3
10°	756.1	636.8	514.1	441.2	390.6	304.7	260.9	240.4	221.5	198.2	182.8
12.5°	598.3	428.3	316.7	287.6	266.9	238.6	210.3	188.0	192.2	193.2	199.2
15°	408.5	308.1	272.9	253.2	230.9	214.5	224.1	230.0	241.2	242.0	249.8
17.5°	332.2	289.2	260.9	260.1	261.8	271.3	285.8	293.6	308.1	311.5	322.7
20°	332.2	307.3	331.3	331.3	335.6	348.5	367.3	378.5	394.8	400.8	414.5
22.5°	378.5	395.7	425.7	429.2	430.9	444.6	468.7	479.8	498.7	502.1	516.7
25°	461.7	477.2	504.7	507.3	508.1	518.4	536.4	542.4	555.3	548.5	557.1
27.5°	488.4	495.2	512.5	514.1	509.9	514.1	521.0	521.0	525.3	511.5	514.1
30°	429.2	430.9	439.4	440.4	430.9	432.6	433.4	432.6	431.8	417.1	417.1
32.5°	318.5	318.5	329.6	327.0	316.7	319.3	319.3	319.3	318.5	306.4	304.7
35°	211.1	212.0	221.5	219.7	212.0	213.7	213.7	216.3	213.7	206.9	205.1
37.5°	128.7	129.6	133.9	134.8	132.2	133.0	133.9	133.0	134.8	131.3	129.6
40°	74.7	76.3	79.8	80.7	79.8	79.8	80.7	81.5	85.0	80.7	78.9
42.5°	43.8	44.6	46.4	46.4	46.4	46.4	47.2	48.0	49.0	48.0	47.2
45°	24.9	25.7	26.6	26.6	27.5	26.6	27.5	27.5	28.3	27.5	27.5
47.5°	14.6	14.6	15.5	15.5	16.3	15.5	16.3	16.3	16.3	15.5	15.5
50°	8.6	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	8.6	8.6
52.5°	6.8	6.8	6.8	6.8	6.8	6.0	6.0	6.0	6.0	5.2	5.2
55°	6.0	6.0	6.0	6.0	6.0	6.0	5.2	4.2	4.2	3.4	3.4
57.5°	5.2	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	2.6	2.6
60°	6.0	6.0	6.0	6.0	5.2	5.2	5.2	4.2	3.4	2.6	2.6
62.5°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	2.6	2.6
65°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	2.6	2.6
67.5°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	3.4	2.6
70°	6.0	6.8	6.8	6.0	6.0	6.0	5.2	4.2	4.2	3.4	2.6
72.5°	6.0	6.8	6.8	6.0	6.0	6.0	5.2	4.2	4.2	3.4	2.6
75°	6.8	6.8	6.8	6.8	6.0	6.0	5.2	5.2	4.2	3.4	2.6
77.5°	6.8	6.8	6.8	6.8	6.0	6.0	5.2	5.2	4.2	3.4	2.6
80°	6.8	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.2	3.4	3.4
82.5°	6.8	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.2	3.4	3.4
85°	6.8	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.2	3.4	2.6
87.5°	6.8	6.8	6.8	6.8	6.0	6.0	5.2	5.2	4.2	3.4	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212602

CATALOG NUMBER: LDSQA6A50935D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6	1219.6
2.5°	840.3	820.6	812.0	825.8	818.8	798.3	802.5	789.7
5°	501.3	471.2	452.3	460.9	433.4	408.5	408.5	390.6
7.5°	242.0	232.6	227.5	229.2	223.1	215.5	211.1	211.1
10°	169.9	166.5	167.3	167.3	172.5	171.7	174.3	173.3
12.5°	201.7	203.4	204.3	207.7	212.0	212.0	214.5	212.9
15°	258.3	256.6	261.8	262.7	269.5	270.3	273.8	270.3
17.5°	328.7	332.2	337.4	336.4	350.2	351.0	351.0	350.2
20°	423.1	425.7	430.9	432.6	448.9	450.6	456.7	457.5
22.5°	526.2	526.2	528.8	532.2	547.6	548.5	551.1	551.1
25°	561.3	556.3	557.1	561.3	569.9	566.5	569.1	567.3
27.5°	515.9	508.1	506.5	512.5	518.4	508.9	512.5	512.5
30°	418.9	412.1	410.3	416.3	420.6	410.3	413.7	415.5
32.5°	306.4	302.1	301.3	305.6	309.0	300.4	303.8	306.4
35°	206.9	205.1	203.4	204.3	209.4	202.6	206.0	207.7
37.5°	131.3	127.9	128.7	130.5	133.9	129.6	133.0	133.0
40°	80.7	78.9	78.9	80.7	82.4	78.9	80.7	81.5
42.5°	47.2	47.2	47.2	48.0	49.0	47.2	47.2	48.0
45°	27.5	26.6	26.6	27.5	28.3	26.6	27.5	27.5
47.5°	15.5	14.6	14.6	15.5	15.5	14.6	15.5	15.5
50°	8.6	7.7	7.7	8.6	8.6	7.7	7.7	7.7
52.5°	4.2	4.2	4.2	4.2	4.2	4.2	3.4	3.4
55°	2.6	2.6	1.8	1.8	1.8	1.8	1.8	0.8
57.5°	1.8	1.8	0.8	0.8	0.8	0.8	0.0	0.0
60°	1.8	1.8	0.8	0.8	0.8	0.0	0.0	0.0
62.5°	1.8	1.8	0.8	0.8	0.8	0.0	0.0	0.0
65°	1.8	1.8	0.8	0.8	0.8	0.0	0.0	0.0
67.5°	1.8	1.8	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.6	1.8	1.8	0.8	0.8	0.8	0.0	0.0
72.5°	2.6	1.8	1.8	1.8	0.8	0.8	0.0	0.0
75°	2.6	1.8	1.8	1.8	0.8	0.8	0.0	0.0
77.5°	2.6	1.8	1.8	1.8	0.8	0.8	0.8	0.0
80°	2.6	1.8	1.8	1.8	0.8	0.8	0.8	0.8
82.5°	2.6	1.8	1.8	1.8	0.8	0.8	0.8	0.8
85°	2.6	1.8	1.8	1.8	0.8	0.8	0.8	0.0
87.5°	2.6	1.8	1.8	1.8	0.8	0.8	0.8	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)