

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212604

Luminaire Tested: **LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4720.3 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212604

CATALOG NUMBER: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212604

CATALOG NUMBER: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36662	36662	36662
5°	94038	33349	10390
10°	183313	25629	4988
15°	329067	17411	6695
20°	488567	13214	11052
25°	555324	10889	17326
30°	601981	11902	16302
35°	634083	7716	10102
40°	647793	3423	4924
45°	585085	1309	1833
50°	385144	516	516
55°	105467	450	0
60°	21063	517	0
65°	1487	693	0
70°	227	856	0
75°	0	1281	0
80°	0	1909	198
85°	0	3804	395

TEST NUMBER: P1212604

CATALOG NUMBER: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.3	2.2
10°-20°	554.1	11.7
20°-30°	1255.9	26.6
30°-40°	1507.5	31.9
40°-50°	1062.5	22.5
50°-60°	219.2	4.6
60°-70°	7.7	0.2
70°-80°	4.6	0.1
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1914.3	40.6
0°-40°	3421.8	72.5
0°-60°	4703.5	99.6
0°-90°	4720.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4720.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	852	852	852	852	852	
5°	2176	1585	772	321	240	268
15°	7382	3248	391	139	150	2191
25°	11689	3929	229	321	365	5395
35°	12064	2751	147	192	192	7500
45°	9609	943	22	29	30	7067
55°	1405	19	6	4	0	1852
65°	15	4	7	4	0	43
75°	0	4	8	5	0	0
85°	0	5	8	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212604

CATALOG NUMBER: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5
2.5°	1451.4	1407.6	1424.8	1374.2	1363.0	1353.6	1363.0	1308.0	1277.2	1237.7	1206.0
5°	2175.8	2123.5	2135.4	2047.1	2006.7	1979.3	1974.1	1860.9	1775.9	1682.3	1585.3
7.5°	3029.1	2979.3	2972.4	2835.1	2751.8	2704.6	2684.9	2522.6	2375.8	2209.3	2027.4
10°	4192.9	4079.6	4044.4	3845.3	3686.4	3586.0	3462.5	3203.2	2945.8	2694.3	2462.5
12.5°	5547.3	5485.6	5398.0	5047.0	4768.9	4626.3	4441.8	4036.7	3647.0	3231.5	2843.6
15°	7382.4	7162.7	7013.3	6506.0	6058.0	5838.3	5568.8	4949.0	4360.2	3834.2	3247.8
17.5°	9175.4	9060.4	8827.0	8168.7	7478.5	7131.8	6730.1	5888.1	5056.4	4307.9	3592.0
20°	10663.0	10554.7	10288.7	9668.1	8902.5	8391.0	7885.4	6730.1	5643.5	4685.5	3822.1
22.5°	11375.3	11306.6	11089.5	10558.2	9905.9	9419.2	8875.8	7446.7	6077.7	4932.8	3926.8
25°	11689.4	11657.7	11517.7	11099.0	10484.4	10071.5	9558.2	7954.0	6348.2	5047.8	3928.6
27.5°	12007.9	12013.9	11704.9	11373.5	10790.7	10394.3	9899.8	8178.9	6397.0	4983.4	3799.8
30°	12108.3	12044.8	11908.3	11432.8	10879.2	10457.8	9927.3	8075.1	6196.2	4719.1	3543.2
32.5°	12067.2	12042.3	11892.0	11389.0	10729.0	10264.7	9662.1	7663.0	5799.7	4341.3	3179.3
35°	12063.7	12017.4	11673.2	11241.4	10428.6	9855.2	9061.3	6997.0	5238.4	3843.6	2750.9
37.5°	11845.7	11730.6	11472.3	10890.3	9819.1	9092.1	8202.1	6183.3	4551.6	3284.8	2326.0
40°	11525.5	11371.1	11031.1	10150.5	8763.5	7925.7	7057.1	5258.9	3824.7	2733.7	1874.5
42.5°	10856.9	10623.4	10142.8	8931.7	7356.7	6601.4	5878.6	4322.5	3119.1	2227.4	1430.9
45°	9608.9	9289.6	8639.8	7310.3	5943.0	5326.8	4745.6	3477.9	2496.9	1652.2	943.3
47.5°	7723.2	7427.0	6835.6	5819.4	4660.6	4139.7	3676.2	2587.0	1692.6	957.0	450.6
50°	5749.9	5495.8	5034.0	4044.4	3128.5	2719.2	2322.6	1469.5	793.1	454.9	187.1
52.5°	3430.7	3304.6	2895.1	2242.8	1545.0	1331.3	1068.6	622.3	400.0	164.8	50.6
55°	1405.0	1296.9	1143.3	917.6	672.0	569.9	487.6	307.3	124.5	34.3	18.9
57.5°	635.2	611.1	541.6	425.7	309.0	259.2	175.1	58.4	27.5	17.1	11.2
60°	244.6	220.5	188.8	102.2	43.8	36.9	30.1	19.7	13.7	9.4	6.8
62.5°	35.2	33.5	30.1	24.1	18.9	17.1	14.6	10.3	7.7	6.0	5.2
65°	14.6	14.6	12.9	10.3	8.6	7.7	6.8	5.2	4.2	4.2	4.2
67.5°	6.0	6.0	5.2	4.2	3.4	3.4	3.4	2.6	3.4	3.4	4.2
70°	1.8	1.8	1.8	1.8	1.8	1.8	2.6	2.6	3.4	3.4	4.2
72.5°	0.0	0.0	0.8	0.8	1.8	1.8	1.8	2.6	3.4	4.2	4.2
75°	0.0	0.0	0.8	0.8	1.8	1.8	1.8	2.6	3.4	4.2	4.2
77.5°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	4.2
80°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	5.2
82.5°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	5.2
85°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	5.2
87.5°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.4	4.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212604

CATALOG NUMBER: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5
2.5°	1178.5	1123.6	1108.1	1060.0	1019.6	999.9	975.0	919.2	877.2	821.4	787.9
5°	1517.5	1413.6	1331.3	1230.9	1164.8	1121.8	1054.9	952.7	870.4	771.6	701.3
7.5°	1884.0	1694.4	1545.8	1380.1	1284.9	1210.2	1096.1	949.3	828.2	696.9	588.0
10°	2237.6	1954.4	1720.9	1483.1	1357.8	1254.0	1096.9	912.4	751.9	586.2	471.2
12.5°	2549.2	2183.6	1854.8	1549.2	1393.9	1264.3	1067.8	846.3	652.3	482.4	381.1
15°	2809.2	2361.3	1949.2	1574.1	1396.5	1242.0	1006.8	751.9	541.6	390.6	319.3
17.5°	3006.6	2454.8	1978.4	1544.1	1346.7	1178.5	913.2	632.6	439.4	331.3	268.7
20°	3108.8	2472.8	1936.4	1462.6	1254.8	1082.3	790.5	513.3	372.5	288.4	224.9
22.5°	3121.7	2422.2	1836.0	1345.8	1138.9	965.6	654.9	428.3	332.2	254.9	198.2
25°	3045.3	2312.3	1692.6	1213.6	1012.0	831.7	533.0	383.6	302.1	229.2	228.3
27.5°	2882.3	2123.5	1520.9	1060.0	858.3	676.4	452.3	346.8	269.5	243.0	258.3
30°	2652.2	1881.4	1309.8	866.0	670.4	520.1	381.1	285.8	236.9	239.4	252.4
32.5°	2340.6	1581.1	1061.8	634.2	479.8	391.4	285.8	194.8	196.6	197.4	208.6
35°	1949.2	1267.8	793.1	426.6	337.4	275.5	161.3	143.4	146.0	146.8	154.5
37.5°	1562.1	974.2	527.0	284.1	212.0	145.0	100.4	96.2	97.8	97.0	105.6
40°	1196.5	679.0	315.9	140.8	81.5	67.8	61.8	59.2	60.1	60.9	66.1
42.5°	847.1	368.3	156.2	53.2	43.0	39.5	36.9	35.2	36.1	36.1	39.5
45°	430.0	174.3	53.2	29.1	26.6	24.1	22.3	21.5	21.5	21.5	23.1
47.5°	186.2	57.5	24.9	18.1	16.3	15.5	13.7	12.9	12.9	12.9	13.7
50°	58.4	23.1	15.5	12.0	10.3	9.4	8.6	8.6	8.6	7.7	8.6
52.5°	21.5	14.6	10.3	7.7	6.8	6.8	6.8	6.0	6.8	6.0	6.8
55°	12.9	9.4	6.8	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
57.5°	8.6	6.8	6.0	6.0	5.2	5.2	6.0	6.0	6.0	6.0	6.0
60°	6.0	6.0	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0	6.0
62.5°	5.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.0	6.0	6.8
65°	4.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0	6.8	6.8	6.8
67.5°	4.2	5.2	5.2	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8
70°	5.2	5.2	6.0	6.0	6.0	6.0	6.8	6.8	6.8	6.8	7.7
72.5°	5.2	5.2	6.0	6.0	6.0	6.0	6.8	6.8	7.7	7.7	7.7
75°	5.2	6.0	6.0	6.0	6.0	6.8	6.8	6.8	7.7	7.7	7.7
77.5°	5.2	6.0	6.0	6.8	6.8	6.8	6.8	7.7	7.7	7.7	7.7
80°	5.2	6.0	6.0	6.8	6.8	6.8	7.7	7.7	7.7	7.7	8.6
82.5°	5.2	6.0	6.0	6.8	6.8	6.8	7.7	7.7	7.7	7.7	8.6
85°	6.0	6.0	6.8	6.8	6.8	6.8	7.7	7.7	7.7	7.7	8.6
87.5°	6.0	6.0	6.8	6.8	6.8	6.8	7.7	7.7	8.6	7.7	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212604

CATALOG NUMBER: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5
2.5°	743.3	693.5	659.1	646.3	621.4	582.0	558.7	537.3	497.0	488.4	466.1
5°	620.6	540.8	484.0	462.7	434.4	400.8	368.3	346.8	321.0	310.7	295.2
7.5°	489.2	409.5	360.5	343.4	323.6	296.1	266.9	245.4	218.9	205.1	192.2
10°	384.6	325.3	284.1	266.9	246.4	217.1	187.1	158.8	135.6	121.1	118.5
12.5°	312.5	263.5	219.7	201.7	177.7	148.4	127.1	126.1	124.5	123.5	125.3
15°	255.8	208.6	162.2	142.4	135.6	134.8	137.4	139.9	139.0	141.6	143.4
17.5°	210.3	159.7	149.4	150.2	151.0	153.6	157.9	164.8	165.7	169.9	173.3
20°	171.7	169.1	173.3	176.8	179.4	184.6	194.0	202.6	205.1	211.1	218.1
22.5°	194.8	202.6	212.0	216.3	219.7	229.2	239.4	253.2	258.3	266.1	275.5
25°	235.2	248.0	262.7	267.7	272.9	288.4	300.4	316.7	321.0	330.4	339.8
27.5°	268.7	282.4	297.8	304.7	309.0	324.5	334.8	345.0	345.0	350.2	357.1
30°	263.5	274.7	287.6	292.6	294.4	305.6	315.9	319.3	317.5	320.1	325.3
32.5°	218.9	227.5	237.8	242.0	243.8	251.5	260.1	260.1	259.2	259.2	262.7
35°	162.2	168.3	173.3	177.7	180.3	185.4	193.2	192.2	192.2	190.6	193.2
37.5°	109.0	112.5	118.5	120.1	121.1	124.5	130.5	130.5	128.7	129.6	131.3
40°	66.1	70.3	73.9	74.7	76.3	78.9	83.3	83.3	83.3	83.3	84.1
42.5°	39.5	42.0	44.6	44.6	45.5	49.0	50.6	50.6	50.6	50.6	51.4
45°	23.1	24.1	25.7	26.6	26.6	28.3	29.1	29.1	29.1	29.1	30.1
47.5°	13.7	14.6	14.6	15.5	15.5	16.3	17.1	17.1	16.3	16.3	16.3
50°	8.6	8.6	8.6	8.6	9.4	9.4	9.4	9.4	9.4	9.4	8.6
52.5°	6.8	6.8	6.8	6.8	6.0	6.0	6.0	6.0	5.2	5.2	4.2
55°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	5.2	4.2	3.4	2.6
57.5°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	3.4	2.6
60°	6.0	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	3.4	2.6
62.5°	6.8	6.8	6.0	6.0	6.0	5.2	5.2	4.2	4.2	3.4	2.6
65°	6.8	6.8	6.0	6.0	6.0	6.0	5.2	5.2	4.2	3.4	2.6
67.5°	6.8	6.8	6.8	6.8	6.0	6.0	6.0	5.2	4.2	3.4	2.6
70°	7.7	7.7	6.8	6.8	6.8	6.0	6.0	5.2	4.2	4.2	3.4
72.5°	7.7	7.7	6.8	6.8	6.8	6.8	6.0	5.2	5.2	4.2	3.4
75°	7.7	7.7	7.7	7.7	6.8	6.8	6.0	6.0	5.2	4.2	3.4
77.5°	7.7	7.7	7.7	7.7	6.8	6.8	6.8	6.0	5.2	4.2	3.4
80°	7.7	7.7	7.7	7.7	7.7	6.8	6.8	6.0	5.2	4.2	3.4
82.5°	8.6	8.6	7.7	7.7	7.7	6.8	6.8	6.0	5.2	4.2	4.2
85°	8.6	8.6	7.7	7.7	7.7	6.8	6.8	6.0	5.2	5.2	4.2
87.5°	8.6	8.6	7.7	7.7	7.7	6.8	6.8	6.0	5.2	5.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212604

CATALOG NUMBER: LDSQA6A50935D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	851.5	851.5	851.5	851.5	851.5	851.5	851.5	851.5
2.5°	452.3	426.6	418.0	424.0	417.1	411.9	405.1	401.7
5°	283.2	264.3	258.3	260.1	254.1	248.9	242.0	240.4
7.5°	174.3	156.2	149.4	149.4	142.4	136.5	132.2	129.6
10°	116.7	113.3	114.1	115.0	114.1	115.0	112.5	114.1
12.5°	125.3	123.5	125.3	126.1	126.1	127.9	124.5	127.1
15°	146.0	144.2	146.8	148.4	148.4	151.0	147.6	150.2
17.5°	178.5	177.7	182.0	183.7	184.6	188.8	184.6	188.0
20°	225.7	224.9	230.9	233.5	232.6	241.2	235.2	241.2
22.5°	286.6	285.0	293.6	296.1	297.0	308.1	303.0	307.3
25°	347.6	349.3	353.6	357.9	358.7	368.3	360.5	364.7
27.5°	360.5	357.9	360.5	365.7	366.5	370.8	363.9	367.3
30°	326.2	321.9	322.7	328.7	330.4	332.2	326.2	327.9
32.5°	265.3	258.3	258.3	264.3	266.1	268.7	258.3	262.7
35°	195.6	189.7	189.7	194.0	194.8	196.6	188.8	192.2
37.5°	133.9	128.7	130.5	132.2	133.0	134.8	133.9	133.0
40°	85.8	82.4	85.0	85.0	85.8	86.7	86.7	87.6
42.5°	52.4	49.8	51.4	51.4	52.4	52.4	52.4	53.2
45°	30.1	29.1	29.1	30.1	30.1	30.1	29.1	30.1
47.5°	16.3	15.5	16.3	16.3	16.3	16.3	16.3	16.3
50°	8.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7
52.5°	4.2	3.4	3.4	3.4	2.6	3.4	2.6	2.6
55°	2.6	1.8	1.8	1.8	0.8	0.8	0.0	0.0
57.5°	1.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0
60°	1.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.8	0.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.6	1.8	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.6	1.8	1.8	0.8	0.8	0.0	0.0	0.0
72.5°	2.6	1.8	1.8	1.8	0.8	0.8	0.0	0.0
75°	2.6	1.8	1.8	1.8	0.8	0.8	0.0	0.0
77.5°	2.6	2.6	1.8	1.8	0.8	0.8	0.8	0.0
80°	3.4	2.6	1.8	1.8	1.8	0.8	0.8	0.8
82.5°	3.4	2.6	1.8	1.8	1.8	0.8	0.8	0.8
85°	3.4	2.6	2.6	1.8	1.8	0.8	0.8	0.8
87.5°	3.4	2.6	2.6	1.8	1.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)