

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203438

Luminaire Tested: **LE_6B15D010 EC6B10209050 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209050 6LBMB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 695.1 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203438

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBMB1

Luminous Intensity Polar Plot






TEST NUMBER: P203438

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	106	111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	96	106	102	98	95		99	96	93			96	93	91			93
3	103	97	92	88	101	95	91	87		93	89	86			90	87	85			88
4	98	91	85	81	96	90	85	81		87	83	80			85	82	79			84
5	93	85	79	75	92	84	79	75		82	78	74			81	77	74			79
6	89	80	74	70	87	79	74	70		78	73	69			76	72	69			75
7	84	75	69	65	83	75	69	65		73	68	65			72	68	65			71
8	80	71	65	61	79	71	65	61		69	64	61			68	64	61			67
9	77	67	61	58	76	67	61	57		66	61	57			65	60	57			64
10	73	64	58	54	72	63	58	54		62	57	54			62	57	54			61

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203438

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.4	11.4
10°-20°	195.9	28.2
20°-30°	236.0	33.9
30°-40°	149.3	21.5
40°-50°	34.2	4.9
50°-60°	0.4	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.3	73.6
0°-40°	660.6	95.0
0°-60°	695.1	100.0
0°-90°	695.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	875	
5°	855	79
15°	699	196
25°	523	236
35°	235	149
45°	38	34
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203438

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	875.1
2.5°	871.5
5°	855.4
7.5°	824.8
10°	787.0
12.5°	742.1
15°	699.0
17.5°	657.6
20°	614.5
22.5°	571.4
25°	522.9
27.5°	465.4
30°	395.4
32.5°	316.2
35°	235.4
37.5°	167.1
40°	113.2
42.5°	70.1
45°	37.8
47.5°	16.1
50°	3.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)