

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212612

Luminaire Tested: **LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5076.8 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212612

CATALOG NUMBER: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212612

CATALOG NUMBER: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	100	98			99	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	88	83	78		86	81	77			83	79	76			81
4	91	82	75	70	89	80	74	69		78	73	68			76	71	67			74
5	85	74	67	62	83	73	66	61		71	65	61			70	64	60			68
6	79	68	60	55	77	67	60	55		65	59	54			64	58	54			62
7	74	62	55	49	72	61	54	49		60	53	49			59	53	49			57
8	69	57	49	44	67	56	49	44		55	49	44			54	48	44			53
9	64	52	45	40	63	52	45	40		51	44	40			50	44	40			49
10	60	48	41	36	59	48	41	36		47	41	36			46	40	36			45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40963	40963	40963
5°	112446	37744	15404
10°	246401	30892	5872
15°	376378	23518	6887
20°	436072	17494	10699
25°	475694	14385	17264
30°	531210	13046	17629
35°	540477	8951	12089
40°	549968	4243	6115
45°	550859	1760	2673
50°	465704	764	824
55°	149958	533	135
60°	29786	611	0
65°	3046	723	0
70°	327	995	0
75°	0	1314	0
80°	0	2157	198
85°	0	4298	395

TEST NUMBER: P1212612

CATALOG NUMBER: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	2.5
10°-20°	668.0	13.2
20°-30°	1279.0	25.2
30°-40°	1506.9	29.7
40°-50°	1183.6	23.3
50°-60°	288.4	5.7
60°-70°	12.4	0.2
70°-80°	4.7	0.1
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2076.2	40.9
0°-40°	3583.1	70.6
0°-60°	5055.1	99.6
0°-90°	5076.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5076.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	951	951	951	951	951	
5°	2602	1883	873	457	356	344
15°	8444	4337	528	151	154	2357
25°	10013	5273	303	317	363	4667
35°	10283	3334	170	220	230	6448
45°	9047	1030	29	40	44	6797
55°	1998	38	7	4	2	2378
65°	30	4	7	4	0	79
75°	0	4	8	5	0	0
85°	0	5	9	5	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212612

CATALOG NUMBER: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4
2.5°	1630.9	1627.3	1603.6	1625.6	1558.9	1556.2	1526.4	1513.2	1474.6	1437.7	1385.1
5°	2601.7	2544.6	2498.1	2499.8	2371.7	2348.0	2281.3	2213.7	2110.1	2013.6	1882.8
7.5°	3965.6	3898.0	3799.7	3758.5	3513.6	3441.6	3303.8	3123.9	2898.3	2673.6	2431.4
10°	5635.9	5646.5	5519.2	5401.6	5031.2	4885.6	4662.5	4307.9	3880.5	3458.3	3029.1
12.5°	7316.8	7309.9	7158.0	6979.8	6523.4	6318.0	6021.3	5578.9	5012.8	4358.0	3686.6
15°	8443.8	8493.9	8429.8	8287.6	7897.9	7662.7	7328.3	6727.9	6037.9	5242.7	4337.0
17.5°	9151.4	9198.7	9175.9	9064.4	8720.3	8469.3	8190.1	7698.7	6900.8	5901.1	4849.6
20°	9517.3	9592.0	9581.4	9460.3	9200.5	8992.4	8684.3	8228.8	7538.1	6358.3	5181.3
22.5°	9761.3	9818.4	9834.2	9697.2	9428.7	9231.1	9005.6	8543.9	7894.4	6637.5	5313.0
25°	10013.2	10114.3	10015.0	9846.5	9599.9	9410.3	9169.8	8727.4	8064.7	6751.6	5273.4
27.5°	10322.2	10370.5	10145.8	9992.2	9718.4	9512.9	9257.6	8833.6	8094.6	6660.3	5047.9
30°	10684.8	10484.7	10327.5	10022.9	9712.2	9512.1	9252.3	8766.9	7937.4	6357.5	4610.7
32.5°	10625.1	10441.6	10263.4	9941.3	9634.1	9435.8	9146.1	8544.9	7566.2	5851.0	4007.8
35°	10282.8	10322.2	10129.9	9863.1	9515.6	9311.0	8995.1	8228.8	6935.9	5152.4	3333.6
37.5°	9993.9	10080.9	9955.3	9708.7	9355.9	9079.4	8652.7	7721.4	6113.5	4265.8	2694.6
40°	9785.0	9813.1	9745.5	9469.0	9045.1	8645.7	8152.5	6810.4	5114.6	3348.6	2126.7
42.5°	9461.1	9535.8	9416.4	9114.4	8471.9	8019.9	7305.4	5757.9	3972.7	2557.8	1601.0
45°	9046.8	9118.0	8970.5	8468.4	7574.9	6912.2	6040.7	4489.7	2938.7	1885.4	1030.5
47.5°	8371.0	8414.9	8129.6	7435.3	6136.2	5512.3	4618.6	3130.1	1893.3	1054.2	501.1
50°	6952.6	6931.6	6343.4	5489.4	4104.3	3449.5	2749.0	1696.7	850.5	499.4	313.4
52.5°	4480.8	4432.6	3850.7	3073.9	2078.5	1586.0	1191.9	732.1	443.2	279.1	123.8
55°	1997.7	1979.3	1620.3	1258.7	850.5	732.1	559.1	359.0	236.1	97.5	37.8
57.5°	740.8	724.2	638.1	535.4	410.8	341.5	271.2	172.0	60.5	32.4	20.2
60°	345.9	344.9	303.7	250.2	173.8	131.7	76.3	40.4	25.5	17.6	11.4
62.5°	110.6	108.0	75.5	55.3	39.5	34.2	27.3	20.2	13.2	9.7	7.1
65°	29.9	29.9	27.3	22.8	18.4	15.8	13.2	9.7	6.1	5.3	4.4
67.5°	11.4	11.4	10.5	9.7	7.1	6.1	5.3	4.4	3.5	4.4	4.4
70°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	3.5	3.5	4.4
72.5°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.5	4.4	4.4
75°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.5	4.4	4.4
77.5°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.5	4.4	4.4
80°	0.0	0.0	0.8	0.8	1.8	1.8	2.6	2.6	3.5	4.4	4.4
82.5°	0.0	0.0	0.8	1.8	1.8	1.8	2.6	3.5	3.5	4.4	5.3
85°	0.0	0.0	0.8	1.8	1.8	2.6	2.6	3.5	3.5	4.4	5.3
87.5°	0.0	0.0	0.8	1.8	1.8	2.6	2.6	3.5	3.5	4.4	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212612

CATALOG NUMBER: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4
2.5°	1346.5	1288.6	1208.7	1162.2	1150.7	1126.2	1083.1	1019.0	966.4	915.4	885.6
5°	1772.1	1635.2	1481.6	1373.6	1329.7	1271.0	1166.5	1058.6	959.3	873.3	805.8
7.5°	2223.4	1997.7	1749.4	1549.2	1477.2	1384.1	1213.9	1053.3	917.2	797.9	707.4
10°	2671.9	2308.4	1971.4	1681.7	1564.1	1437.7	1213.0	1005.0	845.2	706.6	606.5
12.5°	3120.4	2598.1	2134.6	1761.6	1608.9	1449.2	1177.0	931.3	754.0	612.7	517.0
15°	3534.7	2828.9	2245.3	1788.9	1604.6	1415.8	1104.2	841.7	658.3	527.6	438.8
17.5°	3843.6	2950.1	2270.7	1747.6	1535.2	1326.3	992.7	736.4	567.0	452.1	361.7
20°	3995.5	2969.4	2210.1	1629.9	1415.8	1199.0	870.7	635.4	488.9	381.8	305.5
22.5°	3995.5	2878.1	2078.5	1482.6	1266.6	1052.4	753.1	552.1	427.5	332.6	268.6
25°	3843.6	2696.4	1902.0	1312.3	1102.5	907.5	651.2	489.8	380.1	302.8	249.3
27.5°	3548.7	2445.4	1675.6	1122.7	940.9	778.6	570.5	432.7	344.1	272.9	273.9
30°	3143.2	2137.3	1415.8	922.5	775.0	639.9	480.1	362.5	275.6	262.4	270.3
32.5°	2674.5	1768.7	1121.7	715.3	600.4	503.9	365.1	256.3	219.5	221.1	230.0
35°	2193.5	1392.0	844.4	530.2	446.7	365.1	239.7	168.5	166.7	170.3	176.4
37.5°	1731.8	1041.8	610.9	388.0	300.2	224.7	129.0	115.9	115.9	119.4	122.8
40°	1297.3	739.0	420.4	230.0	145.7	102.7	81.7	75.5	74.6	75.5	79.9
42.5°	890.9	467.9	250.2	92.2	70.2	59.7	51.8	47.4	46.5	47.4	50.0
45°	500.3	287.9	97.5	49.2	42.1	37.8	32.4	29.9	28.9	28.9	30.7
47.5°	313.4	114.1	43.9	30.7	26.3	24.5	21.1	19.4	18.4	18.4	19.4
50°	120.2	44.7	27.3	20.2	17.6	15.8	14.0	12.3	11.4	11.4	12.3
52.5°	41.3	26.3	17.6	13.2	11.4	10.5	8.7	7.9	7.9	7.9	7.9
55°	22.8	15.8	10.5	7.9	7.1	7.1	7.1	7.1	7.1	7.1	7.1
57.5°	14.0	9.7	7.1	6.1	6.1	6.1	6.1	6.1	6.1	7.1	7.1
60°	7.9	6.1	5.3	5.3	5.3	5.3	6.1	6.1	6.1	7.1	7.1
62.5°	5.3	5.3	5.3	5.3	5.3	5.3	6.1	6.1	7.1	7.1	7.1
65°	4.4	4.4	4.4	5.3	5.3	5.3	6.1	6.1	7.1	7.1	7.1
67.5°	4.4	4.4	5.3	5.3	5.3	6.1	6.1	7.1	7.1	7.1	7.1
70°	4.4	5.3	5.3	6.1	6.1	6.1	7.1	7.1	7.1	7.9	7.9
72.5°	4.4	5.3	5.3	6.1	6.1	6.1	7.1	7.1	7.9	7.9	7.9
75°	5.3	5.3	5.3	6.1	6.1	6.1	7.1	7.9	7.9	7.9	7.9
77.5°	5.3	5.3	6.1	6.1	6.1	7.1	7.1	7.9	7.9	7.9	7.9
80°	5.3	5.3	6.1	6.1	7.1	7.1	7.9	7.9	7.9	8.7	8.7
82.5°	5.3	5.3	6.1	7.1	7.1	7.1	7.9	7.9	8.7	8.7	8.7
85°	5.3	6.1	6.1	7.1	7.1	7.1	7.9	7.9	8.7	8.7	8.7
87.5°	5.3	6.1	6.1	7.1	7.1	7.1	7.9	7.9	8.7	8.7	8.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212612

CATALOG NUMBER: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4
2.5°	846.2	809.2	772.4	745.2	732.1	718.9	689.9	652.2	636.4	613.5	600.4
5°	737.3	675.0	625.9	593.3	574.1	548.6	515.2	478.4	457.2	433.6	417.8
7.5°	624.9	552.1	504.7	474.8	455.6	424.0	381.8	338.0	312.5	286.2	267.7
10°	526.6	457.2	403.8	369.6	344.9	308.1	266.0	235.3	213.3	190.5	172.0
12.5°	439.8	365.1	308.1	279.1	262.4	227.4	192.2	158.0	144.8	140.4	140.4
15°	356.4	288.7	240.5	215.9	198.4	160.6	153.6	151.9	150.9	150.1	151.9
17.5°	290.5	233.5	182.5	170.3	168.5	167.7	168.5	168.5	169.4	172.0	176.4
20°	244.0	191.4	187.9	188.7	188.7	192.2	196.6	200.1	203.7	208.0	215.9
22.5°	216.8	215.9	222.1	222.9	227.4	232.6	240.5	245.8	254.5	258.9	270.3
25°	250.2	256.3	267.7	271.2	278.2	287.0	299.4	306.3	316.8	322.1	335.2
27.5°	283.6	293.1	307.2	311.6	317.8	331.8	340.5	346.7	352.0	355.5	363.4
30°	280.8	289.7	303.7	304.6	313.4	323.0	328.3	333.6	337.0	336.2	340.5
32.5°	237.9	245.8	258.9	258.9	268.6	276.5	279.1	283.6	283.6	283.6	285.3
35°	182.5	187.9	196.6	199.3	207.1	212.4	214.2	219.5	219.5	217.7	217.7
37.5°	126.4	133.5	139.6	141.4	146.6	150.1	154.5	155.4	153.6	154.5	154.5
40°	82.5	86.8	91.3	92.2	96.5	99.2	103.6	103.6	104.4	103.6	105.4
42.5°	50.9	54.4	57.1	58.8	60.5	62.3	64.9	65.8	66.7	65.8	67.6
45°	31.6	33.4	35.2	36.0	36.8	37.8	40.4	40.4	40.4	40.4	41.3
47.5°	19.4	20.2	21.1	21.1	21.9	22.8	23.7	23.7	23.7	23.7	24.5
50°	11.4	12.3	12.3	12.3	13.2	13.2	14.0	14.0	14.0	13.2	14.0
52.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.1	7.9
55°	7.1	7.1	6.1	6.1	6.1	6.1	6.1	5.3	4.4	4.4	3.5
57.5°	6.1	6.1	6.1	6.1	6.1	5.3	5.3	4.4	4.4	3.5	2.6
60°	6.1	6.1	6.1	6.1	6.1	5.3	5.3	4.4	3.5	3.5	2.6
62.5°	7.1	6.1	6.1	6.1	6.1	5.3	5.3	4.4	3.5	3.5	2.6
65°	7.1	7.1	6.1	6.1	6.1	5.3	5.3	4.4	4.4	3.5	2.6
67.5°	7.1	7.1	7.1	6.1	7.1	6.1	5.3	5.3	4.4	3.5	3.5
70°	7.9	7.1	7.1	7.1	7.1	6.1	6.1	5.3	4.4	3.5	3.5
72.5°	7.9	7.9	7.1	7.1	7.1	6.1	6.1	5.3	4.4	4.4	3.5
75°	7.9	7.9	7.1	7.1	7.1	6.1	6.1	5.3	5.3	4.4	3.5
77.5°	7.9	7.9	7.9	7.1	7.1	7.1	6.1	6.1	5.3	4.4	3.5
80°	7.9	7.9	7.9	7.9	7.9	7.1	7.1	6.1	5.3	4.4	3.5
82.5°	8.7	7.9	7.9	7.9	7.9	7.1	7.1	6.1	5.3	4.4	4.4
85°	8.7	8.7	7.9	7.9	7.9	7.1	7.1	6.1	5.3	5.3	4.4
87.5°	8.7	7.9	7.9	7.9	7.9	7.1	7.1	6.1	5.3	4.4	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212612

CATALOG NUMBER: LDSQA6A50940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4
2.5°	587.2	580.2	580.2	567.9	566.2	556.5	564.4	559.1
5°	400.3	388.8	385.3	373.0	368.6	357.2	360.7	356.4
7.5°	251.9	240.5	236.9	228.2	222.9	214.2	215.0	212.4
10°	153.6	143.0	140.4	137.8	135.2	134.3	135.2	134.3
12.5°	139.6	138.6	136.9	137.8	136.1	136.9	137.8	136.9
15°	151.9	153.6	151.9	152.7	151.9	153.6	154.5	154.5
17.5°	178.2	181.7	180.0	182.5	181.7	186.1	186.1	186.1
20°	218.5	224.7	222.9	226.4	226.4	231.8	231.8	233.5
22.5°	274.7	282.6	281.8	289.7	287.9	294.1	294.1	295.8
25°	342.3	350.2	351.0	356.4	355.5	361.7	361.7	363.4
27.5°	370.4	374.8	373.9	376.5	377.5	380.9	383.6	381.8
30°	347.6	351.0	350.2	352.0	352.0	354.6	357.2	354.6
32.5°	292.3	294.9	294.9	298.4	295.8	296.7	301.0	298.4
35°	223.8	225.6	223.8	225.6	226.4	226.4	230.8	230.0
37.5°	159.8	160.6	160.6	163.3	160.6	160.6	165.0	165.9
40°	107.0	108.0	107.0	110.6	108.8	108.8	111.5	108.8
42.5°	68.4	69.4	68.4	71.2	69.4	71.2	72.0	72.8
45°	42.1	42.1	41.3	43.0	42.1	43.0	43.9	43.9
47.5°	24.5	24.5	23.7	25.5	24.5	24.5	24.5	25.5
50°	13.2	13.2	13.2	14.0	13.2	13.2	13.2	12.3
52.5°	7.1	7.1	6.1	7.1	6.1	6.1	6.1	6.1
55°	3.5	2.6	2.6	2.6	1.8	1.8	1.8	1.8
57.5°	2.6	1.8	1.8	0.8	0.8	0.8	0.0	0.0
60°	1.8	1.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.8	1.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.8	1.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.6	1.8	1.8	0.8	0.8	0.0	0.0	0.0
70°	2.6	1.8	1.8	0.8	0.8	0.0	0.0	0.0
72.5°	2.6	1.8	1.8	1.8	0.8	0.8	0.0	0.0
75°	2.6	2.6	1.8	1.8	0.8	0.8	0.0	0.0
77.5°	3.5	2.6	1.8	1.8	0.8	0.8	0.0	0.0
80°	3.5	2.6	1.8	1.8	1.8	0.8	0.8	0.8
82.5°	3.5	2.6	2.6	1.8	1.8	0.8	0.8	0.8
85°	3.5	2.6	2.6	1.8	1.8	0.8	0.8	0.8
87.5°	3.5	2.6	2.6	1.8	1.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)