

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219635

Luminaire Tested: **LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5279.8 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219635

CATALOG NUMBER: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1219635

CATALOG NUMBER: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	66	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	57	49	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	36	59	48	41	36	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	42604	42604	42604
5°	116945	39253	16022
10°	256255	32130	6108
15°	391435	24458	7163
20°	453515	18195	11125
25°	494720	14960	17953
30°	552459	13568	18335
35°	562095	9309	12573
40°	571966	4412	6362
45°	572895	1833	2783
50°	484332	797	857
55°	155956	555	143
60°	30974	637	0
65°	3168	754	0
70°	340	1032	0
75°	0	1364	0
80°	0	2232	198
85°	0	4446	395



TEST NUMBER: P1219635

CATALOG NUMBER: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.3	2.5
10°-20°	694.7	13.2
20°-30°	1330.2	25.2
30°-40°	1567.2	29.7
40°-50°	1230.9	23.3
50°-60°	300.0	5.7
60°-70°	12.9	0.2
70°-80°	4.8	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2159.2	40.9
0°-40°	3726.4	70.6
0°-60°	5257.3	99.6
0°-90°	5279.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5279.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	990	990	990	990	990	
5°	2706	1958	908	476	371	358
15°	8782	4510	549	157	161	2452
25°	10414	5484	315	330	378	4854
35°	10694	3467	177	228	239	6706
45°	9409	1072	30	42	46	7069
55°	2078	39	7	5	2	2473
65°	31	5	7	5	0	82
75°	0	5	8	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219635

CATALOG NUMBER: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5
2.5°	1696.1	1692.4	1667.7	1690.6	1621.3	1618.4	1587.5	1573.7	1533.6	1495.2	1440.5
5°	2705.8	2646.4	2598.0	2599.8	2466.6	2441.9	2372.6	2302.2	2194.5	2094.1	1958.1
7.5°	4124.2	4053.9	3951.7	3908.8	3654.1	3579.3	3436.0	3248.9	3014.2	2780.5	2528.7
10°	5861.3	5872.4	5740.0	5617.7	5232.4	5081.0	4849.0	4480.2	4035.7	3596.6	3150.3
12.5°	7609.5	7602.3	7444.3	7259.0	6784.3	6570.7	6262.2	5802.1	5213.3	4532.3	3834.1
15°	8781.6	8833.7	8767.0	8619.1	8213.8	7969.2	7621.4	6997.0	6279.4	5452.4	4510.5
17.5°	9517.5	9566.6	9542.9	9427.0	9069.1	8808.1	8517.7	8006.6	7176.8	6137.1	5043.6
20°	9898.0	9975.7	9964.7	9838.7	9568.5	9352.1	9031.7	8558.0	7839.6	6612.6	5388.6
22.5°	10151.8	10211.1	10227.6	10085.1	9805.8	9600.3	9365.8	8885.7	8210.2	6903.0	5525.5
25°	10413.7	10518.9	10415.6	10240.4	9983.9	9786.7	9536.6	9076.5	8387.3	7021.7	5484.3
27.5°	10735.1	10785.3	10551.6	10391.9	10107.1	9893.4	9627.9	9186.9	8418.4	6926.7	5249.8
30°	11112.2	10904.1	10740.6	10423.8	10100.7	9892.6	9622.4	9117.6	8254.9	6611.8	4795.1
32.5°	11050.1	10859.3	10673.9	10339.0	10019.5	9813.2	9511.9	8886.7	7868.8	6085.0	4168.1
35°	10694.1	10735.1	10535.1	10257.6	9896.2	9683.4	9354.9	8558.0	7213.3	5358.5	3466.9
37.5°	10393.7	10484.1	10353.5	10097.0	9730.1	9442.6	8998.8	8030.3	6358.0	4436.4	2802.4
40°	10176.4	10205.6	10135.3	9847.8	9406.9	8991.5	8478.6	7082.8	5319.2	3482.5	2211.8
42.5°	9839.5	9917.2	9793.1	9479.0	8810.8	8340.7	7597.6	5988.2	4131.6	2660.1	1665.0
45°	9408.7	9482.7	9329.3	8807.1	7877.9	7188.7	6282.3	4669.3	3056.2	1960.8	1071.7
47.5°	8705.8	8751.5	8454.8	7732.7	6381.6	5732.8	4803.3	3255.3	1969.0	1096.4	521.1
50°	7230.7	7208.9	6597.1	5709.0	4268.5	3587.5	2859.0	1764.6	884.5	519.4	325.9
52.5°	4660.0	4609.9	4004.7	3196.9	2161.6	1649.4	1239.6	761.4	460.9	290.3	128.8
55°	2077.6	2058.5	1685.1	1309.0	884.5	761.4	581.5	373.4	245.5	101.4	39.3
57.5°	770.4	753.2	663.6	556.8	427.2	355.2	282.0	178.9	62.9	33.7	21.0
60°	359.7	358.7	315.8	260.2	180.8	137.0	79.4	42.0	26.5	18.3	11.9
62.5°	115.0	112.3	78.5	57.5	41.1	35.6	28.4	21.0	13.7	10.1	7.4
65°	31.1	31.1	28.4	23.7	19.1	16.4	13.7	10.1	6.3	5.5	4.6
67.5°	11.9	11.9	10.9	10.1	7.4	6.3	5.5	4.6	3.6	4.6	4.6
70°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.6	3.6	4.6
72.5°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	4.6
75°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	4.6
77.5°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	4.6
80°	0.0	0.0	0.8	0.8	1.9	1.9	2.7	2.7	3.6	4.6	4.6
82.5°	0.0	0.0	0.8	1.9	1.9	1.9	2.7	3.6	3.6	4.6	5.5
85°	0.0	0.0	0.8	1.9	1.9	2.7	2.7	3.6	3.6	4.6	5.5
87.5°	0.0	0.0	0.8	1.9	1.9	2.7	2.7	3.6	3.6	4.6	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219635

CATALOG NUMBER: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5
2.5°	1400.4	1340.1	1257.0	1208.7	1196.7	1171.2	1126.4	1059.8	1005.1	952.0	921.0
5°	1843.0	1700.6	1540.9	1428.5	1382.9	1321.8	1213.2	1100.9	997.7	908.2	838.0
7.5°	2312.3	2077.6	1819.4	1611.2	1536.3	1439.5	1262.5	1095.4	953.9	829.8	735.7
10°	2778.8	2400.7	2050.3	1749.0	1626.7	1495.2	1261.5	1045.2	879.0	734.9	630.8
12.5°	3245.2	2702.0	2220.0	1832.1	1673.3	1507.2	1224.1	968.6	784.2	637.2	537.7
15°	3676.1	2942.1	2335.1	1860.5	1668.8	1472.4	1148.4	875.4	684.6	548.7	456.4
17.5°	3997.3	3068.1	2361.5	1817.5	1596.6	1379.4	1032.4	765.9	589.7	470.2	376.2
20°	4155.3	3088.2	2298.5	1695.1	1472.4	1247.0	905.5	660.8	508.5	397.1	317.7
22.5°	4155.3	2993.2	2161.6	1541.9	1317.3	1094.5	783.2	574.2	444.6	345.9	279.3
25°	3997.3	2804.3	1978.1	1364.8	1146.6	943.8	677.2	509.4	395.3	314.9	259.3
27.5°	3690.6	2543.2	1742.6	1167.6	978.5	809.7	593.3	450.0	357.9	283.8	284.9
30°	3268.9	2222.8	1472.4	959.4	806.0	665.5	499.3	377.0	286.6	272.9	281.1
32.5°	2781.5	1839.4	1166.6	743.9	624.4	524.1	379.7	266.6	228.3	229.9	239.2
35°	2281.2	1447.7	878.2	551.4	464.6	379.7	249.3	175.2	173.4	177.1	183.5
37.5°	1801.1	1083.5	635.3	403.5	312.2	233.7	134.2	120.5	120.5	124.2	127.7
40°	1349.2	768.6	437.2	239.2	151.5	106.8	85.0	78.5	77.6	78.5	83.1
42.5°	926.5	486.6	260.2	95.9	73.0	62.1	53.9	49.3	48.4	49.3	52.0
45°	520.3	299.4	101.4	51.2	43.8	39.3	33.7	31.1	30.1	30.1	31.9
47.5°	325.9	118.7	45.7	31.9	27.4	25.5	21.9	20.2	19.1	19.1	20.2
50°	125.0	46.5	28.4	21.0	18.3	16.4	14.6	12.8	11.9	11.9	12.8
52.5°	43.0	27.4	18.3	13.7	11.9	10.9	9.0	8.2	8.2	8.2	8.2
55°	23.7	16.4	10.9	8.2	7.4	7.4	7.4	7.4	7.4	7.4	7.4
57.5°	14.6	10.1	7.4	6.3	6.3	6.3	6.3	6.3	6.3	7.4	7.4
60°	8.2	6.3	5.5	5.5	5.5	5.5	6.3	6.3	6.3	7.4	7.4
62.5°	5.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	7.4	7.4	7.4
65°	4.6	4.6	4.6	5.5	5.5	5.5	6.3	6.3	7.4	7.4	7.4
67.5°	4.6	4.6	5.5	5.5	5.5	6.3	6.3	7.4	7.4	7.4	7.4
70°	4.6	5.5	5.5	6.3	6.3	6.3	7.4	7.4	7.4	8.2	8.2
72.5°	4.6	5.5	5.5	6.3	6.3	6.3	7.4	7.4	8.2	8.2	8.2
75°	5.5	5.5	5.5	6.3	6.3	6.3	7.4	8.2	8.2	8.2	8.2
77.5°	5.5	5.5	6.3	6.3	6.3	7.4	7.4	8.2	8.2	8.2	8.2
80°	5.5	5.5	6.3	6.3	7.4	7.4	8.2	8.2	8.2	9.0	9.0
82.5°	5.5	5.5	6.3	7.4	7.4	7.4	8.2	8.2	9.0	9.0	9.0
85°	5.5	6.3	6.3	7.4	7.4	7.4	8.2	8.2	9.0	9.0	9.0
87.5°	5.5	6.3	6.3	7.4	7.4	7.4	8.2	8.2	9.0	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219635

CATALOG NUMBER: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5
2.5°	880.0	841.6	803.3	775.0	761.4	747.7	717.5	678.3	661.9	638.0	624.4
5°	766.8	702.0	650.9	617.0	597.1	570.5	535.8	497.5	475.5	450.9	434.5
7.5°	649.9	574.2	524.9	493.8	473.8	441.0	397.1	351.5	325.0	297.6	278.4
10°	547.7	475.5	420.0	384.4	358.7	320.4	276.6	244.7	221.8	198.1	178.9
12.5°	457.4	379.7	320.4	290.3	272.9	236.5	199.9	164.3	150.6	146.0	146.0
15°	370.7	300.2	250.1	224.5	206.3	167.0	159.7	158.0	156.9	156.1	158.0
17.5°	302.1	242.8	189.8	177.1	175.2	174.4	175.2	175.2	176.2	178.9	183.5
20°	253.8	199.1	195.4	196.2	196.2	199.9	204.5	208.1	211.8	216.3	224.5
22.5°	225.5	224.5	231.0	231.8	236.5	241.9	250.1	255.6	264.7	269.3	281.1
25°	260.2	266.6	278.4	282.0	289.3	298.5	311.4	318.6	329.5	335.0	348.6
27.5°	294.9	304.8	319.5	324.1	330.5	345.1	354.1	360.6	366.1	369.7	377.9
30°	292.0	301.3	315.8	316.8	325.9	335.9	341.4	346.9	350.5	349.6	354.1
32.5°	247.4	255.6	269.3	269.3	279.3	287.6	290.3	294.9	294.9	294.9	296.7
35°	189.8	195.4	204.5	207.3	215.4	220.9	222.8	228.3	228.3	226.4	226.4
37.5°	131.5	138.8	145.2	147.1	152.5	156.1	160.7	161.6	159.7	160.7	160.7
40°	85.8	90.3	95.0	95.9	100.4	103.2	107.7	107.7	108.6	107.7	109.6
42.5°	52.9	56.6	59.4	61.2	62.9	64.8	67.5	68.4	69.4	68.4	70.3
45°	32.9	34.7	36.6	37.4	38.3	39.3	42.0	42.0	42.0	42.0	43.0
47.5°	20.2	21.0	21.9	21.9	22.8	23.7	24.6	24.6	24.6	24.6	25.5
50°	11.9	12.8	12.8	12.8	13.7	13.7	14.6	14.6	14.6	13.7	14.6
52.5°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	7.4	8.2
55°	7.4	7.4	6.3	6.3	6.3	6.3	6.3	5.5	4.6	4.6	3.6
57.5°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.6	4.6	3.6	2.7
60°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.6	3.6	3.6	2.7
62.5°	7.4	6.3	6.3	6.3	6.3	5.5	5.5	4.6	3.6	3.6	2.7
65°	7.4	7.4	6.3	6.3	6.3	5.5	5.5	4.6	4.6	3.6	2.7
67.5°	7.4	7.4	7.4	6.3	7.4	6.3	5.5	5.5	4.6	3.6	3.6
70°	8.2	7.4	7.4	7.4	7.4	6.3	6.3	5.5	4.6	3.6	3.6
72.5°	8.2	8.2	7.4	7.4	7.4	6.3	6.3	5.5	4.6	4.6	3.6
75°	8.2	8.2	7.4	7.4	7.4	6.3	6.3	5.5	5.5	4.6	3.6
77.5°	8.2	8.2	8.2	7.4	7.4	7.4	6.3	6.3	5.5	4.6	3.6
80°	8.2	8.2	8.2	8.2	8.2	7.4	7.4	6.3	5.5	4.6	3.6
82.5°	9.0	8.2	8.2	8.2	8.2	7.4	7.4	6.3	5.5	4.6	4.6
85°	9.0	9.0	8.2	8.2	8.2	7.4	7.4	6.3	5.5	5.5	4.6
87.5°	9.0	8.2	8.2	8.2	8.2	7.4	7.4	6.3	5.5	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219635

CATALOG NUMBER: LDSQA6A50950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	989.5	989.5	989.5	989.5	989.5	989.5	989.5	989.5
2.5°	610.7	603.4	603.4	590.6	588.8	578.8	587.0	581.5
5°	416.3	404.4	400.7	387.9	383.3	371.5	375.1	370.7
7.5°	262.0	250.1	246.4	237.3	231.8	222.8	223.6	220.9
10°	159.7	148.7	146.0	143.3	140.6	139.7	140.6	139.7
12.5°	145.2	144.1	142.4	143.3	141.5	142.4	143.3	142.4
15°	158.0	159.7	158.0	158.8	158.0	159.7	160.7	160.7
17.5°	185.3	189.0	187.2	189.8	189.0	193.5	193.5	193.5
20°	227.2	233.7	231.8	235.5	235.5	241.1	241.1	242.8
22.5°	285.7	293.9	293.1	301.3	299.4	305.9	305.9	307.6
25°	356.0	364.2	365.0	370.7	369.7	376.2	376.2	377.9
27.5°	385.2	389.8	388.9	391.6	392.6	396.1	398.9	397.1
30°	361.5	365.0	364.2	366.1	366.1	368.8	371.5	368.8
32.5°	304.0	306.7	306.7	310.3	307.6	308.6	313.0	310.3
35°	232.8	234.6	232.8	234.6	235.5	235.5	240.0	239.2
37.5°	166.2	167.0	167.0	169.8	167.0	167.0	171.6	172.5
40°	111.3	112.3	111.3	115.0	113.2	113.2	116.0	113.2
42.5°	71.1	72.2	71.1	74.0	72.2	74.0	74.9	75.7
45°	43.8	43.8	43.0	44.7	43.8	44.7	45.7	45.7
47.5°	25.5	25.5	24.6	26.5	25.5	25.5	25.5	26.5
50°	13.7	13.7	13.7	14.6	13.7	13.7	13.7	12.8
52.5°	7.4	7.4	6.3	7.4	6.3	6.3	6.3	6.3
55°	3.6	2.7	2.7	2.7	1.9	1.9	1.9	1.9
57.5°	2.7	1.9	1.9	0.8	0.8	0.8	0.0	0.0
60°	1.9	1.9	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.9	1.9	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.9	1.9	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	2.7	1.9	1.9	0.8	0.8	0.0	0.0	0.0
70°	2.7	1.9	1.9	0.8	0.8	0.0	0.0	0.0
72.5°	2.7	1.9	1.9	1.9	0.8	0.8	0.0	0.0
75°	2.7	2.7	1.9	1.9	0.8	0.8	0.0	0.0
77.5°	3.6	2.7	1.9	1.9	0.8	0.8	0.0	0.0
80°	3.6	2.7	1.9	1.9	1.9	0.8	0.8	0.8
82.5°	3.6	2.7	2.7	1.9	1.9	0.8	0.8	0.8
85°	3.6	2.7	2.7	1.9	1.9	0.8	0.8	0.8
87.5°	3.6	2.7	2.7	1.9	1.9	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)