

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203953

Luminaire Tested: **LE_6B15D010 EC6B10209050 6LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209050 6LBNB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 696.9 lumens
Efficiency: N/A
Efficacy: 48.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.83
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203953

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P203953

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88
4	98	91	86	82	96	90	85	81	88	84	80		86	82	79		84
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72
8	81	72	66	62	80	71	66	62	70	65	61		69	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		65
10	74	64	59	55	73	64	58	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203953

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	12.8
10°-20°	194.0	27.8
20°-30°	228.0	32.7
30°-40°	156.9	22.5
40°-50°	29.1	4.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.9	73.3
0°-40°	667.9	95.8
0°-60°	696.9	100.0
0°-90°	696.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	696.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1026	
5°	977	89
15°	690	194
25°	498	228
35°	252	157
45°	29	29
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203953

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1026.0
2.5°	1016.9
5°	976.6
7.5°	920.1
10°	841.6
12.5°	763.1
15°	690.1
17.5°	628.0
20°	578.8
22.5°	536.8
25°	498.4
27.5°	460.0
30°	408.9
32.5°	335.9
35°	251.9
37.5°	175.2
40°	111.4
42.5°	62.1
45°	29.2
47.5°	9.1
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)