

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203644

Luminaire Tested: **LE_6B15D010 EC6B10209050 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209050 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1004.3 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203644

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203644

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203644

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.8	11.5
10°-20°	276.1	27.5
20°-30°	316.3	31.5
30°-40°	212.5	21.2
40°-50°	60.7	6.0
50°-60°	14.9	1.5
60°-70°	5.6	0.6
70°-80°	2.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	708.1	70.5
0°-40°	920.6	91.7
0°-60°	996.2	99.2
0°-90°	1004.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1004.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1287	
5°	1251	116
15°	991	276
25°	690	316
35°	339	212
45°	70	61
55°	16	15
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203644

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1287.4
2.5°	1278.2
5°	1250.8
7.5°	1201.2
10°	1140.9
12.5°	1063.9
15°	990.8
17.5°	913.8
20°	836.9
22.5°	763.6
25°	690.4
27.5°	622.6
30°	543.9
32.5°	439.5
35°	338.8
37.5°	247.2
40°	170.2
42.5°	111.8
45°	69.6
47.5°	42.1
50°	25.6
52.5°	20.1
55°	16.5
57.5°	12.9
60°	9.1
62.5°	7.4
65°	5.5
67.5°	3.6
70°	3.6
72.5°	1.9
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)