

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204676

Luminaire Tested: **LE_6B15D010 EC6B10209050 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209050 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1791.8 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204676

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204676

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204676

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	3.8
10°-20°	195.0	10.9
20°-30°	293.7	16.4
30°-40°	349.4	19.5
40°-50°	348.8	19.5
50°-60°	283.6	15.8
60°-70°	174.5	9.7
70°-80°	67.6	3.8
80°-90°	10.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.0	31.1
0°-40°	906.5	50.6
0°-60°	1538.9	85.9
0°-90°	1791.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1791.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	722	
5°	720	68
15°	692	195
25°	639	294
35°	560	349
45°	453	349
55°	318	284
65°	175	174
75°	62	68
85°	8	11
90°	0	



TEST NUMBER: P204676

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	722.0
2.5°	723.0
5°	719.9
7.5°	715.6
10°	710.2
12.5°	700.8
15°	692.2
17.5°	679.5
20°	665.6
22.5°	653.0
25°	639.1
27.5°	620.0
30°	600.9
32.5°	582.9
35°	559.5
37.5°	534.0
40°	510.6
42.5°	482.0
45°	453.4
47.5°	422.5
50°	389.6
52.5°	355.6
55°	317.5
57.5°	280.2
60°	244.2
62.5°	209.1
65°	175.1
67.5°	143.4
70°	113.6
72.5°	86.0
75°	61.6
77.5°	40.4
80°	24.4
82.5°	14.9
85°	8.5
87.5°	4.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)