

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204468

Luminaire Tested: **LE_6B15D010 EC6B10209050 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209050 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1461.5 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204468

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBSB1

Luminous Intensity Polar Plot






TEST NUMBER: P204468

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204468

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.9	4.2
10°-20°	172.7	11.8
20°-30°	256.8	17.6
30°-40°	298.9	20.4
40°-50°	291.3	19.9
50°-60°	224.1	15.3
60°-70°	123.9	8.5
70°-80°	32.8	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	490.3	33.5
0°-40°	789.2	54.0
0°-60°	1304.6	89.3
0°-90°	1461.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1461.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	645	
5°	641	61
15°	611	173
25°	558	257
35°	480	299
45°	378	291
55°	250	224
65°	124	124
75°	28	33
85°	0	0
90°	0	



TEST NUMBER: P204468

CATALOG NUMBER: LE_6B15D010 EC6B10209050 6LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	644.8
2.5°	644.8
5°	641.0
7.5°	635.5
10°	631.8
12.5°	620.6
15°	611.4
17.5°	602.1
20°	589.1
22.5°	576.2
25°	557.6
27.5°	539.1
30°	520.6
32.5°	500.2
35°	479.9
37.5°	453.9
40°	431.6
42.5°	407.6
45°	378.0
47.5°	350.1
50°	318.6
52.5°	285.4
55°	250.1
57.5°	216.8
60°	185.2
62.5°	153.8
65°	124.1
67.5°	96.4
70°	70.4
72.5°	48.1
75°	27.8
77.5°	13.0
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)