

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212640

Luminaire Tested: **LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5045.9 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212640

CATALOG NUMBER: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212640

CATALOG NUMBER: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39185	39185	39185
5°	100521	35652	11103
10°	195948	27395	5334
15°	351755	18610	7154
20°	522239	14121	11812
25°	593610	11639	18523
30°	643479	12722	17426
35°	677793	8247	10801
40°	692453	3659	5261
45°	625418	1400	1955
50°	411696	556	556
55°	112741	488	0
60°	22518	560	0
65°	1589	754	0
70°	227	932	0
75°	0	1381	0
80°	0	2058	223
85°	0	4100	445

TEST NUMBER: P1212640

CATALOG NUMBER: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	2.2
10°-20°	592.3	11.7
20°-30°	1342.5	26.6
30°-40°	1611.4	31.9
40°-50°	1135.7	22.5
50°-60°	234.4	4.6
60°-70°	8.3	0.2
70°-80°	5.0	0.1
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2046.3	40.6
0°-40°	3657.7	72.5
0°-60°	5027.7	99.6
0°-90°	5045.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5045.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	910	910	910	910	910	
5°	2326	1695	825	343	257	286
15°	7891	3472	418	149	160	2342
25°	12495	4199	245	343	390	5767
35°	12895	2941	157	206	206	8017
45°	10271	1008	23	31	32	7554
55°	1502	20	6	5	0	1979
65°	16	5	7	5	0	46
75°	0	5	8	6	0	0
85°	0	6	8	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212640

CATALOG NUMBER: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1
2.5°	1551.5	1504.7	1523.0	1468.9	1457.0	1446.9	1457.0	1398.3	1365.3	1323.0	1289.1
5°	2325.8	2269.9	2282.7	2188.2	2145.1	2115.7	2110.3	1989.1	1898.3	1798.2	1694.6
7.5°	3237.8	3184.6	3177.2	3030.5	2941.5	2891.1	2869.9	2696.5	2539.7	2361.6	2167.2
10°	4481.9	4360.9	4323.3	4110.3	3940.6	3833.3	3701.1	3424.1	3148.9	2880.0	2632.3
12.5°	5929.7	5863.7	5770.1	5394.8	5097.6	4945.2	4748.0	4314.9	3898.4	3454.3	3039.7
15°	7891.4	7656.5	7496.8	6954.6	6475.7	6240.8	5952.7	5290.3	4660.9	4098.5	3471.7
17.5°	9808.0	9685.1	9435.5	8731.8	7994.1	7623.4	7194.0	6294.0	5405.0	4605.0	3839.7
20°	11397.9	11282.4	10998.0	10334.7	9516.3	8969.4	8429.0	7194.0	6032.5	5008.6	4085.5
22.5°	12159.6	12086.1	11854.0	11286.0	10588.8	10068.6	9487.8	7960.1	6496.8	5272.9	4197.5
25°	12495.3	12461.3	12311.8	11864.0	11207.2	10765.8	10217.2	8502.4	6785.7	5395.8	4199.3
27.5°	12835.7	12842.1	12511.9	12157.7	11534.7	11110.8	10582.3	8742.8	6838.1	5327.0	4061.8
30°	12943.0	12875.1	12729.3	12221.0	11629.2	11178.7	10611.7	8631.7	6623.4	5044.4	3787.3
32.5°	12899.0	12872.4	12711.9	12174.2	11468.7	10972.2	10328.2	8191.4	6199.5	4640.7	3398.3
35°	12895.3	12845.8	12477.8	12016.4	11147.5	10534.7	9685.9	7479.4	5599.4	4108.5	2940.6
37.5°	12662.4	12539.3	12263.2	11641.1	10496.1	9719.0	8767.6	6609.6	4865.5	3511.2	2486.4
40°	12320.1	12155.0	11791.6	10850.3	9367.6	8472.2	7543.7	5621.5	4088.3	2922.2	2003.8
42.5°	11605.3	11355.8	10842.0	9547.4	7863.8	7056.5	6283.9	4620.5	3334.2	2380.9	1529.5
45°	10271.3	9930.0	9235.5	7814.3	6352.8	5694.0	5072.8	3717.6	2669.0	1766.2	1008.3
47.5°	8255.5	7939.0	7306.9	6220.6	4981.9	4425.0	3929.6	2765.3	1809.3	1023.0	481.7
50°	6146.3	5874.7	5381.1	4323.3	3344.2	2906.6	2482.8	1570.8	847.7	486.3	200.0
52.5°	3667.2	3532.3	3094.7	2397.4	1651.5	1423.1	1142.3	665.1	427.5	176.2	54.1
55°	1501.9	1386.3	1222.1	980.8	718.3	609.2	521.1	328.4	133.1	36.7	20.2
57.5°	679.0	653.3	579.0	455.1	330.3	277.1	187.2	62.4	29.3	18.3	11.9
60°	261.5	235.8	201.8	109.2	46.7	39.5	32.1	21.1	14.7	10.0	7.4
62.5°	37.6	35.8	32.1	25.7	20.2	18.3	15.6	11.0	8.3	6.5	5.5
65°	15.6	15.6	13.7	11.0	9.2	8.3	7.4	5.5	4.6	4.6	4.6
67.5°	6.5	6.5	5.5	4.6	3.7	3.7	3.7	2.8	3.7	3.7	4.6
70°	1.8	1.8	1.8	1.8	1.8	1.8	2.8	2.8	3.7	3.7	4.6
72.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.8	3.7	4.6	4.6
75°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.8	3.7	4.6	4.6
77.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	4.6
80°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	5.5
82.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	5.5
85°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	5.5
87.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212640

CATALOG NUMBER: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1
2.5°	1259.7	1200.9	1184.4	1133.1	1089.9	1068.9	1042.3	982.6	937.7	878.1	842.3
5°	1622.1	1511.1	1423.1	1315.6	1245.0	1199.2	1127.5	1018.4	930.3	824.9	749.6
7.5°	2013.9	1811.2	1652.4	1475.4	1373.5	1293.6	1171.6	1014.7	885.3	745.0	628.5
10°	2391.8	2089.2	1839.6	1585.5	1451.5	1340.5	1172.6	975.3	803.7	626.6	503.7
12.5°	2725.0	2334.2	1982.6	1656.1	1490.0	1351.4	1141.4	904.6	697.4	515.6	407.4
15°	3003.0	2524.0	2083.6	1682.7	1492.8	1327.7	1076.2	803.7	579.0	417.5	341.4
17.5°	3213.9	2624.0	2114.8	1650.5	1439.6	1259.7	976.3	676.2	469.8	354.2	287.2
20°	3323.1	2643.3	2069.9	1563.4	1341.4	1157.0	845.1	548.7	398.2	308.2	240.4
22.5°	3337.0	2589.2	1962.6	1438.7	1217.6	1032.2	700.0	457.8	355.1	272.4	212.0
25°	3255.3	2471.7	1809.3	1297.3	1081.7	889.0	569.7	410.1	323.0	245.0	244.1
27.5°	3080.9	2269.9	1625.8	1133.1	917.5	723.0	483.5	370.7	288.2	259.6	276.1
30°	2835.1	2011.2	1400.1	925.7	716.5	556.0	407.4	305.6	253.2	255.9	269.8
32.5°	2502.1	1690.0	1134.9	678.1	512.8	418.4	305.6	208.3	210.1	211.1	222.9
35°	2083.6	1355.1	847.7	455.9	360.6	294.5	172.5	153.3	156.0	156.9	165.1
37.5°	1669.8	1041.3	563.4	303.7	226.6	155.1	107.3	102.7	104.5	103.6	112.9
40°	1278.9	725.7	337.7	150.5	87.1	72.5	66.0	63.4	64.3	65.1	70.6
42.5°	905.5	393.6	167.0	56.9	45.9	42.2	39.5	37.6	38.5	38.5	42.2
45°	459.6	186.3	56.9	31.2	28.4	25.7	23.9	23.0	23.0	23.0	24.8
47.5°	199.1	61.5	26.7	19.3	17.4	16.5	14.7	13.7	13.7	13.7	14.7
50°	62.4	24.8	16.5	12.8	11.0	10.0	9.2	9.2	9.2	8.3	9.2
52.5°	23.0	15.6	11.0	8.3	7.4	7.4	7.4	6.5	7.4	6.5	7.4
55°	13.7	10.0	7.4	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
57.5°	9.2	7.4	6.5	6.5	5.5	5.5	6.5	6.5	6.5	6.5	6.5
60°	6.5	6.5	5.5	5.5	5.5	5.5	6.5	6.5	6.5	6.5	6.5
62.5°	5.5	5.5	5.5	5.5	5.5	5.5	6.5	6.5	6.5	6.5	7.4
65°	4.6	5.5	5.5	5.5	5.5	5.5	6.5	6.5	7.4	7.4	7.4
67.5°	4.6	5.5	5.5	6.5	6.5	6.5	6.5	7.4	7.4	7.4	7.4
70°	5.5	5.5	6.5	6.5	6.5	6.5	7.4	7.4	7.4	7.4	8.3
72.5°	5.5	5.5	6.5	6.5	6.5	6.5	7.4	7.4	8.3	8.3	8.3
75°	5.5	6.5	6.5	6.5	6.5	7.4	7.4	7.4	8.3	8.3	8.3
77.5°	5.5	6.5	6.5	7.4	7.4	7.4	7.4	8.3	8.3	8.3	8.3
80°	5.5	6.5	6.5	7.4	7.4	7.4	8.3	8.3	8.3	8.3	9.2
82.5°	5.5	6.5	6.5	7.4	7.4	7.4	8.3	8.3	8.3	8.3	9.2
85°	6.5	6.5	7.4	7.4	7.4	7.4	8.3	8.3	8.3	8.3	9.2
87.5°	6.5	6.5	7.4	7.4	7.4	7.4	8.3	8.3	9.2	8.3	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212640

CATALOG NUMBER: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1
2.5°	794.5	741.3	704.6	690.9	664.2	622.1	597.3	574.3	531.2	522.1	498.2
5°	663.3	578.0	517.4	494.5	464.2	428.5	393.6	370.7	343.2	332.1	315.6
7.5°	523.0	437.6	385.3	367.0	345.8	316.5	285.4	262.4	233.9	219.3	205.5
10°	411.0	347.7	303.7	285.4	263.3	232.2	200.0	169.8	144.9	129.4	126.6
12.5°	334.0	281.7	234.8	215.6	189.9	158.7	135.8	134.9	133.1	132.1	134.0
15°	273.4	222.9	173.4	152.3	144.9	144.0	146.8	149.6	148.6	151.4	153.3
17.5°	224.8	170.7	159.6	160.5	161.4	164.2	168.8	176.2	177.0	181.6	185.3
20°	183.5	180.7	185.3	189.0	191.8	197.2	207.4	216.5	219.3	225.7	233.0
22.5°	208.3	216.5	226.6	231.3	234.8	245.0	255.9	270.6	276.1	284.5	294.5
25°	251.3	265.2	280.8	286.3	291.7	308.2	321.2	338.6	343.2	353.2	363.3
27.5°	287.2	301.9	318.4	325.6	330.3	346.8	357.9	368.8	368.8	374.4	381.6
30°	281.7	293.6	307.3	312.8	314.7	326.6	337.7	341.4	339.5	342.3	347.7
32.5°	233.9	243.1	254.1	258.7	260.6	268.9	278.0	278.0	277.1	277.1	280.8
35°	173.4	179.8	185.3	189.9	192.7	198.1	206.4	205.5	205.5	203.7	206.4
37.5°	116.6	120.3	126.6	128.4	129.4	133.1	139.5	139.5	137.7	138.6	140.3
40°	70.6	75.2	78.9	79.9	81.7	84.3	89.0	89.0	89.0	89.0	89.9
42.5°	42.2	45.0	47.7	47.7	48.6	52.3	54.1	54.1	54.1	54.1	55.0
45°	24.8	25.7	27.6	28.4	28.4	30.2	31.2	31.2	31.2	31.2	32.1
47.5°	14.7	15.6	15.6	16.5	16.5	17.4	18.3	18.3	17.4	17.4	17.4
50°	9.2	9.2	9.2	9.2	10.0	10.0	10.0	10.0	10.0	10.0	9.2
52.5°	7.4	7.4	7.4	7.4	6.5	6.5	6.5	6.5	5.5	5.5	4.6
55°	6.5	6.5	6.5	6.5	6.5	5.5	5.5	5.5	4.6	3.7	2.8
57.5°	6.5	6.5	6.5	6.5	6.5	5.5	5.5	4.6	3.7	3.7	2.8
60°	6.5	6.5	6.5	6.5	6.5	5.5	5.5	4.6	3.7	3.7	2.8
62.5°	7.4	7.4	6.5	6.5	6.5	5.5	5.5	4.6	4.6	3.7	2.8
65°	7.4	7.4	6.5	6.5	6.5	6.5	5.5	5.5	4.6	3.7	2.8
67.5°	7.4	7.4	7.4	7.4	6.5	6.5	6.5	5.5	4.6	3.7	2.8
70°	8.3	8.3	7.4	7.4	7.4	6.5	6.5	5.5	4.6	4.6	3.7
72.5°	8.3	8.3	7.4	7.4	7.4	7.4	6.5	5.5	5.5	4.6	3.7
75°	8.3	8.3	8.3	8.3	7.4	7.4	6.5	6.5	5.5	4.6	3.7
77.5°	8.3	8.3	8.3	8.3	7.4	7.4	7.4	6.5	5.5	4.6	3.7
80°	8.3	8.3	8.3	8.3	8.3	7.4	7.4	6.5	5.5	4.6	3.7
82.5°	9.2	9.2	8.3	8.3	8.3	7.4	7.4	6.5	5.5	4.6	4.6
85°	9.2	9.2	8.3	8.3	8.3	7.4	7.4	6.5	5.5	5.5	4.6
87.5°	9.2	9.2	8.3	8.3	8.3	7.4	7.4	6.5	5.5	5.5	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212640

CATALOG NUMBER: LDSQA6A60927D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	910.1	910.1	910.1	910.1	910.1	910.1	910.1	910.1
2.5°	483.5	455.9	446.8	453.3	445.9	440.4	433.1	429.4
5°	302.8	282.6	276.1	278.0	271.5	266.1	258.7	256.9
7.5°	186.3	167.0	159.6	159.6	152.3	145.9	141.2	138.6
10°	124.7	121.0	122.0	122.9	122.0	122.9	120.3	122.0
12.5°	134.0	132.1	134.0	134.9	134.9	136.8	133.1	135.8
15°	156.0	154.2	156.9	158.7	158.7	161.4	157.9	160.5
17.5°	190.9	189.9	194.6	196.3	197.2	201.8	197.2	200.9
20°	241.3	240.4	246.8	249.6	248.7	257.8	251.3	257.8
22.5°	306.5	304.7	313.8	316.5	317.5	329.3	323.9	328.4
25°	371.6	373.4	378.0	382.5	383.5	393.6	385.3	389.9
27.5°	385.3	382.5	385.3	390.9	391.8	396.4	389.0	392.7
30°	348.6	344.1	344.9	351.4	353.2	355.1	348.6	350.5
32.5°	283.5	276.1	276.1	282.6	284.5	287.2	276.1	280.8
35°	209.2	202.8	202.8	207.4	208.3	210.1	201.8	205.5
37.5°	143.1	137.7	139.5	141.2	142.2	144.0	143.1	142.2
40°	91.7	88.0	90.8	90.8	91.7	92.7	92.7	93.6
42.5°	56.0	53.2	55.0	55.0	56.0	56.0	56.0	56.9
45°	32.1	31.2	31.2	32.1	32.1	32.1	31.2	32.1
47.5°	17.4	16.5	17.4	17.4	17.4	17.4	17.4	17.4
50°	9.2	8.3	8.3	8.3	8.3	8.3	8.3	8.3
52.5°	4.6	3.7	3.7	3.7	2.8	3.7	2.8	2.8
55°	2.8	1.8	1.8	1.8	0.9	0.9	0.0	0.0
57.5°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
60°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
65°	1.8	0.9	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.8	1.8	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.8	1.8	1.8	0.9	0.9	0.0	0.0	0.0
72.5°	2.8	1.8	1.8	1.8	0.9	0.9	0.0	0.0
75°	2.8	1.8	1.8	1.8	0.9	0.9	0.0	0.0
77.5°	2.8	2.8	1.8	1.8	0.9	0.9	0.9	0.0
80°	3.7	2.8	1.8	1.8	1.8	0.9	0.9	0.9
82.5°	3.7	2.8	1.8	1.8	1.8	0.9	0.9	0.9
85°	3.7	2.8	2.8	1.8	1.8	0.9	0.9	0.9
87.5°	3.7	2.8	2.8	1.8	1.8	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)