

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212642

Luminaire Tested: **LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5306.4 lumens
Efficiency: N/A
Efficacy: 73.9 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212642

CATALOG NUMBER: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212642

CATALOG NUMBER: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	42819	42819	42819
5°	117524	39451	16099
10°	257545	32287	6134
15°	393401	24578	7194
20°	455792	18282	11184
25°	497205	15036	18043
30°	555228	13637	18430
35°	564913	9351	12636
40°	574838	4435	6396
45°	575775	1839	2795
50°	486763	797	857
55°	156744	555	135
60°	31121	637	0
65°	3179	754	0
70°	352	1045	0
75°	0	1381	0
80°	0	2281	223
85°	0	4545	445

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212642

CATALOG NUMBER: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.0	2.5
10°-20°	698.2	13.2
20°-30°	1336.8	25.2
30°-40°	1575.0	29.7
40°-50°	1237.1	23.3
50°-60°	301.5	5.7
60°-70°	13.0	0.2
70°-80°	4.9	0.1
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2170.0	40.9
0°-40°	3745.1	70.6
0°-60°	5283.7	99.6
0°-90°	5306.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5306.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	994	994	994	994	994	
5°	2719	1968	913	478	372	359
15°	8826	4533	551	158	161	2464
25°	10466	5512	316	331	380	4878
35°	10748	3484	178	229	240	6739
45°	9456	1077	30	42	46	7105
55°	2088	40	7	5	2	2485
65°	31	5	7	5	0	83
75°	0	5	8	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212642

CATALOG NUMBER: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5
2.5°	1704.6	1701.0	1676.1	1699.1	1629.4	1626.6	1595.4	1581.6	1541.2	1502.7	1447.6
5°	2719.2	2659.7	2611.0	2612.8	2479.0	2454.1	2384.4	2313.7	2205.5	2104.6	1967.9
7.5°	4144.9	4074.3	3971.6	3928.5	3672.5	3597.3	3453.3	3265.2	3029.4	2794.4	2541.3
10°	5890.8	5901.9	5768.8	5645.9	5258.7	5106.4	4873.4	4502.8	4056.0	3614.7	3166.0
12.5°	7647.7	7640.4	7481.6	7295.4	6818.3	6603.7	6293.6	5831.2	5239.5	4555.1	3853.2
15°	8825.7	8877.9	8811.0	8662.4	8255.0	8009.2	7659.6	7032.2	6311.1	5479.8	4533.0
17.5°	9565.1	9614.6	9590.9	9474.3	9114.7	8852.3	8560.6	8046.7	7212.9	6167.8	5068.8
20°	9947.7	10025.7	10014.7	9888.1	9616.5	9399.1	9077.1	8600.9	7878.9	6645.8	5415.6
22.5°	10202.8	10262.3	10278.8	10135.8	9855.0	9648.7	9412.8	8930.3	8251.3	6937.7	5553.2
25°	10466.0	10571.6	10467.9	10291.8	10034.0	9835.7	9584.4	9122.0	8429.4	7056.9	5511.9
27.5°	10789.0	10839.4	10604.6	10444.0	10157.8	9943.2	9676.1	9233.0	8460.5	6961.4	5276.2
30°	11167.9	10958.8	10794.4	10476.2	10151.3	9942.2	9670.6	9163.3	8296.3	6645.0	4819.3
32.5°	11105.6	10913.8	10727.5	10390.8	10069.8	9862.4	9559.6	8931.1	7908.3	6115.6	4189.0
35°	10747.7	10789.0	10588.1	10309.2	9945.8	9732.1	9401.8	8600.9	7249.6	5385.3	3484.4
37.5°	10445.8	10536.6	10405.6	10147.8	9779.0	9489.9	9044.0	8070.6	6389.9	4458.7	2816.5
40°	10227.5	10256.9	10186.2	9897.2	9454.1	9036.7	8521.1	7118.4	5345.9	3500.0	2222.9
42.5°	9889.0	9966.9	9842.2	9526.6	8855.1	8382.5	7635.8	6018.4	4152.3	2673.4	1673.4
45°	9456.0	9530.3	9376.1	8851.4	7917.4	7224.8	6313.7	4692.6	3071.5	1970.6	1077.1
47.5°	8749.5	8795.4	8497.2	7771.5	6413.7	5761.4	4827.5	3271.6	1978.9	1101.8	523.9
50°	7267.0	7245.0	6630.2	5737.6	4289.9	3605.4	2873.4	1773.4	889.0	522.1	327.5
52.5°	4683.5	4633.1	4024.8	3212.9	2172.5	1657.8	1245.8	765.1	463.3	291.7	129.4
55°	2088.1	2068.8	1693.6	1315.6	889.0	765.1	584.4	375.3	246.8	101.8	39.5
57.5°	774.3	756.9	667.0	559.7	429.4	356.9	283.5	179.8	63.4	33.9	21.1
60°	361.4	360.5	317.5	261.5	181.6	137.7	79.9	42.2	26.7	18.3	11.9
62.5°	115.6	112.9	78.9	57.8	41.3	35.8	28.4	21.1	13.7	10.0	7.4
65°	31.2	31.2	28.4	23.9	19.3	16.5	13.7	10.0	6.5	5.5	4.6
67.5°	11.9	11.9	11.0	10.0	7.4	6.5	5.5	4.6	3.7	4.6	4.6
70°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.7	3.7	4.6
72.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	4.6
75°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	4.6
77.5°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	4.6
80°	0.0	0.0	0.9	0.9	1.8	1.8	2.8	2.8	3.7	4.6	4.6
82.5°	0.0	0.0	0.9	1.8	1.8	1.8	2.8	3.7	3.7	4.6	5.5
85°	0.0	0.0	0.9	1.8	1.8	2.8	2.8	3.7	3.7	4.6	5.5
87.5°	0.0	0.0	0.9	1.8	1.8	2.8	2.8	3.7	3.7	4.6	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212642

CATALOG NUMBER: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5
2.5°	1407.4	1346.8	1263.2	1214.7	1202.8	1177.0	1132.2	1065.1	1010.1	956.9	925.7
5°	1852.4	1709.1	1548.6	1435.8	1390.0	1328.4	1219.3	1106.4	1002.8	912.8	842.2
7.5°	2323.9	2088.1	1828.5	1619.2	1544.0	1446.9	1268.8	1100.9	958.7	834.0	739.5
10°	2792.7	2412.8	2060.5	1757.8	1634.8	1502.7	1267.9	1050.5	883.5	738.5	634.0
12.5°	3261.5	2715.6	2231.2	1841.3	1681.7	1514.7	1230.2	973.4	788.0	640.3	540.4
15°	3694.5	2956.9	2346.8	1869.8	1677.1	1479.9	1154.1	879.8	688.1	551.4	458.7
17.5°	4017.4	3083.5	2373.4	1826.6	1604.6	1386.3	1037.7	769.7	592.7	472.4	377.9
20°	4176.1	3103.7	2310.1	1703.7	1479.9	1253.2	910.1	664.2	511.0	399.0	319.3
22.5°	4176.1	3008.3	2172.5	1549.5	1323.8	1100.0	787.1	577.1	446.8	347.7	280.8
25°	4017.4	2818.3	1988.1	1371.6	1152.2	948.7	680.7	511.9	397.2	316.5	260.6
27.5°	3709.2	2555.9	1751.4	1173.3	983.5	813.8	596.4	452.2	359.6	285.4	286.2
30°	3285.3	2234.0	1479.9	964.3	810.1	668.8	501.9	378.8	288.0	274.3	282.6
32.5°	2795.4	1848.7	1172.4	747.6	627.5	526.5	381.6	267.8	229.4	231.1	240.4
35°	2292.7	1455.0	882.6	554.1	467.0	381.6	250.4	176.1	174.4	177.9	184.4
37.5°	1810.1	1089.0	638.5	405.5	313.8	234.8	134.9	121.0	121.0	124.7	128.4
40°	1355.9	772.5	439.4	240.4	152.3	107.3	85.3	78.9	78.0	78.9	83.4
42.5°	931.1	488.9	261.5	96.4	73.4	62.4	54.1	49.5	48.6	49.5	52.3
45°	523.0	301.0	101.8	51.3	44.1	39.5	33.9	31.2	30.2	30.2	32.1
47.5°	327.5	119.3	45.9	32.1	27.6	25.7	22.0	20.2	19.3	19.3	20.2
50°	125.7	46.7	28.4	21.1	18.3	16.5	14.7	12.8	11.9	11.9	12.8
52.5°	43.2	27.6	18.3	13.7	11.9	11.0	9.2	8.3	8.3	8.3	8.3
55°	23.9	16.5	11.0	8.3	7.4	7.4	7.4	7.4	7.4	7.4	7.4
57.5°	14.7	10.0	7.4	6.5	6.5	6.5	6.5	6.5	6.5	7.4	7.4
60°	8.3	6.5	5.5	5.5	5.5	5.5	6.5	6.5	6.5	7.4	7.4
62.5°	5.5	5.5	5.5	5.5	5.5	5.5	6.5	6.5	7.4	7.4	7.4
65°	4.6	4.6	4.6	5.5	5.5	5.5	6.5	6.5	7.4	7.4	7.4
67.5°	4.6	4.6	5.5	5.5	5.5	6.5	6.5	7.4	7.4	7.4	7.4
70°	4.6	5.5	5.5	6.5	6.5	6.5	7.4	7.4	7.4	8.3	8.3
72.5°	4.6	5.5	5.5	6.5	6.5	6.5	7.4	7.4	8.3	8.3	8.3
75°	5.5	5.5	5.5	6.5	6.5	6.5	7.4	8.3	8.3	8.3	8.3
77.5°	5.5	5.5	6.5	6.5	6.5	7.4	7.4	8.3	8.3	8.3	8.3
80°	5.5	5.5	6.5	6.5	7.4	7.4	8.3	8.3	8.3	9.2	9.2
82.5°	5.5	5.5	6.5	7.4	7.4	7.4	8.3	8.3	9.2	9.2	9.2
85°	5.5	6.5	6.5	7.4	7.4	7.4	8.3	8.3	9.2	9.2	9.2
87.5°	5.5	6.5	6.5	7.4	7.4	7.4	8.3	8.3	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212642

CATALOG NUMBER: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5
2.5°	884.4	845.9	807.3	778.9	765.1	751.3	721.1	681.6	665.1	641.3	627.5
5°	770.6	705.5	654.2	620.1	599.9	573.4	538.6	500.0	478.0	453.2	436.7
7.5°	653.3	577.1	527.5	496.3	476.1	443.1	399.0	353.2	326.6	299.1	279.8
10°	550.4	478.0	422.0	386.2	360.5	322.1	278.0	245.9	222.9	199.1	179.8
12.5°	459.6	381.6	322.1	291.7	274.3	237.6	200.9	165.1	151.4	146.8	146.8
15°	372.5	301.9	251.3	225.7	207.4	167.9	160.5	158.7	157.7	156.8	158.7
17.5°	303.7	244.1	190.9	177.9	176.1	175.2	176.1	176.1	177.0	179.8	184.4
20°	255.0	200.0	196.3	197.2	197.2	200.9	205.5	209.2	212.8	217.4	225.7
22.5°	226.6	225.7	232.1	233.0	237.6	243.1	251.3	256.9	266.1	270.6	282.6
25°	261.5	267.8	279.8	283.5	290.8	300.0	312.8	320.2	331.2	336.7	350.5
27.5°	296.3	306.4	321.2	325.6	332.1	346.8	356.0	362.3	367.9	371.6	379.8
30°	293.6	302.8	317.5	318.4	327.5	337.7	343.1	348.6	352.3	351.4	356.0
32.5°	248.7	256.9	270.6	270.6	280.8	288.9	291.7	296.3	296.3	296.3	298.2
35°	190.9	196.3	205.5	208.3	216.5	222.0	223.9	229.4	229.4	227.6	227.6
37.5°	132.1	139.4	145.9	147.7	153.3	156.8	161.4	162.4	160.5	161.4	161.4
40°	86.2	90.8	95.4	96.4	101.0	103.6	108.2	108.2	109.2	108.2	110.1
42.5°	53.2	56.9	59.7	61.5	63.4	65.1	67.8	68.8	69.7	68.8	70.6
45°	33.0	34.8	36.7	37.6	38.5	39.5	42.2	42.2	42.2	42.2	43.2
47.5°	20.2	21.1	22.0	22.0	23.0	23.9	24.8	24.8	24.8	24.8	25.7
50°	11.9	12.8	12.8	12.8	13.7	13.7	14.7	14.7	14.7	13.7	14.7
52.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	7.4	8.3
55°	7.4	7.4	6.5	6.5	6.5	6.5	6.5	5.5	4.6	4.6	3.7
57.5°	6.5	6.5	6.5	6.5	6.5	5.5	5.5	4.6	4.6	3.7	2.8
60°	6.5	6.5	6.5	6.5	6.5	5.5	5.5	4.6	3.7	3.7	2.8
62.5°	7.4	6.5	6.5	6.5	6.5	5.5	5.5	4.6	3.7	3.7	2.8
65°	7.4	7.4	6.5	6.5	6.5	5.5	5.5	4.6	4.6	3.7	2.8
67.5°	7.4	7.4	7.4	6.5	7.4	6.5	5.5	5.5	4.6	3.7	3.7
70°	8.3	7.4	7.4	7.4	7.4	6.5	6.5	5.5	4.6	3.7	3.7
72.5°	8.3	8.3	7.4	7.4	7.4	6.5	6.5	5.5	4.6	4.6	3.7
75°	8.3	8.3	7.4	7.4	7.4	6.5	6.5	5.5	5.5	4.6	3.7
77.5°	8.3	8.3	8.3	7.4	7.4	7.4	6.5	6.5	5.5	4.6	3.7
80°	8.3	8.3	8.3	8.3	8.3	7.4	7.4	6.5	5.5	4.6	3.7
82.5°	9.2	8.3	8.3	8.3	8.3	7.4	7.4	6.5	5.5	4.6	4.6
85°	9.2	9.2	8.3	8.3	8.3	7.4	7.4	6.5	5.5	5.5	4.6
87.5°	9.2	8.3	8.3	8.3	8.3	7.4	7.4	6.5	5.5	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212642

CATALOG NUMBER: LDSQA6A60927D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	994.5	994.5	994.5	994.5	994.5	994.5	994.5	994.5
2.5°	613.8	606.4	606.4	593.6	591.8	581.6	589.9	584.4
5°	418.3	406.4	402.7	389.9	385.3	373.4	377.1	372.5
7.5°	263.3	251.3	247.8	238.5	233.0	223.9	224.8	222.0
10°	160.5	149.6	146.8	144.0	141.2	140.3	141.2	140.3
12.5°	145.9	144.9	143.1	144.0	142.2	143.1	144.0	143.1
15°	158.7	160.5	158.7	159.6	158.7	160.5	161.4	161.4
17.5°	186.3	189.9	188.1	190.9	189.9	194.4	194.4	194.4
20°	228.5	234.8	233.0	236.7	236.7	242.2	242.2	244.1
22.5°	287.1	295.4	294.5	302.8	301.0	307.3	307.3	309.1
25°	357.9	366.0	367.0	372.5	371.6	377.9	377.9	379.8
27.5°	387.2	391.8	390.9	393.6	394.5	398.1	400.9	399.0
30°	363.3	367.0	366.0	367.9	367.9	370.7	373.4	370.7
32.5°	305.4	308.2	308.2	311.9	309.1	310.1	314.7	311.9
35°	233.9	235.8	233.9	235.8	236.7	236.7	241.3	240.4
37.5°	167.0	167.9	167.9	170.7	167.9	167.9	172.5	173.4
40°	111.9	112.9	111.9	115.6	113.8	113.8	116.6	113.8
42.5°	71.5	72.5	71.5	74.3	72.5	74.3	75.2	76.2
45°	44.1	44.1	43.2	45.0	44.1	45.0	45.9	45.9
47.5°	25.7	25.7	24.8	26.7	25.7	25.7	25.7	26.7
50°	13.7	13.7	13.7	14.7	13.7	13.7	13.7	12.8
52.5°	7.4	7.4	6.5	7.4	6.5	6.5	6.5	6.5
55°	3.7	2.8	2.8	2.8	1.8	1.8	1.8	1.8
57.5°	2.8	1.8	1.8	0.9	0.9	0.9	0.0	0.0
60°	1.8	1.8	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	1.8	1.8	0.9	0.9	0.0	0.0	0.0	0.0
65°	1.8	1.8	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.8	1.8	1.8	0.9	0.9	0.0	0.0	0.0
70°	2.8	1.8	1.8	0.9	0.9	0.0	0.0	0.0
72.5°	2.8	1.8	1.8	1.8	0.9	0.9	0.0	0.0
75°	2.8	2.8	1.8	1.8	0.9	0.9	0.0	0.0
77.5°	3.7	2.8	1.8	1.8	0.9	0.9	0.0	0.0
80°	3.7	2.8	1.8	1.8	1.8	0.9	0.9	0.9
82.5°	3.7	2.8	2.8	1.8	1.8	0.9	0.9	0.9
85°	3.7	2.8	2.8	1.8	1.8	0.9	0.9	0.9
87.5°	3.7	2.8	2.8	1.8	1.8	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)