

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212646

Luminaire Tested: **LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5400.4 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212646

CATALOG NUMBER: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1212646

CATALOG NUMBER: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	81	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	57	49	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41945	41945	41945
5°	107588	38155	11886
10°	209720	29323	5705
15°	376472	19916	7662
20°	558940	15120	12641
25°	635321	12456	19829
30°	688701	13622	18649
35°	725424	8825	11558
40°	741105	3918	5632
45°	669369	1498	2089
50°	440626	589	589
55°	120667	518	0
60°	24094	594	0
65°	1691	805	0
70°	252	995	0
75°	0	1464	0
80°	0	2182	223
85°	0	4347	445

TEST NUMBER: P1212646

CATALOG NUMBER: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.3	2.2
10°-20°	633.9	11.7
20°-30°	1436.8	26.6
30°-40°	1724.7	31.9
40°-50°	1215.5	22.5
50°-60°	250.8	4.6
60°-70°	8.9	0.2
70°-80°	5.3	0.1
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2190.1	40.6
0°-40°	3914.7	72.5
0°-60°	5381.0	99.6
0°-90°	5400.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5400.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	974	974	974	974	974	
5°	2489	1814	883	367	275	306
15°	8446	3716	447	159	172	2506
25°	13373	4494	262	367	417	6172
35°	13802	3147	168	220	220	8580
45°	10993	1079	25	33	34	8085
55°	1608	22	7	5	0	2118
65°	17	5	8	5	0	50
75°	0	5	9	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212646

CATALOG NUMBER: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2
2.5°	1660.6	1610.4	1630.1	1572.1	1559.3	1548.5	1559.3	1496.5	1461.1	1416.0	1379.7
5°	2489.3	2429.3	2443.2	2341.9	2295.9	2264.5	2258.5	2128.9	2031.7	1924.7	1813.7
7.5°	3465.4	3408.4	3400.6	3243.4	3148.2	3094.2	3071.6	2886.0	2718.0	2527.5	2319.4
10°	4796.9	4667.3	4627.0	4399.2	4217.5	4102.7	3961.2	3664.7	3370.1	3082.3	2817.3
12.5°	6346.4	6275.7	6175.6	5773.9	5455.8	5292.8	5081.6	4618.2	4172.4	3697.1	3253.3
15°	8445.9	8194.4	8023.6	7443.2	6930.7	6679.3	6371.0	5662.0	4988.4	4386.5	3715.8
17.5°	10497.2	10365.6	10098.5	9345.3	8555.8	8159.2	7699.6	6736.2	5784.8	4928.5	4109.6
20°	12198.9	12075.2	11770.8	11060.8	10184.9	9599.7	9021.3	7699.6	6456.4	5360.5	4372.6
22.5°	13014.0	12935.3	12686.9	12079.2	11332.9	10776.1	10154.5	8519.5	6953.2	5643.4	4492.5
25°	13373.3	13337.0	13176.9	12697.7	11994.7	11522.4	10935.1	9099.8	7262.6	5774.9	4494.5
27.5°	13737.6	13744.5	13391.0	13012.0	12345.3	11891.6	11326.0	9357.1	7318.6	5701.2	4347.2
30°	13852.6	13779.9	13623.7	13079.7	12446.4	11964.2	11357.4	9238.3	7088.8	5398.8	4053.6
32.5°	13805.4	13777.0	13605.1	13029.7	12274.5	11743.2	11053.9	8766.9	6635.1	4966.8	3637.1
35°	13801.5	13748.5	13354.7	12860.8	11930.8	11274.9	10366.6	8005.0	5992.9	4397.2	3147.1
37.5°	13552.0	13420.4	13124.9	12459.1	11233.6	10402.0	9383.6	7074.0	5207.4	3757.9	2661.1
40°	13185.7	13009.0	12620.1	11612.7	10025.8	9067.5	8073.6	6016.4	4375.7	3127.6	2144.6
42.5°	12420.8	12153.8	11603.9	10218.3	8416.5	7552.2	6725.4	4945.1	3568.5	2548.1	1636.9
45°	10993.1	10627.8	9884.4	8363.4	6799.1	6094.0	5429.3	3978.9	2856.5	1890.2	1079.2
47.5°	8835.7	8497.0	7820.3	6657.7	5332.0	4736.0	4205.8	2959.6	1936.4	1094.9	515.6
50°	6578.2	6287.6	5759.2	4627.0	3579.3	3110.8	2657.2	1681.2	907.4	520.5	214.1
52.5°	3924.9	3780.6	3312.1	2565.8	1767.5	1523.0	1222.6	711.9	457.6	188.5	57.9
55°	1607.5	1483.7	1308.0	1049.7	768.9	652.1	557.7	351.5	142.4	39.3	21.6
57.5°	726.7	699.2	619.6	487.1	353.5	296.6	200.4	66.8	31.4	19.7	12.8
60°	279.8	252.4	216.1	116.8	50.0	42.2	34.3	22.6	15.7	10.8	7.9
62.5°	40.3	38.3	34.3	27.5	21.6	19.7	16.6	11.7	8.8	6.9	5.9
65°	16.6	16.6	14.8	11.7	9.8	8.8	7.9	5.9	4.9	4.9	4.9
67.5°	6.9	6.9	5.9	4.9	4.0	4.0	4.0	2.9	4.0	4.0	4.9
70°	2.0	2.0	2.0	2.0	2.0	2.0	2.9	2.9	4.0	4.0	4.9
72.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.9	4.9
75°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.9	4.9
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	4.9
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	5.9
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	5.9
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	5.9
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212646

CATALOG NUMBER: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2
2.5°	1348.2	1285.4	1267.7	1212.7	1166.6	1144.0	1115.5	1051.6	1003.6	939.7	901.4
5°	1736.1	1617.3	1523.0	1408.2	1332.5	1283.4	1206.9	1089.9	995.7	882.8	802.3
7.5°	2155.4	1938.4	1768.5	1579.0	1470.0	1384.5	1254.0	1086.1	947.6	797.4	672.7
10°	2560.0	2235.9	1968.8	1696.9	1553.5	1434.7	1254.9	1043.9	860.2	670.7	539.1
12.5°	2916.4	2498.1	2122.0	1772.5	1594.7	1446.5	1221.5	968.2	746.3	551.9	436.0
15°	3213.9	2701.4	2230.0	1800.9	1597.6	1420.8	1151.8	860.2	619.6	446.8	365.2
17.5°	3439.8	2808.4	2263.4	1766.6	1540.7	1348.2	1044.8	723.8	502.8	379.0	307.3
20°	3556.6	2829.0	2215.4	1673.2	1435.6	1238.3	904.3	587.3	426.2	330.0	257.3
22.5°	3571.4	2771.1	2100.4	1539.8	1303.1	1104.7	749.2	490.0	380.0	291.6	226.8
25°	3484.0	2645.4	1936.4	1388.5	1157.8	951.5	609.8	438.9	345.7	262.2	261.2
27.5°	3297.5	2429.3	1740.0	1212.7	981.9	773.8	517.4	396.7	308.4	277.9	295.5
30°	3034.3	2152.5	1498.5	990.8	766.9	595.1	436.0	327.0	271.0	274.0	288.7
32.5°	2677.8	1808.8	1214.7	725.7	548.9	447.7	327.0	222.9	224.9	225.9	238.7
35°	2230.0	1450.4	907.4	488.0	386.0	315.2	184.7	163.9	167.0	167.9	176.7
37.5°	1787.1	1114.5	603.0	325.0	242.5	165.9	114.8	110.0	111.9	111.0	120.8
40°	1368.8	776.7	361.4	161.0	93.3	77.6	70.8	67.7	68.8	69.7	75.6
42.5°	969.1	421.2	178.7	60.9	49.1	45.1	42.2	40.3	41.2	41.2	45.1
45°	492.0	199.3	60.9	33.4	30.5	27.5	25.5	24.6	24.6	24.6	26.5
47.5°	213.0	65.7	28.5	20.6	18.6	17.7	15.7	14.8	14.8	14.8	15.7
50°	66.8	26.5	17.7	13.7	11.7	10.8	9.8	9.8	9.8	8.8	9.8
52.5°	24.6	16.6	11.7	8.8	7.9	7.9	7.9	6.9	7.9	6.9	7.9
55°	14.8	10.8	7.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
57.5°	9.8	7.9	6.9	6.9	5.9	5.9	6.9	6.9	6.9	6.9	6.9
60°	6.9	6.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	6.9	6.9
62.5°	5.9	5.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	6.9	7.9
65°	4.9	5.9	5.9	5.9	5.9	5.9	6.9	6.9	7.9	7.9	7.9
67.5°	4.9	5.9	5.9	6.9	6.9	6.9	6.9	7.9	7.9	7.9	7.9
70°	5.9	5.9	6.9	6.9	6.9	6.9	7.9	7.9	7.9	7.9	8.8
72.5°	5.9	5.9	6.9	6.9	6.9	6.9	7.9	7.9	8.8	8.8	8.8
75°	5.9	6.9	6.9	6.9	6.9	7.9	7.9	7.9	8.8	8.8	8.8
77.5°	5.9	6.9	6.9	7.9	7.9	7.9	7.9	8.8	8.8	8.8	8.8
80°	5.9	6.9	6.9	7.9	7.9	7.9	8.8	8.8	8.8	8.8	9.8
82.5°	5.9	6.9	6.9	7.9	7.9	7.9	8.8	8.8	8.8	8.8	9.8
85°	6.9	6.9	7.9	7.9	7.9	7.9	8.8	8.8	8.8	8.8	9.8
87.5°	6.9	6.9	7.9	7.9	7.9	7.9	8.8	8.8	9.8	8.8	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212646

CATALOG NUMBER: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2
2.5°	850.3	793.5	754.1	739.5	711.0	665.8	639.3	614.7	568.5	558.8	533.1
5°	709.9	618.7	553.9	529.3	496.8	458.6	421.2	396.7	367.2	355.5	337.8
7.5°	559.7	468.3	412.4	392.8	370.3	338.7	305.4	280.9	250.4	234.7	219.9
10°	440.0	372.1	325.0	305.4	281.8	248.4	214.1	181.6	155.1	138.5	135.6
12.5°	357.5	301.5	251.3	230.7	203.3	169.9	145.3	144.4	142.4	141.4	143.4
15°	292.6	238.7	185.6	163.0	155.1	154.2	157.1	160.1	159.1	162.0	163.9
17.5°	240.6	182.7	170.8	171.9	172.8	175.8	180.7	188.5	189.6	194.4	198.4
20°	196.4	193.5	198.4	202.2	205.3	211.1	221.9	231.8	234.7	241.6	249.5
22.5°	222.9	231.8	242.5	247.5	251.3	262.2	274.0	289.7	295.5	304.4	315.2
25°	269.0	283.8	300.4	306.4	312.3	330.0	343.7	362.3	367.2	378.0	388.9
27.5°	307.3	323.0	340.7	348.6	353.5	371.2	382.9	394.8	394.8	400.6	408.5
30°	301.5	314.3	328.9	334.9	336.9	349.5	361.4	365.2	363.3	366.3	372.1
32.5°	250.4	260.2	272.1	276.9	278.9	287.8	297.5	297.5	296.6	296.6	300.4
35°	185.6	192.5	198.4	203.3	206.2	212.1	221.0	219.9	219.9	217.9	221.0
37.5°	124.7	128.7	135.6	137.4	138.5	142.4	149.3	149.3	147.3	148.2	150.2
40°	75.6	80.5	84.5	85.4	87.4	90.3	95.3	95.3	95.3	95.3	96.2
42.5°	45.1	48.2	51.1	51.1	52.0	56.0	57.9	57.9	57.9	57.9	58.9
45°	26.5	27.5	29.4	30.5	30.5	32.3	33.4	33.4	33.4	33.4	34.3
47.5°	15.7	16.6	16.6	17.7	17.7	18.6	19.7	19.7	18.6	18.6	18.6
50°	9.8	9.8	9.8	9.8	10.8	10.8	10.8	10.8	10.8	10.8	9.8
52.5°	7.9	7.9	7.9	7.9	6.9	6.9	6.9	6.9	5.9	5.9	4.9
55°	6.9	6.9	6.9	6.9	6.9	5.9	5.9	5.9	4.9	4.0	2.9
57.5°	6.9	6.9	6.9	6.9	6.9	5.9	5.9	4.9	4.0	4.0	2.9
60°	6.9	6.9	6.9	6.9	6.9	5.9	5.9	4.9	4.0	4.0	2.9
62.5°	7.9	7.9	6.9	6.9	6.9	5.9	5.9	4.9	4.9	4.0	2.9
65°	7.9	7.9	6.9	6.9	6.9	6.9	5.9	5.9	4.9	4.0	2.9
67.5°	7.9	7.9	7.9	7.9	6.9	6.9	6.9	5.9	4.9	4.0	2.9
70°	8.8	8.8	7.9	7.9	7.9	6.9	6.9	5.9	4.9	4.9	4.0
72.5°	8.8	8.8	7.9	7.9	7.9	7.9	6.9	5.9	5.9	4.9	4.0
75°	8.8	8.8	8.8	8.8	7.9	7.9	6.9	6.9	5.9	4.9	4.0
77.5°	8.8	8.8	8.8	8.8	7.9	7.9	7.9	6.9	5.9	4.9	4.0
80°	8.8	8.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	4.9	4.0
82.5°	9.8	9.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	4.9	4.9
85°	9.8	9.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	5.9	4.9
87.5°	9.8	9.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	5.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212646

CATALOG NUMBER: LDSQA6A60930D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	974.2	974.2	974.2	974.2	974.2	974.2	974.2	974.2
2.5°	517.4	488.0	478.2	485.1	477.2	471.4	463.5	459.6
5°	324.1	302.4	295.5	297.5	290.7	284.7	276.9	275.0
7.5°	199.3	178.7	170.8	170.8	163.0	156.2	151.3	148.2
10°	133.6	129.6	130.5	131.6	130.5	131.6	128.7	130.5
12.5°	143.4	141.4	143.4	144.4	144.4	146.3	142.4	145.3
15°	167.0	165.0	167.9	169.9	169.9	172.8	169.0	171.9
17.5°	204.2	203.3	208.2	210.1	211.1	216.1	211.1	215.0
20°	258.2	257.3	264.1	267.0	266.1	275.9	269.0	275.9
22.5°	328.0	326.0	335.8	338.7	339.8	352.6	346.6	351.5
25°	397.7	399.7	404.6	409.5	410.5	421.2	412.4	417.4
27.5°	412.4	409.5	412.4	418.3	419.4	424.2	416.3	420.3
30°	373.2	368.3	369.2	376.1	378.0	380.0	373.2	375.1
32.5°	303.5	295.5	295.5	302.4	304.4	307.3	295.5	300.4
35°	223.9	217.0	217.0	221.9	222.9	224.9	216.1	219.9
37.5°	153.3	147.3	149.3	151.3	152.2	154.2	153.3	152.2
40°	98.2	94.2	97.2	97.2	98.2	99.1	99.1	100.2
42.5°	59.9	56.9	58.9	58.9	59.9	59.9	59.9	60.9
45°	34.3	33.4	33.4	34.3	34.3	34.3	33.4	34.3
47.5°	18.6	17.7	18.6	18.6	18.6	18.6	18.6	18.6
50°	9.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
52.5°	4.9	4.0	4.0	4.0	2.9	4.0	2.9	2.9
55°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
57.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
60°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
65°	2.0	0.9	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.9	2.0	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.9	2.0	2.0	0.9	0.9	0.0	0.0	0.0
72.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	2.9	2.9	2.0	2.0	0.9	0.9	0.9	0.0
80°	4.0	2.9	2.0	2.0	2.0	0.9	0.9	0.9
82.5°	4.0	2.9	2.0	2.0	2.0	0.9	0.9	0.9
85°	4.0	2.9	2.9	2.0	2.0	0.9	0.9	0.9
87.5°	4.0	2.9	2.9	2.0	2.0	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)