

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212648

Luminaire Tested: **LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5679.2 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212648

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212648

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45824	45824	45824
5°	125784	42222	17228
10°	275641	34556	6567
15°	421042	26308	7702
20°	487820	19574	11968
25°	532146	16091	19316
30°	594240	14597	19722
35°	604607	10013	13524
40°	615233	4749	6840
45°	616230	1967	2990
50°	520965	857	918
55°	167756	593	150
60°	33316	680	0
65°	3403	805	0
70°	365	1108	0
75°	0	1464	0
80°	0	2430	223
85°	0	4841	445

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212648

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.5	2.5
10°-20°	747.3	13.2
20°-30°	1430.8	25.2
30°-40°	1685.7	29.7
40°-50°	1324.1	23.3
50°-60°	322.7	5.7
60°-70°	13.9	0.2
70°-80°	5.2	0.1
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2322.5	40.9
0°-40°	4008.2	70.6
0°-60°	5655.0	99.6
0°-90°	5679.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5679.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1064	1064	1064	1064	1064	
5°	2910	2106	977	512	399	385
15°	9446	4852	590	169	173	2637
25°	11202	5899	339	354	407	5221
35°	11503	3729	190	246	257	7213
45°	10120	1153	32	45	49	7604
55°	2235	42	8	5	2	2660
65°	33	5	8	5	0	88
75°	0	5	9	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212648

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3
2.5°	1824.4	1820.4	1793.9	1818.4	1743.9	1740.9	1707.6	1692.8	1649.6	1608.3	1549.4
5°	2910.3	2846.6	2794.4	2796.4	2653.1	2626.5	2552.0	2476.3	2360.4	2252.4	2106.2
7.5°	4436.3	4360.6	4250.7	4204.5	3930.6	3850.0	3695.9	3494.6	3242.2	2990.9	2719.9
10°	6304.7	6316.6	6174.2	6042.6	5628.2	5465.2	5215.8	4819.2	4341.0	3868.7	3388.6
12.5°	8185.1	8177.3	8007.4	7808.1	7297.5	7067.7	6735.8	6241.0	5607.6	4875.2	4123.9
15°	9445.8	9501.8	9430.1	9271.0	8835.2	8571.9	8197.9	7526.2	6754.4	5864.9	4851.5
17.5°	10237.3	10290.3	10264.7	10140.1	9755.2	9474.3	9162.1	8612.2	7719.6	6601.3	5424.9
20°	10646.7	10730.1	10718.4	10582.8	10292.3	10059.6	9714.9	9205.3	8432.6	7112.8	5796.1
22.5°	10919.7	10983.5	11001.1	10848.0	10547.6	10326.6	10074.2	9557.7	8831.2	7425.1	5943.4
25°	11201.5	11314.4	11203.5	11014.9	10739.0	10526.9	10257.9	9763.0	9021.7	7552.8	5899.2
27.5°	11547.1	11601.1	11349.8	11177.9	10871.5	10641.8	10356.1	9881.8	9055.1	7450.6	5646.8
30°	11952.6	11728.7	11553.0	11212.3	10864.7	10640.8	10350.1	9807.2	8879.2	7111.9	5157.9
32.5°	11885.8	11680.7	11481.4	11121.0	10777.3	10555.4	10231.3	9558.8	8464.0	6545.4	4483.4
35°	11502.9	11547.1	11332.1	11033.6	10644.7	10416.0	10062.5	9205.3	7759.0	5763.8	3729.3
37.5°	11179.9	11277.2	11136.7	10860.8	10466.0	10156.7	9679.6	8637.8	6838.9	4772.1	3014.5
40°	10946.2	10977.6	10902.0	10592.7	10118.5	9671.6	9119.9	7618.5	5721.5	3745.9	2379.2
42.5°	10583.9	10667.3	10533.7	10196.1	9477.3	8971.6	8172.4	6441.2	4444.0	2861.2	1791.0
45°	10120.4	10199.9	10035.0	9473.4	8473.7	7732.4	6757.5	5022.5	3287.3	2109.1	1152.8
47.5°	9364.3	9413.4	9094.3	8317.7	6864.4	6166.4	5166.7	3501.4	2117.9	1179.3	560.6
50°	7777.6	7754.1	7096.2	6140.8	4591.4	3858.9	3075.3	1898.0	951.5	558.8	350.6
52.5°	5012.6	4958.6	4307.6	3438.6	2325.2	1774.3	1333.5	818.9	495.9	312.2	138.5
55°	2234.8	2214.2	1812.6	1408.0	951.5	818.9	625.4	401.5	264.1	109.0	42.2
57.5°	828.7	810.1	713.9	599.0	459.5	382.0	303.5	192.5	67.7	36.3	22.6
60°	386.9	385.8	339.8	279.8	194.4	147.3	85.4	45.1	28.5	19.7	12.8
62.5°	123.7	120.8	84.5	61.9	44.2	38.3	30.5	22.6	14.8	10.8	7.9
65°	33.4	33.4	30.5	25.5	20.6	17.7	14.8	10.8	6.9	5.9	4.9
67.5°	12.8	12.8	11.7	10.8	7.9	6.9	5.9	4.9	4.0	4.9	4.9
70°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	4.0	4.0	4.9
72.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	4.9
75°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	4.9
77.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	4.9
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.9	2.9	4.0	4.9	4.9
82.5°	0.0	0.0	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.9	5.9
85°	0.0	0.0	0.9	2.0	2.0	2.9	2.9	4.0	4.0	4.9	5.9
87.5°	0.0	0.0	0.9	2.0	2.0	2.9	2.9	4.0	4.0	4.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212648

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3
2.5°	1506.3	1441.4	1352.1	1300.1	1287.3	1259.8	1211.6	1140.0	1081.1	1024.1	990.8
5°	1982.5	1829.3	1657.4	1536.6	1487.6	1421.8	1305.0	1184.2	1073.2	976.9	901.4
7.5°	2487.1	2234.8	1956.9	1733.0	1652.5	1548.5	1358.0	1178.2	1026.0	892.6	791.5
10°	2988.9	2582.4	2205.3	1881.3	1749.8	1608.3	1357.0	1124.2	945.5	790.4	678.5
12.5°	3490.6	2906.4	2388.0	1970.6	1799.8	1621.1	1316.7	1041.7	843.5	685.3	578.3
15°	3954.1	3164.7	2511.7	2001.1	1794.9	1583.7	1235.3	941.7	736.4	590.2	490.9
17.5°	4299.8	3300.1	2540.2	1954.9	1717.3	1483.7	1110.5	823.8	634.3	505.7	404.6
20°	4469.7	3321.8	2472.4	1823.4	1583.7	1341.3	974.0	711.0	546.9	427.2	341.7
22.5°	4469.7	3219.6	2325.2	1658.4	1416.9	1177.3	842.4	617.6	478.2	372.1	300.4
25°	4299.8	3016.3	2127.7	1468.0	1233.3	1015.3	728.5	547.9	425.2	338.7	278.9
27.5°	3969.8	2735.6	1874.4	1255.8	1052.6	870.9	638.2	484.0	384.9	305.3	306.4
30°	3516.2	2390.9	1583.7	1032.0	867.0	715.8	537.1	405.5	308.4	293.6	302.4
32.5°	2991.8	1978.5	1254.9	800.2	671.6	563.6	408.4	286.7	245.5	247.5	257.3
35°	2453.7	1557.3	944.6	593.1	499.8	408.4	268.1	188.5	186.5	190.5	197.3
37.5°	1937.2	1165.6	683.4	434.0	335.8	251.3	144.3	129.6	129.6	133.6	137.4
40°	1451.2	826.7	470.3	257.3	163.0	114.8	91.3	84.5	83.4	84.5	89.4
42.5°	996.6	523.4	279.8	103.1	78.5	66.8	57.9	53.1	52.0	53.1	56.0
45°	559.7	322.1	109.0	55.0	47.1	42.2	36.3	33.4	32.3	32.3	34.3
47.5°	350.6	127.6	49.1	34.3	29.4	27.5	23.6	21.6	20.6	20.6	21.6
50°	134.5	50.0	30.5	22.6	19.7	17.7	15.7	13.7	12.8	12.8	13.7
52.5°	46.2	29.4	19.7	14.8	12.8	11.7	9.8	8.8	8.8	8.8	8.8
55°	25.5	17.7	11.7	8.8	7.9	7.9	7.9	7.9	7.9	7.9	7.9
57.5°	15.7	10.8	7.9	6.9	6.9	6.9	6.9	6.9	6.9	7.9	7.9
60°	8.8	6.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9
62.5°	5.9	5.9	5.9	5.9	5.9	5.9	6.9	6.9	7.9	7.9	7.9
65°	4.9	4.9	4.9	5.9	5.9	5.9	6.9	6.9	7.9	7.9	7.9
67.5°	4.9	4.9	5.9	5.9	5.9	6.9	6.9	7.9	7.9	7.9	7.9
70°	4.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9	8.8	8.8
72.5°	4.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	8.8	8.8	8.8
75°	5.9	5.9	5.9	6.9	6.9	6.9	7.9	8.8	8.8	8.8	8.8
77.5°	5.9	5.9	6.9	6.9	6.9	7.9	7.9	8.8	8.8	8.8	8.8
80°	5.9	5.9	6.9	6.9	7.9	7.9	8.8	8.8	8.8	9.8	9.8
82.5°	5.9	5.9	6.9	7.9	7.9	7.9	8.8	8.8	9.8	9.8	9.8
85°	5.9	6.9	6.9	7.9	7.9	7.9	8.8	8.8	9.8	9.8	9.8
87.5°	5.9	6.9	6.9	7.9	7.9	7.9	8.8	8.8	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212648

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3
2.5°	946.6	905.3	864.1	833.6	818.9	804.1	771.8	729.6	711.9	686.4	671.6
5°	824.7	755.0	700.1	663.8	642.2	613.7	576.3	535.1	511.6	485.1	467.4
7.5°	699.1	617.6	564.6	531.2	509.7	474.3	427.2	378.0	349.5	320.1	299.5
10°	589.1	511.6	451.7	413.4	385.8	344.7	297.5	263.2	238.7	213.0	192.5
12.5°	492.0	408.4	344.7	312.2	293.6	254.4	215.0	176.7	162.0	157.1	157.1
15°	398.6	323.0	269.0	241.6	221.9	179.7	171.9	169.9	168.8	167.9	169.9
17.5°	325.0	261.2	204.2	190.5	188.5	187.6	188.5	188.5	189.6	192.5	197.3
20°	273.0	214.1	210.1	211.1	211.1	215.0	219.9	223.9	227.8	232.7	241.6
22.5°	242.5	241.6	248.4	249.3	254.4	260.2	269.0	275.0	284.7	289.6	302.4
25°	279.8	286.7	299.5	303.5	311.3	321.0	334.9	342.7	354.4	360.4	375.1
27.5°	317.2	327.9	343.7	348.6	355.5	371.2	381.0	387.8	393.8	397.7	406.6
30°	314.2	324.1	339.8	340.7	350.6	361.3	367.2	373.2	377.0	376.1	381.0
32.5°	266.1	275.0	289.6	289.6	300.4	309.3	312.2	317.2	317.2	317.2	319.2
35°	204.2	210.1	219.9	222.9	231.8	237.6	239.6	245.5	245.5	243.5	243.5
37.5°	141.4	149.3	156.2	158.1	163.9	167.9	172.8	173.8	171.9	172.8	172.8
40°	92.3	97.2	102.2	103.1	108.0	111.0	115.9	115.9	116.8	115.9	117.9
42.5°	56.9	60.9	63.9	65.7	67.7	69.7	72.6	73.7	74.6	73.7	75.6
45°	35.4	37.4	39.3	40.3	41.2	42.2	45.1	45.1	45.1	45.1	46.2
47.5°	21.6	22.6	23.6	23.6	24.6	25.5	26.5	26.5	26.5	26.5	27.5
50°	12.8	13.7	13.7	13.7	14.8	14.8	15.7	15.7	15.7	14.8	15.7
52.5°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8	7.9	8.8
55°	7.9	7.9	6.9	6.9	6.9	6.9	6.9	5.9	4.9	4.9	4.0
57.5°	6.9	6.9	6.9	6.9	6.9	5.9	5.9	4.9	4.9	4.0	2.9
60°	6.9	6.9	6.9	6.9	6.9	5.9	5.9	4.9	4.0	4.0	2.9
62.5°	7.9	6.9	6.9	6.9	6.9	5.9	5.9	4.9	4.0	4.0	2.9
65°	7.9	7.9	6.9	6.9	6.9	5.9	5.9	4.9	4.9	4.0	2.9
67.5°	7.9	7.9	7.9	6.9	7.9	6.9	5.9	5.9	4.9	4.0	4.0
70°	8.8	7.9	7.9	7.9	7.9	6.9	6.9	5.9	4.9	4.0	4.0
72.5°	8.8	8.8	7.9	7.9	7.9	6.9	6.9	5.9	4.9	4.9	4.0
75°	8.8	8.8	7.9	7.9	7.9	6.9	6.9	5.9	5.9	4.9	4.0
77.5°	8.8	8.8	8.8	7.9	7.9	7.9	6.9	6.9	5.9	4.9	4.0
80°	8.8	8.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	4.9	4.0
82.5°	9.8	8.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	4.9	4.9
85°	9.8	9.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	5.9	4.9
87.5°	9.8	8.8	8.8	8.8	8.8	7.9	7.9	6.9	5.9	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212648

CATALOG NUMBER: LDSQA6A60930D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3
2.5°	656.8	649.0	649.0	635.3	633.3	622.5	631.4	625.4
5°	447.7	434.9	431.1	417.3	412.4	399.7	403.5	398.6
7.5°	281.8	269.0	265.1	255.3	249.3	239.6	240.5	237.6
10°	171.9	160.0	157.1	154.2	151.3	150.2	151.3	150.2
12.5°	156.2	155.1	153.1	154.2	152.2	153.1	154.2	153.1
15°	169.9	171.9	169.9	170.8	169.9	171.9	172.8	172.8
17.5°	199.3	203.3	201.3	204.2	203.3	208.2	208.2	208.2
20°	244.5	251.3	249.3	253.3	253.3	259.2	259.2	261.2
22.5°	307.3	316.1	315.2	324.1	322.1	328.9	328.9	330.9
25°	382.9	391.8	392.7	398.6	397.7	404.6	404.6	406.6
27.5°	414.3	419.2	418.3	421.2	422.3	426.1	429.1	427.2
30°	388.9	392.7	391.8	393.8	393.8	396.7	399.7	396.7
32.5°	327.0	329.9	329.9	333.8	330.9	331.8	336.7	333.8
35°	250.4	252.4	250.4	252.4	253.3	253.3	258.2	257.3
37.5°	178.7	179.7	179.7	182.7	179.7	179.7	184.5	185.6
40°	119.9	120.8	119.9	123.7	121.7	121.7	124.7	121.7
42.5°	76.6	77.6	76.6	79.6	77.6	79.6	80.5	81.4
45°	47.1	47.1	46.2	48.0	47.1	48.0	49.1	49.1
47.5°	27.5	27.5	26.5	28.5	27.5	27.5	27.5	28.5
50°	14.8	14.8	14.8	15.7	14.8	14.8	14.8	13.7
52.5°	7.9	7.9	6.9	7.9	6.9	6.9	6.9	6.9
55°	4.0	2.9	2.9	2.9	2.0	2.0	2.0	2.0
57.5°	2.9	2.0	2.0	0.9	0.9	0.9	0.0	0.0
60°	2.0	2.0	0.9	0.9	0.0	0.0	0.0	0.0
62.5°	2.0	2.0	0.9	0.9	0.0	0.0	0.0	0.0
65°	2.0	2.0	0.9	0.9	0.0	0.0	0.0	0.0
67.5°	2.9	2.0	2.0	0.9	0.9	0.0	0.0	0.0
70°	2.9	2.0	2.0	0.9	0.9	0.0	0.0	0.0
72.5°	2.9	2.0	2.0	2.0	0.9	0.9	0.0	0.0
75°	2.9	2.9	2.0	2.0	0.9	0.9	0.0	0.0
77.5°	4.0	2.9	2.0	2.0	0.9	0.9	0.0	0.0
80°	4.0	2.9	2.0	2.0	2.0	0.9	0.9	0.9
82.5°	4.0	2.9	2.9	2.0	2.0	0.9	0.9	0.9
85°	4.0	2.9	2.9	2.0	2.0	0.9	0.9	0.9
87.5°	4.0	2.9	2.9	2.0	2.0	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)